

ELECTRICAL COMPONENTS



Part Name	Part Number	List Price
MODEL WFDT - WATERFLOW DETECTOR		
1" - 2" T-Tap Waterflow	TTAP	\$ 238.13
1" - 2" Threaded T-Tap Waterflow	TTAPTH	\$ 238.13
MODEL WFD - WATERFLOW DETECTOR		
2"	2W	\$ 231.56
2-1/2"	25W	\$ 231.56
3"	3W	\$ 231.56
3-1/2"	35W	\$ 231.56
4"	4W	\$ 231.56
5"	5W	\$ 231.56
6"	6W	\$ 231.56
8"	8W	\$ 258.75
MODEL EPS PRESSURE SWITCH		
EPS10-1	6999991339	\$ 199.98
EPS10-2	6999991212	\$ 231.33
EPS40-1	6999991213	\$ 199.98
EPS40-2	6999991340	\$ 231.33
MODEL OSY2 - TAMPER SWITCH		
Supervisory Switch for OS & Y	OST	\$ 153.75
MODEL PIB V2 - TAMPER SWITCH		
Supervisory Switch for PIV/Butterfly Valves	PIT	\$ 144.38
MODEL PSP1 - TAMPER SWITCH		
Plug in style Supervisory Switch	PSP1	\$ 293.44
ACCESSORIES		
1 & 1-1/2" Waterflow Detector Gasket	6999990717	\$ 12.19
2 & 3-1/2" Waterflow Detector Gasket	6999990357	\$ 12.19
4 - 8" Waterflow Detector Gasket	6999990356	\$ 12.19
Repl. Terminal block	6999990957	\$ 63.75
Repl. Timer	6999992444	\$ 83.44
Waterflow Detector Tamper Switch Kit	6923000000	\$ 45.94
Wrench Cover (Key)	6999990769	\$ 15.00
Plastic Cover	6999990595	\$ 37.00
ELECTRIC ALARM BELLS & HORN/STROBE		
6" -- 24 VDC	6KMS	\$ 72.69
8" -- 24 VDC	8KMS	\$ 90.86
10" -- 24VDC	10KMS	\$ 102.62
BRK MA Polarized Sounder -- 24 VDC	6999993325	\$ 155.90
BRK MASS Polarized Sounder Strobe (#P2R)	6990006617	\$ 114.00
P2RHK-120	6990001425	\$ 168.00
6" -- 120 VAC	6KBS	\$ 72.69
8" -- 120 VAC	8KBS	\$ 90.86
10" -- 120 VAC	10KBS	\$ 102.62
WBB Weatherproof Back Box	WBB	\$ 40.62

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

ELECTRICAL COMPONENTS CANADIAN VERSIONS



Part Name	Part Number	List Price
MODEL WFDTA - WATERFLOW DETECTOR		
1" - 2" T-Tap Waterflow	6930000003	\$ 249.38
1" - 2" Threaded T-Tap Waterflow	6930000004	\$ 249.38
MODEL WFDA - WATERFLOW DETECTOR		
2"	6983020050	\$ 242.81
2-1/2"	6983025050	\$ 242.81
3"	6983030050	\$ 242.81
4"	6983040050	\$ 242.81
5"	6983050050	\$ 242.81
6"	6983060050	\$ 242.81
8"	6983080050	\$ 270.00
MODEL EPSA PRESSURE SWITCH		
EPSA10-1	6999992366	\$ 162.19
EPSA10-2	6999992360	\$ 185.63
EPSA40-1	6999992367	\$ 162.19
EPSA40-2	6999992361	\$ 185.63
EPSA120-1	6999992534	\$ 207.19
EPSA120-2	6990007994	\$ 261.56
MODEL OSY2A - TAMPER SWITCH		
Supervisory Switch for OS & Y	6999992362	\$ 170.63
MODEL PIB V2A - TAMPER SWITCH		
Supervisory Switch for PIV/Butterfly Valves	6985020001	\$ 151.88
MODEL PSP1A - TAMPER SWITCH		
Plug in style Supervisory Switch	6990007844	\$ 292.50

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.