

UL & FM APPROVED RECESSED SPRINKLERS



Model	Nominal Orifice Size (in.)	Nominal Thread Size (NPT)	K-Factor	UL Approved Escutcheons	FM Approved Escutcheons
F1 SSP	3/8	1/2	2.82	F1, F2, FP	-
F1 SSP	7/16	1/2	4.24	F1, F2, FP	-
F1 SSP	1/2	1/2	5.6	F1, F2, FP	F2
F1FR SSP	1/2	1/2	5.6	F1, F2, FP	F2
F1FR SSP	3/8	1/2	2.82	F1, F2, FP	-
F1FR SSP	7/16	1/2	4.24	F1, F2, FP	-
F1 EC-P	1/2	1/2	5.6	F1, F2, FP	-
F1FR EC-P	1/2	1/2	5.6	F1, F2, FP	-
F1 SSP	17/32	3/4	8.0	F1, F2, FP	F2
F1FR SSP	17/32	3/4	8.0	F1, F2, FP	F2
F1FR HSW	1/2	1/2	5.6	F1, F2, FP	-
F1 EC-P	17/32	3/4	8.0	F1, F2, FP	-
F1FR EC-P	17/32	3/4	8.0	F1, F2, FP	F2
F1FR HSW EC-8	1/2	1/2	5.6	F1, F2	F2
F1FR HSW EC-9	17/32	3/4	8.0	F1, F2	F2
F1-300 SSP	1/2	1/2	5.6	F1, F2, FP	-
F1FR-300 SSP	1/2	1/2	5.6	F1, F2, FP	-
F1-300 EC-P	1/2	1/2	5.6	F1, F2, FP	-
F1FR-300 EC-P	1/2	1/2	5.6	F1, F2, FP	-
F1-300 SSP	17/32	3/4	8.0	F1, F2, FP	-
F1FR-300 SSP	17/32	3/4	8.0	F1, F2, FP	-
F1-300 EC-P	17/32	3/4	8.0	F1, F2, FP	-
F1FR-300 EC-P	17/32	3/4	8.0	F1, F2, FP	-
F1FR-300 HSW EC-9	17/32	3/4	8.0	F1, F2	-
F1 RES 16 (Pendent)	3/8	1/2	3.0	F1, F2	-
F1 RES 18 (Pendent)	3/8	1/2	3.9	F2, FP	-
F1 RES 20 (Pendent)	7/16	1/2	4.2	F1, F2	-
F1 RES 2 (Pendent)	7/16	1/2	4.2	F2	-
F1 RES (Pendent)	1/2	1/2	5.6	F2	-
HSW F1/RES 3	3/8	1/2	3.9	F2	-
HSW F1/RES	1/2	1/2	5.6	F2	-
F1 RES 49 (Pendent)	7/16	1/2	4.9	F1, F2, FP	-
F1 RES 40 HSW	3/8	1/2	4.0	F2	-
F1 RES 44 HSW	3/8	1/2	4.4	F2	-
F1 RES 58 HSW	1/2	1/2	5.8	F2	-
F1 RES 58 (Pendent)	1/2	1/2	5.8	F1, F2, FP	-
F1 RES 76 Pendent	17/32	3/4	7.6	F1, F2, FP	-
F1 RES 30 Pendent	21/64	1/2	3.0	F2, FP	-
N252	1	1	25.2	FP	-
F3 HSW	1/2	1	5.6	F1, F2, FP	F1, F2, FP
F3QR HSW	1/2	1	5.6	F1, F2, FP	F1, F2, FP
F3QR (Pendent)	1/2	1	5.6	F1, F2, FP	F1, F2, FP
DH80	17/32	3/4	8.0	F2, FP	-
DH56	1/2	1/2	5.6	F2, FP	-
DH56 DRY	1/2	1	5.6	FP	-
F156	1/2	1/2	5.6	F1, F2, FP	F2
F1FR56	1/2	1/2	5.6	F1, F2, FP	F2
SW56	1/2	1/2	5.6	FP	-
G	1/2	1/2	5.6	F1, F2	-
G	7/16	1/2	4.2	F1, F2	-
G	3/8	1/2	2.8	F1, F2	-
G	1/2	1/2	5.6	GF1, F2	GF1, F2
G	17/32 (11 mm)	1/2	4.2	GF1, F2	-
G	3/8	1/2	2.8	GF1, F2	-
G	17/32 (20mm)	1/2	7.96	GF1, F2	-
JL112 Pendent	5/8	3/4	11.2	F1, F2, FP	-

P/N 9999970374