Reliable

Storz Connections

Product Description

Reliable Storz Connections provide a quick connection of large diameter hose by Fire Service Professionals to fire sprinkler or standpipe systems. Conforms with NFPA 1963 requirements. Constructed with forged aluminum.

Installation

The Reliable Storz Connections and Storz accessories shall be installed in accordance with NFPA 13, "Standard for the Installation of Sprinkler Systems," as well as the requirements of any authorities having jurisdiction. Verify compatibility of the Reliable Storz connection materials with the water supply and the environment where the valve will be installed prior to installation.

Maintenance

The owner is responsible for maintaining the fire protection system in proper operating condition. Any system maintenance or testing that involves placing a control valve out of service will eliminate the fire protection that is provided by the fire protection system.

The Reliable Storz Connections and Storz accessories shall periodically be given a thorough inspection and test. NFPA 25, "Inspection, Testing and Maintenance of Water Based Fire Protection Systems," provides minimum maintenance requirements.

Guarantee

For Reliable Automatic Sprinkler Co., Inc. guarantee, terms, and conditions, visit www.reliablesprinkler.com.

Ordering Information

Specify the following when ordering:


| Reliable Storz Connection |
|---------------------------------------|
| 4" Storz x 4" FNPT |
| 5" Storz x 4" FNPT |
| 4" Storz x 4" FNPT w/ Cap |
| 5" Storz x 4" FNPT w/ Cap |
| 4" Storz x 4" FNPT w/ 30° Elbow |
| 5" Storz x 4" FNPT w/ 30° Elbow |
| 4" Storz x 4" FNPT w/ 30° Elbow & Cap |
| 5" Storz x 4" FNPT w/ 30° Elbow & Cap |
| 4" Storz Cap & Chain |
| 5" Storz Cap & Chain |
| Storz Wall Connection Plate |



Storz Connection with Cap



Storz Connection with 30° Elbow and Cap



Storz Connection Wall Plate

Storz Connections

Inlet: 4" or 5" Storz connection Outlet: 4" FNPT Threads

Configuration: Straight or 30° Elbow

Accessories: Cap and chain Wall connection plate **Material Specifications**

Body: Forged 6061 T-6 Aluminum Alloy

Finish: Powder Coated Seal: Metal Face

Wall Plate: 6061 Aluminum Alloy Red Painted Chain: Q235A Steel Alloy Black Painted Bushing: 6061 Aluminum Alloy Silver grey powder

coated outside

Screen: Type 304 Stainless Steel

Lock Mechanism: Type 304 Stainless Steel

Spring: Type 302 Stainless Steel **Screw:** Type 304 Stainless Steel

Lock, quick disconnect: 6061 Aluminum Alloy Silver

grey powder coated outside

Gasket: NBR nitrile rubber (A60+-5)

Cap: 6061 Aluminum Alloy Silver grey powder coated

outside


Retaining Ring: Type Type 304 Stainless Steel Adapter, quick disconnect: 6061 Aluminum Alloy


Silver grey powder coated outside



Storz with Wall Plate, Cap and Chain Specification and Dimensions

Figure 1







Storz with 30° Elbow, Wall Plate, Cap and Chain Specification and Dimensions

Figure 2

