



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover
- cULus listed and FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	£ 7,846.66
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		£ 8,559.99
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		£ 8,559.99
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		£ 8,559.99
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		£ 8,559.99
1-1/2" ISO7-1 Thread/Thread	6507608000		£ 8,559.99
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	£ 7,846.66
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		£ 8,559.99
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		£ 8,559.99
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		£ 8,559.99
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		£ 8,559.99
2" ISO7-1 Thread/Thread	6507628000		£ 8,559.99
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	£ 9,094.99
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		£ 9,094.99
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		£ 9,897.49
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		£ 9,897.49
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		£ 9,897.49
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		£ 9,897.49
2-1/2" ISO7-1 Thread/Thread	6507618000		£ 9,897.49
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	£ 9,094.99
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		£ 9,897.49
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		£ 9,897.49
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		£ 9,897.49
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		£ 9,897.49
3" ISO7-1 Thread/Thread	6507638000		£ 9,897.49
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	£ 10,878.32
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		£ 11,859.15
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		£ 11,859.15
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		£ 11,859.15
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	£ 13,374.99
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		£ 13,374.99
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		£ 14,712.49
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		£ 14,712.49
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		£ 14,712.49

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

"0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges

"1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges

"2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges

"3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges