

ACCESSORIES

CABINETS

Description	Part Number	Short Code	List Price
A4 EMERGENCY CABINETS FOR LL RESIDENTIAL SPRINKLERS			
3 Capacity	6999991473	3CAB	\$ 118.97
6 Capacity	6999991470	6CAB	\$ 118.97
6 Capacity (Large)	6999991472	6LCAB	\$ 213.14
12 Capacity	6999991471	12CAB	\$ 147.61
A3 EMERGENCY CABINETS FOR RECESSED, CONCEALED LL RESIDENTIAL SPRINKLERS			
12 Capacity	6803200000	A312CAB	\$ 576.91

ESCUTCHEONS

Part Number	Short Code	Temperature	Finish	List Price
ONE PIECE TYPE - MODEL B 1/2"				
6800110000	BB	165°F	Bright Brass	\$ 5.10
6800150000	BC	165°F	Chrome	\$ 3.50
6800120000	BW	165°F	White	\$ 3.94
ONE PIECE TYPE - MODEL B 3/4"				
6800080000	BLB	165°F	Bright Brass	\$ 5.38
6800070000	BLC	165°F	Chrome	\$ 3.77
6800090000	BLW	165°F	White	\$ 3.77
ONE PIECE TYPE - MODEL C 1/2"				
6800340000	CBB	165°F	Bright Brass	\$ 38.85
6800350000	CC	165°F	Chrome	\$ 3.74
6800380000	CW	165°F	White	\$ 3.74
TWO PIECE TYPE - MODEL HB 1/2"				
6800210000	HBB	165°F	Brass	\$ 8.89
6800270000	HBC	165°F	Chrome	\$ 8.00
6800200000	HBW	165°F	White	\$ 8.29
TWO PIECE TYPE - MODEL HB 3/4"				
6800220000	HBLB	165°F	Brass	\$ 9.17
6800240000	HBLC	165°F	Chrome	\$ 8.29
6800250000	HBLW	165°F	White	\$ 8.89
FLUSH ESCUTCHEONS - MODEL B				
86791100	BFB	165°F	Brass	\$ 61.97
86792100	BFC	165°F	Chrome	\$ 96.26
86797200	BFW	165°F	White	\$ 96.26



ESCUTCHEONS

Description	Part Number	Short Code	List Price
MODEL FP PUSH-ON/THREAD-OFF ESCUTCHEONS			
1/2" Chrome	6801412100	FPC	\$ 23.82
1/2" White	6801417200	FPW	\$ 23.82
3/4" Chrome	6801402100	FPLC	\$ 23.82
3/4" White	6801407200	FPLW	\$ 23.82
MODEL F1 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800630001	GF1B	\$ 22.89
1/2" Chrome	6800600001	GF1C	\$ 12.35
1/2" White	6800640001	GF1W	\$ 12.35
3/4" Brass	6801030000	GF1LB	\$ 22.89
3/4" Chrome	6801000000	GF1LC	\$ 12.35
3/4" White	6801040000	GF1LW	\$ 12.35
ESCUTCHEON ONLY			
Brass	6800430000	BZESCF1	\$ 17.46
Chrome Bright	6800400000	CBESCF1	\$ 7.43
White	6800440000	WHESCF1	\$ 7.43
COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	\$ 13.67
1/2" Chrome Bright	6800500000	CBCOLLAR12	\$ 11.21
1/2" White	6800540000	WHCOLLAR12	\$ 11.21
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome Bright	6800560001	CBCOLLAR34	\$ 11.21
3/4" White	6800551003	WHCOLLAR34	\$ 11.21
ESCUTCHEON EXTENDER RING			
Chrome	6814002100	EERC	\$ 15.86
White	6814001500	EERW	\$ 16.91
F1 OR F2			
4-1/2" Chrome	6814002100	EERC	\$ 15.86
4-1/2" White	6814001500	EERW	\$ 16.91
5-1/2" Chrome	6814042100	EERC5	\$ 15.86
5-1/2" White	6814041500		\$ 16.91
FP / G4 / RFC43 / F4FR / CCP / SWC / DH80 / DH56			
4-1/2" Chrome	6814022100	G4ERC	\$ 15.86
4-1/2" White	6814021800		\$ 16.91
5-1/2" Chrome	6814032100	G4ERC5	\$ 15.86
5-1/2" White	6814031800	G4ERW5	\$ 16.91

MODEL F2 RECESSED ESCUTCHEONS & COLLAR ASSEMBLY			
1/2" Brass	6800830000	GF2B	\$ 22.89
1/2" Chrome	6800800000	GF2C	\$ 12.35
1/2" White	6800840000	GF2W	\$ 12.35
3/4" Brass	6800880004	GF2LB	\$ 22.89
3/4" Chrome	6800880001	GF2LC	\$ 12.35
3/4" White	6800880005	GF2LW	\$ 12.35
ESCUTCHEON ONLY			
Brass	6800730000	BZESCF2	\$ 17.34
Chrome	6800100000		\$ 11.18
White	6800740000	WHESCF2	\$ 11.18
COLLAR ONLY			
1/2" Brass	6800530000	B2COLLAR12	\$ 13.67
1/2" Chrome	6800500000	CBCOLLAR12	\$ 11.21
1/2" White	6800540000	WHCOLLAR12	\$ 11.21
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome	6800560001	CBCOLLAR34	\$ 11.21
3/4" White	6800551003	WHCOLLAR34	\$ 11.21

G/F1 for use with SP & HSW Sprinklers
G/F2 for use with SP & HSW Sprinklers
G/F2 for use with SP & HSW Sprinklers



**MP LL
 Multipurpose
 Residential Riser**

• See Bulletin 426

Accessories

Description	Part Number	Short Code	List Price
MODEL MPLL MULTIPURPOSE RESIDENTIAL RISER			
Model MP LL 1" (30mm)	6501200125	1MPLL	\$ 1,238.11
RISER ACCESSORIES			
Optional Support Bracket Kit	6899190001	RRB	\$ 120.74

Description	Part Number	Short Code	List Price
PRESSURE GAUGES			
WATER	98248001	WATER	\$ 124.70
AIR	98248000	AIR	\$ 133.33
Air (0-60 oz/in ²)	98248002	AIRO	\$ 472.26
INSPECTORS TEST CONNECTIONS			
Sight Test Type (Model B)	6851010000	ISC	\$ 515.02
Blind Test Type (Model A)	6851020000	IBC	\$ 171.68
AUTOMATIC BALL DRIPS			
1/2" NPT (Female)	78653500	5ABD	\$ 295.96
3/4" NPT (Female)	78653700	75ABD	\$ 338.17
MECHANICAL BALL DRIPS			
1/2" NPT (Female)	78653100	5MBD	\$ 528.32
STRAINER			
3/4" NPT (Female)	78650200	34ST	\$ 310.50
MISCELLANEOUS			
Model C Sight Drain 2" NPT (Female)	6863000000	2ISC	\$ 558.65
Model B Drum Drip Only 3/4" NPT (Female)	71010448		\$ 339.33
Model A Fill Cup 1/2" NPT (Female)	75000050	5FC	\$ 160.15
Model A Fill Cup 3/4" NPT (Female)	75000075	75FC	\$ 181.20
Model A Control Valve Seal Only	6869800000		\$ 44.26
SIGNS—MODEL A			
Valve Control Sign	6892011000	VCS	\$ 18.55
SIGNS—MODEL B			
Inspector Test Sign	6892110000	ITS	\$ 4.28
Open Sprinkler Control Sign	6892030000	OSCS	\$ 4.28
Open Sprinkler Drain Sign	6892040000	OSDS	\$ 4.28
Test Valve Sign	6892050000	TVS	\$ 4.28
Water Motor Line Sign	6892060000	WMLS	\$ 4.28
Auxiliary Drain Sign	6892070000	ADS	\$ 4.28
Main Drain Sign	6892080000	MDS	\$ 4.28
Drain Sign	6892090000	DS	\$ 4.28
Alarm Test Sign	6892100000	ATS	\$ 4.28
SIGNS—MODEL C			
Cold Weather Sign	6892010000	CWS	\$ 12.00
SIGNS—MODEL D			
Fire Alarm Sign	6892020000	FAS	\$ 18.55
SIGNS—MODEL E			
Hydraulically Calculated System	6892120000	HCS	\$ 12.42

ELECTRICAL COMPONENTS



Description	Part Number	Short Code	List Price
MODEL WFDT - WATERFLOW DETECTOR			
1" - 2", w/1" NPT T-Tap Waterflow	7M99003216	TTAPN	\$ 400.00
ACCESSORIES			
1 & 1-1/2" Waterflow Detector Gasket	6999990717		\$ 25.00
2 & 3-1/2" Waterflow Detector Gasket	6999990357		\$ 25.00
4 - 8" Waterflow Detector Gasket	6999990356		\$ 25.00
Repl. Terminal block			\$ Call
Repl. Timer	6999992444	TIMER	\$ 150.00
Waterflow Detector Tamper Switch Kit	6923000000	5467000	\$ 80.00
Wrench Cover (Key)	6999990769	WFDW	\$ 27.00
Cover	6999991174		\$ 38.80
ELECTRIC ALARM BELLS & HORN/STROBE			
6" -- 24 VDC	6611220400	6KMS	\$ 108.30
8" -- 24 VDC	6611220500	8KMS	\$ 137.99
10" -- 24VDC	6611220600	10KMS	\$ 157.05
BRK MA Polarized Sounder -- 24 VDC	6999993325	HORNWBB24	\$ 206.96
BRK MASS Polarized Sounder Strobe (#P2R)	6990006617	P2RL	\$ 159.12
P2RHK-120	6990001425	HORNWBB	\$ 234.00
6" -- 120 VAC	6611221100	6KBS	\$ 108.30
8" -- 120 VAC	6611221200	8KBS	\$ 137.99
10" -- 120 VAC	6611221300	10KBS	\$ 157.05
WBB Weatherproof Back Box	6611660200	WBB	\$ 59.31