



PRV DIAPHRAGM PRESSURE REGULATING VALVE

- See Bulletin 820
- 400 psi (27.6 Bar) Rated Pressure
- Adjusted with Pilot Operated Regulator
- Trim Includes Relief Valve
- No Trim Connections to Cover
- cULus listed and FM approved

Description	Part Number	Short Code	List Price
MODEL PRV DIAPHRAGM PRESSURE REGULATING VALVES			
1-1/2" Groove/Groove (ANSI/AWWA C606)	6507008000	15PRV	S\$13,996.76
1-1/2" Flange/Flange Class 150 (ASME B16.5)	6507108000		S\$15,269.19
1-1/2" Flange/Flange Class 300 (ASME B16.5)	6507208000		S\$15,269.19
1-1/2" Flange/Flange PN16 (ISO 7005-2)	6507308000		S\$15,269.19
1-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507508000		S\$15,269.19
1-1/2" ISO7-1 Thread/Thread	6507608000		S\$15,269.19
2" Groove/Groove (ANSI/AWWA C606)	6507028000	2PRV	S\$13,996.76
2" Flange/Flange Class 150 (ASME B16.5)	6507128000		S\$15,269.19
2" Flange/Flange Class 300 (ASME B16.5)	6507228000		S\$15,269.19
2" Flange/Flange PN16 (ISO 7005-2)	6507328000		S\$15,269.19
2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507528000		S\$15,269.19
2" ISO7-1 Thread/Thread	6507628000		S\$15,269.19
2-1/2" Groove/Groove (ANSI/AWWA C606)	6507018000	25PRV	S\$16,223.51
76MM,PRV,GE,PRESS REG,W/O CV VERT RED	6507078000		S\$16,223.51
2-1/2" Flange/Flange Class 150 (ASME B16.5)	6507118000		S\$17,655.00
2-1/2" Flange/Flange Class 300 (ASME B16.5)	6507218000		S\$17,655.00
2-1/2" Flange/Flange PN16 (ISO 7005-2)	6507318000		S\$17,655.00
2-1/2" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507518000		S\$17,655.00
2-1/2" ISO7-1 Thread/Thread	6507618000		S\$17,655.00
3" Groove/Groove (ANSI/AWWA C606)	6507038000	3PRV	S\$16,223.51
3" Flange/Flange Class 150 (ASME B16.5)	6507138000		S\$17,655.00
3" Flange/Flange Class 300 (ASME B16.5)	6507238000		S\$17,655.00
3" Flange/Flange PN16 (ISO 7005-2)	6507338000		S\$17,655.00
3" NPT Thread/Thread (ANSI/ASME B1.20.1)	6507538000		S\$17,655.00
3" ISO7-1 Thread/Thread	6507638000		S\$17,655.00
4" Groove/Groove (ANSI/AWWA C606)	6507048000	4PRV	S\$19,404.59
4" Flange/Flange Class 150 (ASME B16.5)	6507148000		S\$21,154.19
4" Flange/Flange Class 300 (ASME B16.5)	6507248000		S\$21,154.19
4" Flange/Flange PN16 (ISO 7005-2)	6507348000		S\$21,154.19
6" Groove/Groove (ANSI/AWWA C606)	6507068000	6PRV	S\$23,858.11
165MM Groove/Groove (ANSI/AWWA C606)	6507058000		S\$23,858.11
6" Flange/Flange Class 150 (ASME B16.5)	6507168000		S\$26,243.92
6" Flange/Flange Class 300 (ASME B16.5)	6507268000		S\$26,243.92
6" Flange/Flange PN16 (ISO 7005-2)	6507368000		S\$26,243.92

Notes:

Part numbers shown include a 185 psi (12.8 Bar) relief valve and 300 psi (20.7 Bar) gauges. Replace the last digit in the part number as follows for other relief valve and gauge combinations:

"0"-185 psi (12.8 Bar) relief valve and 300 psi (20 Bar) gauges

"1"-260 psi (17.9 Bar) relief valve and 300 psi (20 Bar) gauges

"2"-185 psi (12.8 Bar) relief valve and 600 psi (40 Bar) gauges

"3"-260 psi (17.9 Bar) relief valve and 600 psi (40 Bar) gauges