

CPVC Pipe and Anti-Freeze



Description	Part Number	Short Code	Per Lift Qty	Box Qty	List Price
PIPE*					
3/4" x 15'	7199030000	75CPVCS	7800 ft	390 ft	£ 2.68
3/4" x 10'	7199030010	75CPVC10S	5200 ft	260 ft	£ 2.68
1" x 15"	7199040000	1CPVCS	5100 ft	255 ft	£ 4.03
1" x 10'	7199040010	1CPVC10S	3400 ft	170 ft	£ 4.03
1-1/4" x 15'	7199050000	125CPVCS	2700 ft	135 ft	£ 6.52
1-1/4" x 10'	7199050010	125CPVC10S	1800 ft	90 ft	£ 6.52
1-1/2" x 15'	7199060000	15CPVCS	2520 ft	105 ft	£ 9.15
1-1/2" x 10'	7199060010	15CPVC10S	1680 ft	70 ft	£ 9.15
2" x 15'	7199080000	2CPVCS	1800 ft	75 ft	£ 13.91
2" x 10'	7199080010	2CPVC10S	1200 ft	50 ft	£ 13.91
2-1/2" x 15'	7199100000	25CPVCS	1260 ft	60 ft	£ 23.57
2-1/2" x 10'	7199100010	25CPVC10S	840 ft	40 ft	£ 23.57
3" x 15'	7199120000	3CPVCS	945 ft	45 ft	£ 35.68
3" x 10'	7199120010	3CPVC10S	630 ft	30 ft	£ 35.68

Description	Part Number	List Price
NOBLE ELIMINATORS		
NOBLE,FF ELIMINATOR 1330, 5 GAL PAIL	6990028241	£ 454.55
NOBLE,FF ELIMINATOR 1330, 30 GAL DRUM	6990028242	£ 2,715.91
NOBLE,FF ELIMINATOR 1330, 55 GAL DRUM	6990028243	£ 4,977.27
NOBLE,FF ELIMINATOR 1330, 275 GAL TOTE	6990028244	£ 24,886.34
NOBLE,FF ELIMINATOR 1330, 330 GAL TOTE	6990028245	£ 29,863.61

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

CPVC Hangers



Description	Part Number	Short Code	Box Qty	List Price
CPVC HANGERS - SINGLE FASTENER - 075				
3/4"	7M99001900	751HSPHD	100	£ 2.96
1"	7M99001901	11HSPHD	100	£ 3.11
1-1/4"	7M99001902	1251HSPHD	100	£ 3.33
1-1/2"	7M99001903	151HSPHD	100	£ 3.54
2"	7M99001904	21HSPHD	100	£ 3.92
CPVC HANGERS - DOUBLE FASTENER - 070				
3/4"	7M99001905	752HSPHD	100	£ 2.96
1"	7M99001906	12HSPHD	100	£ 3.11
1-1/4"	7M99001907	1252HSPHD	100	£ 3.33
1-1/2"	7M99001908	152HSPHD	100	£ 3.54
2"	7M99001909	22HSPHD	100	£ 3.92
CPVC HANGERS - SIDEMOUNT FASTENER - 077				
3/4"	7M99001910	75SMPHD	100	£ 3.14
1"	7M99001911	1SMPHD	100	£ 3.21
1-1/4"	7M99001912	125SMPHD	100	£ 3.39
1-1/2"	7M99001913	15SMPHD	100	£ 3.75
2"	7M99001914	2SMPHD	100	£ 4.05
CPVC HANGERS - STAND OFF FASTENER - 076				
3/4"	7M99001915	75NBPHD	100	£ 3.14
1"	7M99001916	1NBPHD	100	£ 3.21
1-1/4"	7M99001917	125NBPHD	100	£ 3.39
1-1/2"	7M99001918	15NBPHD	100	£ 3.75
2"	7M99001919	2NBPHD	100	£ 4.05
SURGE RESTRAINER - 055				
3/8"	7M99001920	SURGEPHD	100	£ 3.88

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

Fire Stop



Description	Approvals	Part Number	List Price
LCI INTUMESCENT SEALANT			
10.1 OZ TUBE	UL/FM/CPVC	7M99002726	£ 25.94
20 OZ SAUSAGE	UL/FM/CPVC	7M99002728	£ 45.39
5 GALLON PAIL	UL/FM/CPVC	7M99002727	£ 1,114.58
WF300 FIRESTOP CAULK			
10.1 OZ TUBE	UL/CPVC	7M99002729	£ 22.95
20 OZ SAUSAGE	UL/CPVC	7M99002731	£ 40.53
5 GALLON PAIL	UL/CPVC	7M99002730	£ 729.54
SMOKE AND SOUND ACOUSTICAL SEALANT (WHITE)			
20 OZ SAUSAGE	UL	7M99002732	£ 18.94
5 GALLON PAIL	UL	7M99002733	£ 689.01
FIRE STOP COLLARS			
LCC150	UL/FM	7M99002755	£ 28.82
LCC200	UL/FM	7M99002756	£ 32.82
LCC300	UL/FM	7M99002757	£ 51.09
LCC400	UL/FM	7M99002758	£ 77.23

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

PLASTIC PIPE FITTINGS



Description	Part Number	Short Code	Box Qty	List Price
45° ELBOWS				
3/4"	7103030300	P7545	20	£ 4.37
1"	7103040400	P145	15	£ 5.20
1-1/4"	7103050500	P12545	10	£ 7.63
1-1/2"	7103060600	P1545	10	£ 10.48
2"	7103080800	P245	10	£ 13.17
2-1/2"	7103101000	P2545	5	£ 23.46
3"	7103121200	P345	5	£ 33.95
90° ELBOWS				
3/4"	7107030300	P7590	30	£ 2.78
1"	7107040400	P190	20	£ 6.30
1-1/4"	7107050500	P12590	10	£ 8.14
1-1/2"	7107060600	P1590	10	£ 11.31
2"	7107080800	P290	25	£ 15.62
2-1/2"	7107101000	P2590	5	£ 30.49
3"	7107121200	P390	5	£ 41.61
90° ELBOWS - SIDE OUTLET				
3/4"	7107030303	P7590SO	50	£ 5.18
1"	7107040404	P190SO	25	£ 9.10
90° ELBOWS - REDUCING				
1" x 3/4"	7109040300	P175R90	20	£ 6.34
90° ELBOWS - SPRINKLER HEAD ADAPTER (BRASS)				
3/4" x 1/2"T	7109030201	P755SHA90	20	£ 8.05
1" x 1/2"T	7109040201	P15SHA90	10	£ 10.20
1" x 3/4"T	7109040301	P175SHA90	25	£ 12.58
1-1/4" x 1/2"T	7109050201	P1255SHA90	10	£ 14.11
90° ELBOWS - SPRINKLER HEAD ADAPTER (STAINLESS STEEL)				
3/4" x 1/2"T	7109030200	P755SHA90S	20	£ 7.32
1" x 1/2"T	7109040200	P15SHA90S	10	£ 8.05
90 ELBOWS SWEEP STYLE				
SPEARS,#4206-010S,ELBOW,90,1"(SWEEP)	6990023464	P190S	12	£ 13.07
TEE - STRAIGHT				
3/4"	7111030303	P75T	20	£ 3.80
1"	7111040404	P1T	15	£ 7.77
1-1/4"	7111050505	P125T	10	£ 12.38
1-1/2"	7111060606	P15T	10	£ 18.23
2"	7111080808	P2T	10	£ 28.78
2-1/2"	7111101010	P25T	10	£ 46.86
3"	7111121212	P3T	5	£ 55.20

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

PLASTIC PIPE FITTINGS



Description	Part Number	Short Code	Box Qty	List Price
TEE - REDUCING				
1 x 1 x 3/4"	7115040403	P1175RT	20	£ 7.48
1-1/4 x 1 x 3/4"	7115050403	P125175RT	20	£ 13.80
1-1/4 x 1-1/4 x 3/4"	7115050503	P12512575RT	15	£ 13.80
1-1/4 x 1-1/4 x 1"	7115050504	P1251251RT	15	£ 13.80
1-1/2 x 1-1/4 x 3/4"	7115060503	P1512575RT	10	£ 16.69
1-1/2 x 1-1/4 x 1"	7115060504	P151251RT	10	£ 16.69
1-1/2 x 1-1/2 x 3/4"	7115060603	P151575RT	15	£ 16.69
1-1/2 x 1-1/2 x 1"	7115060604	P15151RT	10	£ 16.69
1-1/2 x 1-1/2 x 1-1/4"	7115060605	P1515125RT	10	£ 16.69
2 x 2 x 3/4"	7115080803	P2275RT	10	£ 26.48
2 x 2 x 1"	7115080804	P221RT	10	£ 26.48
2 x 2 x 1-1/4"	7115080805	P22125RT	10	£ 26.48
2 x 2 x 1-1/2"	7115080806	P2215RT	10	£ 26.48
2-1/2 x 2-1/2 x 1"	7115101004	P25251RT	10	£ 36.40
2-1/2 x 2-1/2 x 1-1/4"	7115101005	P2525125RT	10	£ 36.40
2-1/2 x 2-1/2 x 1-1/2"	7115101006	P252515RT	10	£ 36.40
3 x 3 x 2"	7115121208	P332RT	5	£ 42.02
3 x 3 x 2-1/2"	7115121210	P3325RT	5	£ 42.02
TEE - RUN REDUCER				
3/4 x 3/4 x 1"	7117030304	P75751RT	15	£ 7.48
1 x 3/4 x 3/4"	7117040303	P17575RT	15	£ 7.48
1 x 3/4 x 1"	7117040304	P1751RT	15	£ 7.48
1-1/4 x 1 x 1"	7117050404	P12511RT	15	£ 13.80
1-1/4 x 1 x 1-1/4"	7117060405	P1251125RT	15	£ 13.80
1-1/4 x 1-1/4 x 1-1/2"	7117050506	P12512515RT	10	£ 16.69
1-1/2 x 1-1/2 x 2"	7117060608	P15152RT	10	£ 26.48
TEE - SPRINKLER HEAD ADAPTER (BRASS THREADED)				
3/4 x 3/4 x 1/2"T	7119030302	P75755SHAT	50	£ 10.95
1 x 1/2 x 1" Sha Tee	7119040204	P151SHAT	50	£ 21.70
1 x 1 x 1/2"T	7119040402	P115SHAT	50	£ 12.28
1 x 1 x 1"T	7119040404	P1SHAT	10	£ 28.76
1-1/4 x 1-1/4 x 1/2"T	7119050502	P1251255SHAT	15	£ 19.53
1-1/2 x 1-1/2 x 1/2"T	7119060602	P15155SHAT	10	£ 26.31
2 x 2 x 1/2"T	7119080802	P225SHAT	10	£ 35.54

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

PLASTIC PIPE FITTINGS



Description	Part Number	Short Code	Box Qty	List Price
TEE - SPRINKLER HEAD ADAPTER (STAINLESS STEEL BAND)				
3/4 x 3/4 x 1/2"T	7118030302	P75755SHATS	50	£ 10.74
1 x 1 x 1/2"T	7118040402	P115SHATS	50	£ 9.33
1 x 1 x 1"T	7118040404	P1SHATS	15	£ 23.93
1-1/4 x 1-1/4 x 1 T	7118050504	P1251251SHATS	15	£ 34.09
1-1/2 x 1-1/4 x 1/2"T			10	£ Call
1-1/2 x 1-1/2 x 1/2"T	7118060602	P15155SHATS	25	£ 20.47
2 x 1-1/2 x 1/2"T	7118080602	P2155SHATS	10	£ 28.88
2 x 2 x 1/2"T	7118080802	P225SHATS	10	£ 28.88
TEE - RUN REDUCER ADAPTER				
1 x 3/4 x 1/2"T	7121040302	P1755SHAT	50	£ 15.13
1-1/4 x 1 x 1/2"T	7121050402	P12515SHAT	15	£ 20.56
1-1/2 x 1-1/4 x 1/2"T	7121060502	P151255SHAT	10	£ 26.41
2 x 1-1/2 x 1/2"T	7121080602	P2155SHAT	10	£ 35.54
BUSHING - REDUCER				
1 x 3/4"	7125040300	P175HB	50	£ 2.45
1-1/4 x 3/4"	7125050300	P12575HB	25	£ 3.84
1-1/4 x 1"	7125050400	P1251HB	25	£ 3.84
1-1/2 x 3/4"	7125060300	P1575HB	25	£ 4.02
1-1/2 x 1"	7125060400	P151HB	25	£ 4.02
1-1/2 x 1-1/4"	7125060500	P15125HB	25	£ 4.02
2 x 3/4"	7125080300	P275HB	10	£ 6.33
2 x 1"	7125080400	P21HB	10	£ 6.33
2 x 1-1/4"	7125080500	P2125HB	10	£ 6.33
2 x 1-1/2"	7125080600	P215HB	10	£ 6.33
2-1/2 x 1-1/4"	7125100500	P25125HB	10	£ 10.95
2-1/2 x 1-1/2"	7125100600	P2515HB	10	£ 10.95
2-1/2 x 2"	7125100800	P252HB	15	£ 10.95
3 x 2"	7125120800	P32HB	10	£ 16.39
3 x 2-1/2"	7125121000	P325HB	10	£ 16.39
ADAPTER - SPRINKLER HEAD, BUSHING STYLE (4238-130BR)				
1" S x 1/2" T	6990003821	P15SHABUSH		£ 10.27
ADAPTER - SPRINKLER HEAD, SOCKET (BRASS THREADED)				
3/4" S x 1/2"T	7135030201	P755SHA	50	£ 7.70
1" S x 1/2"T	7135040201	P15SHA	50	£ 8.18
1" S x 3/4"T	7135040301	P175SHA	50	£ 12.30
ADAPTER - SPRINKLER HEAD, SOCKET (STAINLESS STEEL BAND)				
3/4" S x 1/2"T	7135030200	P755SHAS	50	£ 6.21
1" S x 1/2"T	7135040200	P15SHAS	50	£ 6.64
1" S x 3/4"T	7135040300	P175SHAS	25	£ 10.48
ADAPTER - SPRK HEAD w/METAL START + PLASTIC THREAD				
3/4" S x 1/2"T	7135030202	P755SHAZSR	50	£ 6.21
1" S x 1/2"T			50	£ Call
ADAPTER - SPRK. HEAD, SOCKET, 401 (STAINLESS STEEL BAND)				
3/4" S x 1/2"T	7135030203	P755SHAS401	50	£ 7.63
1" S x 1/2"T			50	£ Call

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

PLASTIC PIPE FITTINGS



Description	Part Number	Short Code	Box Qty	List Price
ADAPTER - SPRINKLER HEAD, SPIGOT (BRASS THREADED)				
3/4" SPG x 1/2"T	7139030201	P755SHASP	50	£ 7.70
1" SPG x 1/2"T	7139040201	P15SHASP	50	£ 8.18
ADAPTER - SPRINKLER HEAD, SPIGOT (STAINLESS STEEL BAND)				
3/4" SPG x 1/2"T	7139030200	P755SHASPS	50	£ 6.21
1" SPG x 1/2"T	7139040200	P15SHASPS	50	£ 6.70
ADAPTER - SPRINKLER HEAD, ADJUSTABLE, SOCKET				
3/4" S x 1/2"T	7145030200	P755SADJ	10	£ 29.85
1" S x 1/2"T	7145040200	P15SADJ	10	£ 34.36
ADAPTER - SPRINKLER HEAD, ADJUSTABLE, SPIGOT				
1" SOC x 1/2"T	7145040201	P15SOCADJ	10	£ 26.86
1" SPG x 1/2"T			10	£ Call
ADAPTER - FEMALE (BRASS THREADED)				
3/4"	7158030000	P75FMA	15	£ 13.36
1"	7158040000	P1FMA	15	£ 23.42
1-1/4"	7158050000	P125FMA	15	£ 42.26
1-1/2"	7158060000	P15FMA	10	£ 58.98
2"	7158080000	P2FMA	5	£ 75.89
ADAPTER - FEMALE (STAINLESS STEEL BAND)				
3/4"	7158030001	P75FMAS	25	£ 10.15
1"	7158040001	P1FMAS	25	£ 17.83
1-1/4"	7158050001	P125FMAS	10	£ 29.05
ADAPTER - FEMALE SPIGOT (BRASS THREADED)				
3/4"	7139030300	P75SPA	15	£ 13.14
1"	7139040400	P1SPA	15	£ 22.25
ADAPTER - FEMALE SPIGOT (STAINLESS STEEL BAND)				
3/4"	7139030301	P75SPAS	15	£ 10.66
1"	7139040401	1SPAS	15	£ 18.98
COUPLING				
3/4"	7153030300	P75C	25	£ 2.78
1"	7153040400	P1C	25	£ 3.08
1-1/4"	7153050500	P125C	10	£ 6.05
1-1/2"	7153060600	P15C	10	£ 8.61
2"	7153080800	P2C	20	£ 11.64
2-1/2"	7153101000	P25C	5	£ 17.71
3"	7153121200	P3C	5	£ 23.03
COUPLING - REDUCER				
1 x 3/4"	7155040300	P175RC	15	£ 4.03
1-1/4 x 1"	7155050400	P1251RC	25	£ 6.05
1-1/2 x 1"	7155060400	P151RC	10	£ 9.08
1-1/2 x 1-1/4"	7155060500	P15125RC	10	£ 8.61
2 x 1"	7155080400	P21RC	10	£ 12.13
2 x 1-1/4"	7155080500	P2125RC	10	£ 11.85
2 x 1-1/2"	7155080600	P215RC	10	£ 11.64
MISC.				
1 x 1/2 FM head adpt., long	6999991743	P15SHAL		£ 11.49
3/4 x 1/2 head adpt.	7137030201	P755SHAR		£ 10.08

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

PLASTIC PIPE FITTINGS



Description	Part Number	Short Code	Box Qty	List Price
GROOVED COUPLING ADAPTER (CPVC)				
1-1/4"	7149050501	P125GCAB	10	£ 55.89
1-1/2"	7149060601	P15GCAB	10	£ 59.14
2"	7149080801	P2GCAB	10	£ 68.51
2-1/2"	7149101001	P25GCAB	5	£ 80.64
3"	7149121201	P3GCAB	1	£ 94.20
CAPS				
3/4"	7167030000	P75CAP	25	£ 1.79
1"	7167040000	P1CAP	25	£ 2.45
1-1/4"	7167050000	P125CAP	10	£ 4.33
1-1/2"	7167060000	P15CAP	10	£ 5.99
2"	7167080000	P2CAP	10	£ 9.12
2-1/2"	7167100000	P25CAP	5	£ 12.95
3"	7167120000	P3CAP	5	£ 21.19
TEST PLUG (FTP-005)				
1/2"	7139020000	TESTPLUG		£ 3.66
CROSS				
3/4"	7171030000	P75CRS	20	£ 6.91
1"	7171040000	P1CRS	15	£ 8.61
1-1/4"	7171050000	P125CRS	10	£ 12.03
1-1/2"	7171060000	P15CRS	10	£ 16.39
2"	7171080000	P2CRS	8	£ 26.70
2-1/2"	7171100000	P25CRS	5	£ 58.71
3"	7171120000	P3CRS	5	£ 86.10
MALE THREADED ADAPTER				
3/4"	7157030000	P75MA	40	£ 17.14
1"	7157040000	P1MA	10	£ 25.10
1-1/4"	7157050000	P125MA	10	£ 38.46
1-1/2"	7157060000	P15MA	10	£ 101.10
2"	7157080000	P2MA	5	£ 134.61
CROSS REDUCING				
1" x 1" x 3/4" x 3/4"	7173040403	P117575CRS	20	£ 9.30
SEE PAGE SC-55				
SEE PAGE SC-55				
CEMENT				
Dauber - Pint	7175200000	DOBPT	100	£ 6.46
Dauber - Quart	7175100000	DOBQT	100	£ 6.46
One-Step Cement - Pint	7175000001	1STEPPT	12	£ 52.05
One-Step Cement - Qrt	7175050001	1STEPQT	12	£ 96.75
BLUE 75 THREAD SEALANT				
Pint	7175000002	BLUE75P	12	£ 107.36
Quart	7175050002	BLUE75Q	12	£ 193.25

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

PLASTIC PIPE FITTINGS



Description	Part Number	Short Code	Box Qty	List Price
TORQUE SAFE FITTINGS				
3/4" x 3/4" x 1/2" TEE	7120030302	P75755TGS	50	£ 10.95
1" x 3/4" x 1/2" TEE	7122040302	P1755TGS	50	£ 15.13
1" x 1" x 1/2" TEE	7120040402	P115TGS	50	£ 15.43
1-1/4" x 1-1/4" x 1/2" TEE	7120050502	P1251255TGS	15	£ 19.53
1-1/2" x 1-1/2" x 1/2" TEE	7120060602	P15155TGS	10	£ 26.31
2" x 2" x 1/2" TEE	7120080802	P225TGS	10	£ 35.54
1" x 1/2" T x 1" TEE	7120040204	P151TGS	50	£ 22.04
3/4" x 1/2" T 90 deg. Elbow	7109030205	P755R90GS	20	£ 8.55
1" x 1/2" T 90 deg. Elbow	7109040205	P15SHA90GS	15	£ 11.30
1-1/4" x 1/2" T 90 deg. Elbow	7109050205	P1255R90GS	10	£ 14.11
3/4" x 1/2" T head adpt.	7135030205	P755SHAGS	50	£ 7.70
1" x 1/2" T head adpt.	7135040205	P15SHAGS	50	£ 8.18
1" x 3/4" T head adpt.	7135040305	P175SHAGS	50	£ 12.30
3/4" SPG x 1/2" T head adpt.	7139030205	P755SPGHAGS	50	£ 7.70
1" SPG x 1/2" T head adpt.	7139040205	P15SPGHAGS	50	£ 8.18
1" x 1/2" T Bushing adpt.	7135040208	P15SHABUSHGS	50	£ 10.27
1" x 1/2" T Soft Torque Adptr.	7139040209	P15SHAGSR	50	£ 6.34
Test Plug	7139020005	TESTPLUGGS	50	£ 4.29
GRIPLOC FITTINGS				
Push on Coupling - 3/4"	6990017186	GL4229007		£ 43.14
Push on Coupling - 1"	6990017187	GL4229010		£ 45.58
SPEARS, #GL4235-130G, 1X1/2, GRIPLOC HD ADT	6990023462	GL4235130G	12	£ 35.20
Repair Coupling - 1"	6990017228	P1GRC		£ 101.56

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.