

# Reliable®

## RASCOFLEX FLEXIBLE SPRINKLER HOSE

RELIABLE FIRE  
SPRINKLER (UK)  
LIMITED

[www.reliablesprinkler.com](http://www.reliablesprinkler.com)



Produced in the United Kingdom.  
Design and materials subject to change without notice.  
Second Edition. 2017.

# RASCOFLEX Accessories

RASCOFLEX Flexible Kits include:

- 1 x Hose,
- 1 x Inlet Nipple (25/32mm)
- 1 x 135mm Straight reducer (15/20mm)
- 1 x Bar (700mm)
- 2 x 105mm T-Bar Grid Brackets
- 1 x Centre Bracket

The kits are boxed and supplied in units of 10 only.

## Straight Reducer

Size (mm)	Part No.
15 x 300	RF15300MRD
15 x 155	RF15155MRD
15 x 135	RF15135MRD
15 x 110	RF15110MRD
20 x 300	RF20300MRD
20 x 155	RF20155MRD
20 x 135	RF20135MRD
20 x 110	RF20110MRD



## 90° Elbow Reducer

Size (mm)	Part No.
15 x 110	RF15110MER
15 x 155	RF15155MER
20 x 110	RF20110MER
20 x 155	RF20155MER



## Inlet Nipple

Size (mm)	Part No.
25	RF25MINLET
32	RF32MINLET



## Metal Stud End Bracket

Size (mm)	Part No.
38 (Short)	RF38MPLASB
53 (Long)	RF53MPLASB



## Long Radius Reducer

Size (mm)	Part No.
15 x 150	RF15150MRE
20 X 150	RF20150MRE



## Open Hat Channel Bracket

Size (mm)	Part No.
96	RFOPHATCHB



## Stock Bar

Size (mm)	Part No.
700	RF0700MBAR
1270	RF15155MRD
1600	7U99001366



## Centre Bracket

Size (mm)	Part No.
One Size	RFCENTR01B



## Wood Beam Bracket

Size (mm)	Part No.
One Size	RFWOOD01BC




## Radius Bend Indicator

Size (mm)	Part No.
One Size	7U99001692



## T-Bar Grid Bracket

Size (mm)	Part No.
60	RF068MTBRC
78	RF078MTBRC
105	RF105MTBRC



# RASCOFLEX Sprinkler Hose



**Unbraided.** LPCB Approved & UL Listed



Flexible Kit, Unbraided. LPCB & UL

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	25	700	RF070U2164
15	25	1000	RF100U2164
15	25	1200	RF120U2164
15	25	1500	RF150U2164
15	25	1800	RF180U2164
20	25	700	RF070U2264
20	25	1000	RF100U2264
20	25	1200	RF120U2264
20	25	1500	RF150U2264
20	25	1800	RF180U2264

Flexible Kit, Unbraided. LPCB

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	32	700	RF070U3164
15	32	1000	RF100U3164
15	32	1200	RF120U3164
15	32	1500	RF150U3164
15	32	1800	RF180U3164
20	32	700	RF070U3264
20	32	1000	RF100U3264
20	32	1200	RF120U3264
20	32	1500	RF150U3264
20	32	1800	RF180U3264



**Braided.** FM, VdS & LPCB Approved & UL Listed



Flexible Kit, Braided. FM, VdS, LPCB & UL

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	25	700	RF070B2164
15	25	1000	RF100B2164
15	25	1200	RF120B2164
15	25	1500	RF150B2164
15	25	1800	RF180B2164
20	25	700	RF070B2264
20	25	1000	RF100B2264
20	25	1200	RF120B2264
20	25	1500	RF150B2264
20	25	1800	RF180B2264

Flexible Kit, Braided. LPCB

Outlet (mm)	Inlet (mm)	Length (mm)	Part No.
15	32	700	RF070B3164
15	32	1000	RF100B3164
15	32	1200	RF120B3164
15	32	1500	RF150B3164
15	32	1800	RF180B3164
20	32	700	RF070B3264
20	32	1000	RF100B3264
20	32	1200	RF120B3264
20	32	1500	RF150B3264
20	32	1800	RF180B3264





# WORLDWIDE DISTRIBUTION CENTRES, FABRICATION FACILITIES & SALES OFFICES.

## HEADQUARTERS

---

Corporate  
Elmsford, New York  
800.432.1588  
info@reliablesprinkler.com

International  
Crawley, United Kingdom  
+44 (0) 1342 316 800  
rfsl@reliablesprinkler.com

Manufacturing  
Liberty, South Carolina  
864.843.1700  
info@reliablesprinkler.com

## SALES OFFICES

---

### America & Canada

info@reliablesprinkler.com

Seattle, Washington  
877.327.2563

Atlanta, Georgia  
800.652.1819

Orlando, Florida  
800.801.3097

Chicago, Illinois  
800.228.6274

Minneapolis, Minnesota  
877.827.2816

Dallas, Texas  
800.426.742

Houston, Texas  
866.978.9965

Denver, Colorado  
877.440.2598

Los Angeles, California  
800.352.43.65

San Francisco, California  
800.352.4365

Toronto, East Canada  
800.790.6443

Vancouver, West Canada  
604.542.1864

### International

Singapore  
+65 9859 0690  
asiasales@reliablesprinkler.com

Australia  
+61 8 816 29555  
ausales@reliablesprinkler.com

Europe  
+49.405589818-71  
europe@reliablesprinkler.com

Dubai  
+971 4 880 8830  
csme@reliablesprinkler.com

Shanghai  
+86 21 54037021  
asiasales@reliablesprinkler.com

## FABRICATION FACILITIES

---

Grand Prairie, Texas  
972.352.6400  
info@reliablesprinkler.com

Portland, Oregon  
503.282.5506  
info@reliablesprinkler.com

Denver, Colorado  
877.440.2598  
info@reliablesprinkler.com