



FOR PROTECTION OF YOUR PROPERTY AND FOR PROTECTION OF YOUR SPRINKLER SYSTEM, RELIABLE HAS YOU COVERED!

Contact us today
1.800.431.1588

We'll help you pick the right fire protection products for your property.

If your property has been previously protected by "non-protected" sprinklers, it may not be too late to make the change to concealed protection. One of our Technical Service Managers can help you in making that decision.

Please see our complete line of fire sprinkler products at:
www.reliablesprinkler.com

WHETHER A RETROFIT OR NEW CONSTRUCTION, **RELIABLE** HAS THE RIGHT QUICK RESPONSE CONCEALED SPRINKLER FOR YOUR PROPERTY'S PROTECTION!



Reliable's complete line of concealed sprinklers will help to eliminate "accidental" operation of fire sprinklers and resulting damage which can be caused by:

- Hanging clothes and suitcases
- Identified "flying objects" - footballs and golf balls

REGIONAL DISTRIBUTION CENTERS & SALES OFFICES

NORTHEAST REGION:
Corporate Distribution Center & Sales Office:
New York, NY
Tel.: 800.431.1588
Fax: 800.848.6051

Corporate Headquarters
Tel.: 914.668.3470
Fax: 914.668.2936

SOUTHEAST REGION:
Distribution Center & Sales Office:
Atlanta, GA
Tel.: 800.652.1819
Fax: 800.848.6052

Distribution Center & Sales Office:
Orlando, FL
Tel.: 800.801.3097
Fax: 800.862.0934

MIDWEST REGION:
Distribution Center & Sales Office:
Chicago, IL
Tel.: 800.228.6274
Fax: 800.848.6053

Distribution Center & Sales Office:
Minneapolis, MN
Tel.: 877.827.2816
Fax: 877.827.3043

SOUTHWEST REGION:
Distribution Center & Sales Office:
Dallas, TX
Tel.: 800.442.6742
Fax: 800.848.6054

Distribution Center & Sales Office:
Denver, CO
Tel.: 877.440.2598
Fax: 877.205.7230

WEST COAST REGION:
Distribution Center & Sales Office:
Los Angeles, CA
Tel.: 800.352.4365
Fax: 800.848.6055

Distribution Center & Sales Office:
Seattle, WA
Tel.: 877.327.2563
Fax: 877.327.2574

INTERNATIONAL:
Distribution Center & Sales Office:
Eastern Canada
Tel.: 800.431.1588
Fax: 800.848.6051

Distribution Center & Sales Office:
Western Canada
Tel.: 877.327.2563
Fax: 877.327.2574

Sales Office:
Mexico & Latin America
Tel.: 214.259.5023
Fax: 972.620.0158

Distribution Center & Sales Office:
London, United Kingdom
RELIABLE FIRE SPRINKLER LTD.
Tel.: 011.441.372.728899
Fax: 011.441.372.724461

Sales Office:
Beijing PR China
Tel.: 011.86.10.84983998
Fax: 011.86.10.84983997

Sales Office:
Shanghai PR China
Tel.: 011.86.21.62193885
Fax: 011.86.21.62192885




1.800.431.1588
www.reliablesprinkler.com
The Reliable Automatic Sprinkler Co., Inc.
Manufacturer & Distributor of Fire Protection Equipment

Other Concealed Sidewall Sprinklers Are Not Equal!

For rooms larger than 14 feet x 14 feet, **Reliable's SWC is the concealed sidewall sprinkler that can provide protection with one sprinkler.** One SWC can protect a room up to 16 feet wide and 22 feet deep.

The SWC

Maximum Coverage: **16' x 22'**
 Response: **Quick**
 Finish: **White, custom colors available**
 Approvals: **cULus for Light Hazard**
 Distance from ceiling: **4" to 12"**
 K Factor: **8.0**
 PSI required for 16' x 22': **37 gpm @ 21.4 psi**
 Temperature rating: **135°F**
 Pressure rating: **300 psi**
 Technical Bulletin: **163**



We also have Smaller Rooms and Larger Hazards Covered




For smaller areas and other portions of the property, Reliable's SWC56 provides concealed coverage for light hazard (14 feet x 14 feet coverage) and ordinary hazard applications (10 feet x 10 feet coverage).

It provides concealed protection for: alcoves, foyers, rest rooms, corridors, storage rooms, meeting rooms, dining areas and kitchens.

The SWC56

Maximum Coverage: **Per NFPA**
 Response: **Quick**
 Finish: **White, custom colors available**
 Approvals: **cULus for Ordinary and Light Hazard**
 Distance from ceiling: **4" to 12"**
 K Factor: **5.6**
 Temperature rating: **135°F**
 Pressure rating: **300 psi**
 Technical Bulletin: **168**



There are other brands and styles of sidewall, concealed sprinklers being offered for sale. Ask them if they compare:

1. Is your sprinkler approved for extended coverage?
2. Can your sprinkler be installed in a 4" stud wall without an extension piece?
3. Is your sprinkler approved for ordinary hazard applications?
4. What is the pressure rating of your sprinkler?



If your rooms are larger than 14 feet in any dimension, you may find out they are just "bed wetters".

Install 1 Sprinkler Instead of 2!

For long and narrow applications such as: hallways, corridors, and rooms up to 28' long, Reliable's DH80 sprinkler is the right choice. One DH80 provides coverage up to 28 feet in width and a length of 14 feet.


The DH80

Maximum Coverage: **28' x 14'**
 Response: **Quick**
 Finish: **White, custom colors available**
 Approvals: **cULus for Light Hazard**
 Distance From Ceiling: **4" to 12"**
 K Factor: **8.0**
 PSI Required For 28' x 14': **40 gpm @ 25 psi**
 Temperature Rating: **155°F**
 Pressure Rating: **300 psi**
 Technical Bulletin: **003**



Reliable also Offers a Complete Line of Pendent Concealed Sprinklers for In-Ceiling Installation.


From the cost effective Conical Concealed (CCP) Models to the Low Pressure, Extended Coverage ConcealerPlus



The ConcealerPlus
 Low Pressure and Quick Response,
 Extended Coverage up to 18' x 18'



F1FREC - CCP
The industry's only Quick Response,
Extended Coverage up to 20' x 20'



DH80
 Light Hazard/EC Quick Response
 Coverage up to 28ft. in width and a length of 14ft.

And for those areas where dry sprinklers may be required, Reliable has the F3QR Concealed Dry Pendent Sprinkler. A Quick Response, Standard Coverage Concealed Sprinkler using a Belleville spring washer closure.