

Reliable®

K-22 Magnum Early Suppression Fast Response Sprinkler

K-22, Model H22 ESFR (SIN R6611)

Performance Characteristics: Single Sprinkler Minimum Pressure and Flow

Features

1. Eliminates in-rack sprinklers for 45' high buildings.
2. Lower flows offer opportunities to reduce:
 - Interior Piping
 - Fire Pump Sizes
 - Underground Pipe
 - Tank Sizes
3. Maximum deflector distance from ceiling (roof) is 18" (457mm).
4. Available in 155°F and 200°F.



K-22 Magnum Sprinkler

Bldg. Height	UL		FM & VdS	
	Pressure	Flow	Pressure	Flow
* 45 ft. (13.7m)	40 psi (2,8 bar)	142 gpm (537L/min)	50 psi (3,4 bar)	158 gpm (597 L/min)
40 ft. (12.2 m)	40 psi (2,8 bar)	142 gpm (537L/min)	45 psi (3,1 bar)	150 gpm (567 L/min)
35 ft. (10.7m)	35 psi (2,4 bar)	133 gpm (503 L/min)	35 psi (2,4 bar)	133 gpm (503 L/min)
30 ft. (9.1 m)	25 psi (1,7 bar)	112 gpm (423 L/min)	25 psi (1,7 bar)	112 gpm (423 L/min)

* with up to 40 ft. (12.2 m) storage (In-rack sprinklers are not required)

Requirements

Product Description

The K-22 Early Suppression Fast Response (ESFR) Sprinkler is intended for use against severe fire challenges. This sprinkler is designed to respond quickly to growing fires with a high volume of water discharge to "suppress" rather than "control" fires at lower pressures and without in-rack sprinklers for 35' (10.7m) to 40' (12.2m) storage as is required with a K14 or K17 ESFR.

The K-22 Sprinkler utilizes a 2.5mm glass bulb in either 155°F or 200°F temperature ratings. The sprinkler has a Nominal K Factor of 22.4 (320 metric) and will deliver approximately 112 gpm (424 L/min) of water at 25 psi (1,7 bar).

The deflector and frame provide a broad, very symmetrical, hemispherical pattern capable of suppressing fires between sprinklers in high storage height areas and at the same time maintaining good central core distribution to penetrate and suppress fires occurring directly beneath the sprinkler.

Application and Installation

The K-22 ESFR sprinkler is intended for installation in accordance with NFPA 13 and Factory Mutual (FM) Loss Prevention Data Sheet 2-2, as well as the Authority Having Jurisdiction.

This sprinkler is intended for protection of Class I to IV Commodities and Group A or B plastics, which includes cartoned unexpanded plastics. The storage can be palletized and solid piled, open frame single row or multiple row and portable rack storage.

Approval Organizations

1. Listed by Underwriters Laboratories Inc. and UL certified for Canada (cULus). Listed for installation in accordance with NFPA standards for storage heights to 40ft. (12.2m) in buildings to 45ft. (13.7m) high.
2. Factory Mutual Research Corp. (FM)
The K-22 Sprinkler is for use in buildings with ceilings up to 45ft. (13.7m) high with storage heights to 40 ft. (12.2m) when installed in accordance with FM Loss Prevention Data Sheet 2-2 or other FM Installation Standards.
3. NYC MEA 258-93-E
4. Verband der Schadenversicherer E.V. (VdS)

K-22, Model H22 Temperature Ratings and Approvals

Classification	Sprinkler Temperature Rating		Bulb Color	Frame Color	Maximum Ambient Temperature		Approvals	Sprinkler Identification No. (SIN)
	°F	°C			°F	°C		
Ordinary	155	68	Red	Uncolored	100	38	cULus, FM, NYC VdS	R6611
Intermediate	200	93	Green	White	150	66		R6611

Installation Data

Sprinkler Type	Nominal Orifice	Thread Size	Nominal K Factor		Maximum Working Pressure	Finish
			US	Metric		
Pendent Only	0.87" (22.1mm)	1" NPT R1	22.4	320	175 psi (12,1 bar)	Bronze



Use only the Model H1 sprinkler wrench for removal and installation. Any other type of wrench may damage the sprinkler.

Maintenance


The K-22 Sprinkler should be inspected quarterly and the sprinkler system maintained in accordance with NFPA 25. Do not clean sprinklers with soap and water, ammonia or any other cleaning fluids. Remove dust by using a soft brush or gentle vacuuming. Remove any sprinkler that has been painted (other than factory applied) or damaged in any way. A stock of spare sprinklers should be maintained to allow quick replacement of damaged or operated sprinklers. Prior to installation, sprinklers should be maintained in the original cartons and packaging until used. This will minimize the potential for damage to sprinklers that would cause improper operation or non-operation.

Ordering Information

Specify:

1. Temperature Rating
2. Thread type 1" NPT or ISO 7-R1

Patents: U.S. Patent No. 6,450,265



The equipment presented in this bulletin is to be installed in accordance with the latest pertinent Standards of the National Fire Protection Association, Factory Mutual Research Corporation, or other similar organizations and also with the provisions of governmental codes or ordinances whenever applicable.

Products manufactured and distributed by Reliable have been protecting life and property for over 80 years, and are installed and serviced by the most highly qualified and reputable sprinkler contractors located throughout the United States, Canada and foreign countries.

Manufactured by

Reliable®

The Reliable Automatic Sprinkler Co., Inc.

(800) 431-1588
(800) 848-6051
(914) 668-3470
www.reliablesprinkler.com

Sales Offices
Sales Fax
Corporate Offices
Internet Address



Revision lines indicate updated or new data.

EG Printed in USA 6/04 P/N 999970170