

FOREIGN DUCTILE IRON FITTINGS



Part Name	Part Number	Box Qty	List Price
90° ELBOWS			
1"	DI190	70	\$ 6.40
1-1/4"	DI12590	42	\$ 10.15
1-1/2"	DI1590	32	\$ 14.65
2"	DI290	17	\$ 22.20
REDUCING 90° ELBOWS			
1 x 1/2"	DI15R90	110	\$ 7.95
1 x 3/4"	DI175R90	90	\$ 8.55
1-1/4 x 1/2"	DI1255R90	70	\$ 14.20
1-1/4 x 3/4"	DI12575R90	65	\$ 15.00
1-1/4 x 1"	DI1251R90	50	\$ 12.65
1-1/2" x 1"	DI151R90	40	\$ 17.50
1-1/2 x 1-1/4"	DI15125R90	38	\$ 17.50
2 x 1/2"	DI25R90	45	\$ 41.00
2 x 3/4"	DI275R90	40	\$ 29.50
2 x 1"	DI21R90	32	\$ 28.55
2 x 1-1/4"	DI2125R90	25	\$ 38.55
2 x 1-1/2"	DI215R90	20	\$ 28.80
45° ELBOWS			
1"	DI145	85	\$ 10.00
1-1/4"	DI12545	50	\$ 13.30
1-1/2"	DI1545	35	\$ 22.25
2"	DI245	EA	\$ 25.55
REDUCING COUPLINGS			
1 x 1/2"	DI15RC	130	\$ 5.75
1 x 3/4"	DI175RC	120	\$ 7.65
TEES STANDARD			
1"	DI1T	56	\$ 9.20
1-1/4"	DI125T	32	\$ 16.95
1-1/2"	DI15T	25	\$ 21.60
2"	DI2T	15	\$ 30.35
HEX BUSHINGS			
1 x 1/2"	DI15HB	250	\$ 6.20
1 x 3/4"	DI175HB	250	\$ 6.20
1-1/4 X 1	DI1251HB	130	\$ 7.00
1-1/2 X 1	DI151HB	100	\$ 8.00
1-1/2 x 1-1/4"	DI15125HB	100	\$ 8.00
2 X 1	DI21HB	70	\$ 11.15
2 x 1-1/4"	DI2125HB	70	\$ 11.15
2 x 1-1/2"	DI215HB	70	\$ 11.55

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

FOREIGN DUCTILE IRON FITTINGS



Part Name	Part Number	Box Qty	List Price
REDUCING TEES			
1 x .5 x 1"	DI151RT	64	\$ 11.10
1 x .75 x 1"	DI1751RT	64	\$ 13.10
1 x 1 x .5"	DI115RT	74	\$ 10.35
1 x 1 x .75"	DI1175RT	66	\$ 12.50
1.25 x 1 x .5"	DI12515RT	55	\$ 16.85
1.25 x 1 x .75"	DI125175RT	48	\$ 19.00
1.25 x 1 x 1"	DI12511RT	45	\$ 16.95
1.25 x 1 x 1.25"	DI1251125RT	40	\$ 16.95
1.25 x 1.25 x .5"	DI1251255RT	48	\$ 16.10
1.25 x 1.25 x .75"	DI12512575RT	44	\$ 18.00
1.25 x 1.25 x 1"	DI1251251RT	40	\$ 16.55
1.5 x 1 x .5"	DI1515RT	45	\$ 34.00
1.5 x 1 x .75"	DI15175RT	42	\$ 31.55
1.5 x 1 x 1"	DI1511RT	38	\$ 30.00
1.5 x 1 x 1.25"	DI151125RT	33	\$ 37.55
1.5 x 1 x 1.5"	DI15115RT	30	\$ 21.55
1.5 x 1.25 x .5"	DI151255RT	40	\$ 23.45
1.5 x 1.25 x .75"	DI1512575RT	40	\$ 23.45
1.5 x 1.25 x 1"	DI151251RT	32	\$ 21.65
1.5 x 1.5 x .5"	DI15155RT	38	\$ 21.00
1.5 x 1.5 x .75"	DI151575RT	36	\$ 23.45
1.5 x 1.5 x 1"	DI15151RT	32	\$ 21.00
1.5 x 1.5 x 1.25"	DI1515125RT	26	\$ 30.00
2 x 1 x 2"	DI212RT	18	\$ 30.50
2 x 1.25 x 2"	DI21252RT	16	\$ 33.00
2 x 1.5 x .5"	DI2155RT	30	\$ 34.85
2 x 1.5 x .75"	DI21575RT	28	\$ 34.50
2 x 1.5 x 1"	DI2151RT	23	\$ 30.85
2 x 1.5 x 1.25"	DI215125RT	20	\$ 46.50
2 x 1.5 x 1.5"	DI21515RT	18	\$ 45.15
2 x 1.5" x 2"	DI2152RT	15	\$ 34.85
2 x 2 x .5"	DI225RT	24	\$ 30.55
2 x 2 x .75"	DI2275RT	EA	\$ 30.55
2 x 2 x 1"	DI221RT	23	\$ 30.55
2 x 2 x 1.25"	DI22125RT	19	\$ 33.00
2 x 2 x 1.5"	DI2215RT	15	\$ 35.20

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

FOREIGN DUCTILE IRON FITTINGS



Part Name	Part Number	Box Qty	List Price
BULLHEAD TEES			
1 x 1 x 1.25"	DI11125BT	46	\$ 16.85
1 x 1 x 1.5"	DI1115BT	34	\$ 30.00
1.25 x 1.25 x 1.5"	DI12512515BT	30	\$ 30.00
1.25 x 1 x 1.5"	DI125115BT	32	\$ 21.75
1.25 x 1.25 x 2"	DI1251252BT	24	\$ 45.00
1.5 x 1.25 x 2"	DI151252BT	22	\$ 45.00
1.5 x 1.5 x 2"	DI15152BT	22	\$ 44.20
CROSSES STANDARD			
1"	DI1CR	42	\$ 27.00
1-1/4"	DI125CR	24	\$ 38.10
1-1/2"	DI15CR	19	\$ 49.50
2"	DI2CR	12	\$ 70.00
REDUCING CROSSES			
1-1/4 x 1"	DI1251RC	32	\$ 34.00
1-1/2 x 1"	DI151RC	28	\$ 49.50
2 x 1"	DI21RC	EA	\$ 71.00
CAPS			
1"	DI1CAP	200	\$ 7.00
1-1/4"	DI125CAP	130	\$ 9.45
1-1/2"	DI15CAP	96	\$ 12.65
2"	DI2CAP	72	\$ 17.00
COUPLINGS			
1"	DI1C	140	\$ 5.60
1-1/4"	DI125C	90	\$ 8.35
1-1/2"	DI15C	56	\$ 11.65
2"	DI2C	36	\$ 17.35
PIPE DOPE			
PIPEDOPE (QUART)		12	\$ 57.00
TEFLON TAPE			
3/4"	6999991902	600	\$ 3.17
1/2"	6999992086	1200	\$ 1.75
CUTTING OIL			
1 Gallon	CUTOIL	6	\$ 111.00

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.