

ATTENTION

all 35' & 30' High Buildings
The Best Sprinkler to Install

THE N252 EC

Extended Coverage with No In-Rack Sprinklers
Huge Savings on Materials & Labor

Covering Solid-Pile, Palletized and Single, Double, Multiple Row Racks for Class I-IV and Cartoned Unexpanded Plastics

**FM
APPROVED**



Building Height: 30' Storage Height: 25' Coverage: up to 196 sq ft (14'x14')

K-14.0 ESFR	K-16.8 ESFR	K-25.2 ESFR	K-16.8 CMDA	Ultra K-17	N252 EC
100 sq. ft.	100 sq. ft.	100 sq. ft.	100 sq. ft.	100 sq. ft.	196 sq. ft.
50 psi	35 psi	15 psi-UL 20 psi-FM	22.7 psi (.80)	22 psi	30 psi
12 sprinklers	12 sprinklers	12 sprinklers	2000 sq. ft.	15 sprinklers (1500 sq. ft)	6 sprinklers (3 sprinklers on 2 lines)
1200+ gpm	1200+ gpm	1200+ gpm-UL 1352+ gpm-FM	1600+ gpm	1200+ gpm	Sys. demand 828+ gpm
250 gpm HS	250 gpm HS	250 gpm HS	500 gpm HS	500 gpm HS	250 gpm HS

Building Height: 35' Storage Height: 30' Coverage: up to 144 sq ft (12'x12')

K-14.0 ESFR	K-16.8 ESFR	K-25.2 ESFR	N252 EC
100 sq. ft.	100 sq. ft.	100 sq. ft.	144 sq. ft.
75 psi	52 psi	20 psi-UL 30 psi-FM	40 psi
12 sprinklers	12 sprinklers	12 sprinklers	8 sprinklers (min. of 1200 sq. ft.)
1455+ gpm	1452+ gpm	1352+ gpm-UL 1656+ gpm-FM	Sys. demand 1275+ gpm
250 gpm HS	250 gpm HS	250 gpm HS	250 gpm HS

- Wet Pipe or Pre-action Systems (when they meet the equivalency of a wet system).
- Approved for Non-combustible Obstructed Construction.
- Refer to Reliable Bulletins 008 & 908 for more information.
- Refer to FM Global's Data Sheets 2-0 & 8-9 for installation and design of CMSA and extended coverage storage sprinklers.

**PATENT
PENDING**

P/N 999970372

Reliable®

TECHNOLOGY • QUALITY • SERVICE

1.800.431.1588
www.reliablesprinkler.com

The Reliable Automatic Sprinkler Co., Inc.
Manufacturer & Distributor of Fire Protection Equipment

12/2010