

DDX VALVE TRIMS PART NUMBER CONFIGURATION

SELECTIONS IN **BOLD** ARE STANDARD OPTIONS

TRIM TYPE & B1 ACCELERATOR OPTION
1 = DOUBLE INTERLOCK, TYPE D, W/O B1 ACCELERATOR⁸
2 = DOUBLE INTERLOCK, TYPE D, WITH B1 ACCELERATOR⁸

ASSEMBLY CONFIGURATION, VALVE COLOR & INSTALLED CONTROL VALVE OPTIONS

TRIM FINISH⁴

- 0 = GALVANIZED
- 1 = BLACK PIPE
- 2 = BRASS
- 3 = STAINLESS STEEL
- 4 = GALV. (U.S. SOURCED)
- 5 = BLACK PIPE (U.S. SOURCED)
- 6 = BRASS (U.S. SOURCED)
- 7 = STAINLESS STEEL (U.S. SOURCED)

- 0 = LOOSE TRIM FOR 2"-3" VALVES^{1,5}
- 2 = SEGMENTALLY ASSEMBLED FOR 2"-3" VALVES^{1,5}
- 4 = FULLY ASSEM. TO BLACK DDX VALVE, W/O CONTROL VALVE
- 5 = FULLY ASSEM. TO RED DDX VALVE, W/O CONTROL VALVE
- 7 = FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, W/O CONTROL VALVE⁶
- 8 = FULLY ASSEM. TO BLACK DDX VALVE, WITH CONTROL VALVE⁷
- 9 = FULLY ASSEM. TO RED DDX VALVE, WITH CONTROL VALVE⁷
- A = FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, WITH CONTROL VALVE^{5,7}

DDX VALVE SIZE AND ENDS CONNECTION TYPE
0 = NONE (NO VALVE, LOOSE AND SEGMENTED TRIM ONLY)¹
1 = 2 1/2" GE X GE
2 = 2" GE X GE
3 = 3" GE X GE
5 = 76 MM GE X GE⁹



- NOTES:**
1. FOR THE 4TH DIGIT, SELECT "0" FOR LOOSE OR SEGMENTED TRIMS. 7TH DIGIT MUST BE "0", OR "2". FOR ANY 4TH DIGIT SELECTION OTHER THAN "0", THE 7TH HAS TO BE A FULLY-ASSEMBLED SELECTION ("4", "5", ...ETC).
 2. STANDARD FLANGE TYPE IS CLASS 150 PER ASME B16.5.
 3. SOLENOID VALVE REQUIRED, THE 8TH DIGIT CAN NOT BE "0".
 4. GALVANIZED PIPE FITTINGS ARE THE DEFAULT OFFERING. ALL OTHERS TRIM FINISHES ARE MAKE TO ORDER (MTO).
 5. FOR LOOSE AND SEGMENTED ASSEMBLED TRIM CONFIGURATIONS, THE DDX VALVE IS SOLD SEPARATELY (SEE BULLETIN 519 FOR DDX VALVE'S PART NUMBER).
 6. CHINA COMPULSORY CERTIFICATE FOR FIRE PRODUCTS.
 7. FLANGED VALVES ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).
 8. A SYSTEM PRESSURE SWITCH IS INCLUDED BY DEFAULT WITH THE FOLLOWING TRIMS: TYPE D DOUBLE INTERLOCK, TYPE F DOUBLE INTERLOCK, DRY PILOT SINGLE INTERLOCK, DOUBLE INTERLOCK TYPE PL SYSTEMS.
 9. 76 MM AND 165 MM ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7).


SOLENOID VALVE³

- 0 = NONE
- 1 = 175 PSI
- 2 = 300 PSI
- 3 = 175 PSI EXPLOSION PROOF
- 4 = 300 PSI EXPLOSION PROOF
- 5 = 232 PSI

SYSTEM PRESSURE SWITCH⁸

- 0 = NONE
- 1 = POTTER FM, cULus APPROVED
- 2 = SYSTEM SENSOR FM/UL APPROVED
- 3 = SYSTEM SENSOR FM/ULC APPROVED
- 4 = POTTER, EXPLOSION PROOF

MODEL DDX 2"-3" DELUGE DOUBLE INTERLOCK TYPE D
ASSEMBLY P/N 6520100110 REV. J



2" VERSION WHEN ALTERNATIVE REL-RVGB IS USED

DDX VALVE PART NUMBER TABLE

DDX. VALVE	VALVE PART NUMBER	DRAWING FILE NUMBER
2" DUCTILE IRON G/G BLACK	6103022000	6103030000
2" DUCTILE IRON G/G RED	6103022001	
2-1/2" DUCTILE IRON G/G BLACK	6103022500	
2-1/2" DUCTILE IRON G/G RED	6103022501	
3" DUCTILE IRON G/G BLACK	6103030000	
3" DUCTILE IRON G/G RED	6103030001	
76MM DUCTILE IRON G/G RED	6103027600	

30	6990012997	SWITCH, PRESSURE (PS10-EX), SYSTEM	(ULC, UL, FM)	I
	6990017031	SWITCH, PRESSURE (PS15-2), SYSTEM	(ULC, UL, FM)	
	6999992360	SWITCH, PRESSURE (EPSA10-2), SYSTEM	(ULC)	
	6999991212	SWITCH, PRESSURE (EPS10-2), SYSTEM	(UL/FM)	
29	89141112	TIE, RETAINING		9
28	96686756	TUBING, PVC, 3/8" I.D. x 6 FT.		I
27	95516915	PERMA-LOK	NOT SHOWN	A/R
26	98174400	ELBOW, STREET, 1/2", GALV.		I
25	98840243	VALVE, SWING CHECK, M-M, 1/2 NPT, TIEMME		I
24	98840237	VALVE, BALL, 1/4" NPT x 1/4" NPTM		I
23	98815204	UNION, ORING SEAL, GALV., 1/2		I
22	98761651	TEE, 1/2X1/2X1/2, GALVANIZED		I
21	77000263	SUB-ASSEMBLY, TRIM, BASE, GALVANIZED PIPE		I
20	99080002	PAD-ADHESIVE, VALVE NAME PLATES		I
19	98543243	NIPPLE, 1/4X4, GALVANIZED STEEL		I
18	98543230	NIPPLE, 1/2X3, GALVANIZED STEEL		I
17	98543210	NIPPLE, 1/2X2-1/2, GALVANIZED STEEL		2
16	98543223	NIPPLE, 1/2X1-1/2, GALVANIZED STEEL		2
15	94616918	NAMEPLATE, DOUBLE INTERLOCK, TYPE D		I
14	6304001110	MODEL A PRESSURE MAINTENANCE DEVICE (PMD)		I
13	91004299	MANIFOLD, DRAIN, BARBED, 6-3/16		I
12	98248000	GAUGE, AIR PRESSURE (0-80 PSI)		2
11	98174408	ELBOW, STREET, 1/4", GALV.		I
10	98174404	ELBOW, 1/4", MALL IRON, GALV.		I
9	98174401	ELBOW, 1/2", MALL IRON, GALV.		2
8	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		I
7	95306255	CLAMP, HOSE, 1/2" CONSTANT TENSION, ZINC		8
6	98048022	BUSHING, REDUCER, 3/4X1/2, GALVANIZED		I
5	98048000	BUSHING, REDUCER, 1/2X1/4, GALVANIZED		I
4	77000303	SUBASSEMBLY, CONTROL VALVE, 3"	FULLY ASSEMBLED WITH CONTROL VALVE ONLY	I
	77000302	SUBASSEMBLY, CONTROL VALVE, 2-1/2"		
	77000301	SUBASSEMBLY, CONTROL VALVE, 2"		
3	6871020033	VALVE, SOLENOID (300 PSI) EXPLOSION PROOF	300 PSI EX. PROOF	I
	6999990322	VALVE, SOLENOID (175 PSI) EXPLOSION PROOF	175 PSI EX. PROOF	
	6871020020	VALVE, SOLENOID (300 PSI)	300 PSI RATED	
	6871020000	VALVE, SOLENOID (175 PSI)	175 PSI RATED	
	6871100000	VALVE, SOLENOID (232 PSI)	232 PSI RATED	
2	6990012997	SWITCH, POTTER PRESSURE (PS10-EX)	(ULC, UL, FM)	I
	6990006382	SWITCH, PRESSURE (PS10-2)	(ULC, UL, FM)	
	6999992360	SWITCH, PRESSURE (EPSA10-2)	(ULC)	
	6999991212	SWITCH, PRESSURE (EPS10-2)	(UL/FM)	
1	SEE DDX VALVE P/N TABLE			I
ITEM NO.	PART NO.	DESCRIPTION		QTY.

BILL OF MATERIALS

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CO. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.		VOLUME CU. IN.	THE RELIABLE AUTOMATIC SPRINKLER CO., INC. LIBERTY, S.C.	
DO NOT SCALE DRAWING. REMOVE BURRS, BREAK SHARP EDGES		0.000	PART NO: VARIOUS	DWG.SIZE: C
TOLERANCE UNLESS OTHERWISE SPECIFIED			PART: ASSEMBLY, TRIM, DOUBLE INTERLOCK, TYPE D	
ANGLE ± 1/2° MACH. FINISH 63/		FRACT. ± 1/32 [0.79] DEC. XX ± .010 [0.25] DEC. XXX ± .005 [0.13]	PRODUCT: DDX, 2", 2 1/2", 3"	
		8540-2	FILE NO: 6520100110 ENG: JJ SCALE: 1:8	DRW BY: PH DATE: 12/08/17 SHEET 2 of 3

DDX VALVE TRIMS PART NUMBER CONFIGURATION

SELECTIONS IN **BOLD** ARE STANDARD OPTIONS

DDX VALVE SIZE AND ENDS CONNECTION TYPE

0 = NONE (NO VALVE, LOOSE AND SEGMENTED TRIM ONLY)
4 = 4" GEX GE
6 = 6" GEX GE
7 = 165 MM GE X GE*
8 = 8" GEX GE
A = 4" FLANGE¹⁷ INLET X GE OUTLET
B = 4" FLANGE¹⁷ INLET X FLANGE¹⁷ OUTLET
C = 4" PN16 FLANGE¹⁷ INLET X GE OUTLET
D = 4" PN16 FLANGE¹⁷ INLET X PN16 FLANGE¹⁷ OUTLET
E = 6" FLANGE¹⁷ INLET X GE OUTLET
F = 6" FLANGE¹⁷ INLET X FLANGE¹⁷ OUTLET
G = 6" PN16 FLANGE¹⁷ INLET X GE OUTLET
H = 6" PN16 FLANGE¹⁷ INLET X PN16 FLANGE¹⁷ OUTLET
I = 165 MM FLANGE¹⁷ INLET X GE OUTLET
J = 165 MM PN16 FLANGE¹⁷ INLET X GE OUTLET
K = 8" FLANGE¹⁷ INLET X FLANGE¹⁷ OUTLET
L = 8" PN16 FLANGE¹⁷ INLET X PN16 FLANGE¹⁷ OUTLET

TRIM TYPE & B1 ACCELERATOR OPTION

1 = DOUBLE INTERLOCK, TYPE D, W/O B1 ACCELERATOR
2 = DOUBLE INTERLOCK, TYPE D, WITH B1 ACCELERATOR²

ASSEMBLY CONFIGURATION, VALVE COLOR & INSTALLED CONTROL
VALVE OPTIONS

1 = LOOSE TRIM FOR 4" - 8" VALVES^{1,5}
 2 = SEGMENTALLY ASSEMBLED FOR 4" - 8" VALVES^{2,5}
 3 = FULLY ASSEM. TO BLACK DDX VALVE, W/O CONTROL VALVE
 4 = FULLY ASSEM. TO RED DDX VALVE, W/O CONTROL VALVE
 5 = FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, W/O CONTROL VALVE⁶
 6 = FULLY ASSEM. TO BLACK DDX VALVE, WITH CONTROL VALVE⁷
 7 = FULLY ASSEM. TO RED DDX VALVE, WITH CONTROL VALVE⁷
 A = FULLY ASSEM. TO RED CCCF APPROVED DDX VALVE, WITH CONTROL VALVE^{8,7}

TRIM FINISH⁴

0 = GALVANIZED
1 = BLACK PIPE
2 = BRASS
3 = STA IN LESS STEEL
4 = GALV. (U.S. SOURCED)
5 = BLACK PIPE (U.S. SOURCED)
6 = BRASS (U.S. SOURCED)
7 = STA IN LESS STEEL (U.S. SOURCED)

SOLENOID VALVE³

0 = NONE
1 = 175 PSI
2 = 300 PSI
3 = 175 PSI EXPLOSION PROOF
4 = 300 PSI EXPLOSION PROOF
5 = 232 PSI

SYSTEM PRESSURE SWITCH

0 = NONE
1 = POTTER FM, cULus APPROVED
2 = SYSTEM SENSOR FM /UL APPROVED
3 = SYSTEM SENSOR FM /ULC APPROVED
4 = POTTER, EXPOSION PROOF

NOTES:

1. FOR THE 4TH DIGIT, SELECT "0" FOR LOOSE OR SEGMENTED TRIMS. 7TH DIGIT MUST BE "1", OR "3". FOR ANY 4TH DIGIT SELECTION OTHER THAN "0", THE 7TH HAS TO BE A FULLY-ASSEMBLED SELECTION ("4", "5" ...ETC).

2. STANDARD FLANGE TYPE IS CLASS 150 PER ASME B16.5.

4. GALVANIZED PIPE FITTINGS ARE THE DEFAULT OFFERING.

5. FOR LOOSE AND SEGMENTED ASSEMBLED TRIM CONFIGURATIONS, THE DDX VALVE IS SOLD SEPARATELY (SEE BULL

6. CHINA COMPULSORY CERTIFICATE FOR FIRE PRODUCTS


7. FLANGED VALVES ARE NOT AVAILABLE WITH A CONTROL

8. A SYSTEM PRESSURE SWITCH IS INCLUDED BY DEFAULT WITH THE FOLLOWING TRIMS

9. 75 MM AND 155 MM ARE NOT AVAILABLE WITH A CONTROL VALVE (REFER TO DIGIT #7)

[Return to top](#)

MODEL DDX 4", 6" & 8" DELUGE DOUBLE INTERLOCK TYPE D
ASSEMBLY P/N 6520101110 REV. J



DDX VALVE PART NUMBER TABLE

DDX. VALVE		VALVE PART NUMBER	DRAWING FILE NUMBER
4"	DUCTILE IRON G/G BLACK	6103040026	
4"	DUCTILE IRON G/G RED	6103040030	
4"	DUCTILE IRON F/G CLASS 150 BLACK	6103040044	
4"	DUCTILE IRON F/G CLASS 150 RED	6103040046	
4"	DUCTILE IRON F/G PN16 RED	6103040048	6103040026
4"	DUCTILE IRON F/F CLASS 150 BLACK	6103040045	
4"	DUCTILE IRON F/F CLASS 150 RED	6103040047	
4"	DUCTILE IRON F/F PN16 RED	6103040049	
6"	DUCTILE IRON G/G BLACK	6103060024	
6"	DUCTILE IRON G/G RED	6103060030	
6"	DUCTILE IRON F/G CLASS 150 BLACK	6103060045	
6"	DUCTILE IRON F/G CLASS 150 RED	6103060048	
6"	DUCTILE IRON F/G PN16 RED	6103060049	6103060024
6"	DUCTILE IRON F/F CLASS 150 BLACK	6103060046	
6"	DUCTILE IRON F/F CLASS 150 RED	6103060047	
6"	DUCTILE IRON F/F PN16 RED	6103060050	
165MM	DUCTILE IRON G/G RED	6103060028	
165MM	DUCTILE IRON F/G CLASS 150 RED	6103060051	6103060024
165MM	DUCTILE IRON F/G PN16 RED	6103060052	
8"	DUCTILE IRON G/G BLACK	6103080001	
8"	DUCTILE IRON G/G RED	6103080003	
8"	DUCTILE IRON F/F CLASS 150 BLACK	6103080016	6103080001
8"	DUCTILE IRON F/F CLASS 150 RED	6103080018	
8"	DUCTILE IRON F/F PN16 RED	6103080020	

30	6990012997	SWITCH, PRESSURE (PS10-EX), SYSTEM	(ULC, UL, FM)	I
	6990017031	SWITCH, PRESSURE (PS15-2), SYSTEM	(ULC, UL, FM)	
	6999992360	SWITCH, PRESSURE (EPSA10-2), SYSTEM	(ULC)	
	6999991212	SWITCH, PRESSURE (EPS10-2), SYSTEM	(UL/FM)	
29	89141112	TIE, RETAINING		9
28	96686756	TUBING, PVC, 3/8" I.D. x 6 FT.		I
27	95516915	PERMA-LOK	NOT SHOWN	A/R
26	98174400	ELBOW, STREET, 1/2", GALV.		I
25	98840243	VALVE, SWING CHECK, M-M, 1/2 NPT, TIEMME		I
24	98840237	VALVE, BALL, 1/4" NPTF x 1/4" NPTM		I
23	98815204	UNION, ORING SEAL, GALV., 1/2		I
22	98761651	TEE, 1/2X1/2X1/2, GALVANIZED		I
21	6304001110	MODEL A PRESSURE MAINTENANCE DEVICE (PMD)		I
20	98048000	BUSHING, REDUCER, 1/2X1/4, GALVANIZED		I
19	98048022	BUSHING, REDUCER, 3/4X1/2, GALVANIZED		I
18	95306255	CLAMP, HOSE, 1/2" CONSTANT TENSION, ZINC		8
17	92056704	CONNECTOR, ELBOW, 3/8" ID TUBE x 1/2" NPT		I
16	98174408	ELBOW, STREET, 1/4", GALV.		I
15	77000266	SUB-ASSEMBLY, TRIM, BASE, GALVANIZED PIPE		I
14	99080002	PAD-ADHESIVE, VALVE NAME PLATES		I
13	98543217	NIPPLE, 1/4X6, GALVANIZED STEEL		I
12	98543230	NIPPLE, 1/2X3, GALVANIZED STEEL		2
11	98543210	NIPPLE, 1/2X2-1/2, GALVANIZED STEEL		2
10	98543223	NIPPLE, 1/2X1-1/2, GALVANIZED STEEL		I
9	94616918	NAMEPLATE, DOUBLE INTERLOCK, TYPE D		I
8	91004299	MANIFOLD, DRAIN, BARBED, 6-3/16		I
7	98248000	GAUGE, AIR PRESSURE (0-80 PSI)		2
6	98174404	ELBOW, 1/4", MALL IRON, GALV.		I
5	98174401	ELBOW, 1/2", MALL IRON, GALV.		2
4	77000308	SUBASSEMBLY, CONTROL VALVE, 8"	FULLY ASSEMBLED WITH CONTROL VALVE ONLY	I
	77000306	SUBASSEMBLY, CONTROL VALVE, 6"		
	77000304	SUBASSEMBLY, CONTROL VALVE, 4"		
3	6871020033	VALVE, SOLENOID (300 PSI) EXPLOSION PROOF	300 PSI EX. PROOF	I
	6999990322	VALVE, SOLENOID (175 PSI) EXPLOSION PROOF	175 PSI EX. PROOF	
	6871020020	VALVE, SOLENOID (300 PSI)	300 PSI RATED	
	6871020000	VALVE, SOLENOID (175 PSI)	175 PSI RATED	
	6871100000	VALVE, SOLENOID (232 PSI)	232 PSI RATED	
2	6990012997	SWITCH, PRESSURE POTTER (PS10-EX)	(ULC, UL, FM)	I
	6990006382	SWITCH, PRESSURE (PS10-2)	(ULC, UL, FM)	
	6999992360	SWITCH, PRESSURE (EPSA10-2)	(ULC)	
	6999991212	SWITCH, PRESSURE (EPS10-2)	(UL/FM)	
I	SEE DDX VALVE P/N TABLE			I
ITEM NO.	PART NO.	DESCRIPTION		QTY.

BILL OF MATERIALS

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO THE RELIABLE AUTOMATIC SPRINKLER CO. IT MAY NOT BE REPRODUCED NOR MAY ANY INFORMATION HEREON BE DISCLOSED TO OTHERS WITHOUT THE SPECIFIC WRITTEN PERMISSION OF RELIABLE.		VOLUME CU. IN.		THE RELIABLE AUTOMATIC SPRINKLER CO., INC. LIBERTY, S.C.			
		0.000		PART NO: VARIOUS			DWG.SIZE: C
DO NOT SCALE DRAWING. REMOVE BURRS, BREAK SHARP EDGES		TOLERANCE UNLESS OTHERWISE SPECIFIED		PART: ASSEMBLY, TRIM, DOUBLE INTERLOCK, TYPE D			
ANGLE $\pm 1/2^\circ$				PRODUCT: DDX, 4", 6", 8"			
MACH. FINISH $\checkmark$		FRACT. $\pm 1/32$ [0.79]		FILE NO:		ENG: JJ	DRW BY: PH
		DEC. XX $\pm .010$ [0.25]		6520101110		SCALE: 1:8	DATE: 12/05/17
		DEC. XXX $\pm .005$ [0.13]		SHEET 2 of 3			

4

3

2

1

REVISIONS




LTR	DESCRIPTION	DATE	DRAWN BY
	SEE PAGE 1		

MODEL DDX 4", 6", 8" BASIC TRIMS

SUBASSEMBLY P/N 77000266 REV. M

MODEL DDX VALVE WITH STAINLESS STEEL SCREW-IN SEAT

IMPORTANT NOTE: Early generation 4" and 6" DDX valves may incorporate a brass drop-in seat. Prior to ordering replacement parts, confirm the presence of a stainless steel screw-in seat or brass drop-in seat. For replacement parts for valves with brass drop-in seat, please contact Reliable Sprinkler Company Technical Services (techserv@reliablesprinkler.com)



Model DDX (Screw-In Seat Configuration) Deluge Valves Parts List

Item No.	Part No.								Part Description	QTY.	Material
	2" (50mm)	2½" (65mm)	76mm	3" (80mm)	4" (100mm)	165mm	6" (150mm)	8" (200mm)			
1	91006011	91006012	91006023	91006013	91006005	91006027	91006007	91006028	Valve Body Groove/Groove	1	Ductile Iron 65-45-12
	N/A	N/A	N/A	N/A	91006045	N/A	91006067	N/A	Valve Body Flange/Groove		
	N/A	N/A	N/A	N/A	91006035	N/A	91006037	91006039	Valve Body Flange/Flange		
2	N/A	N/A	N/A	N/A	N/A	N/A		95406414	O-ring (Mounting Ring)	1	Buna-N
3	71040416								Pushrod Cover Assembly	1	Ductile Iron 65-45-12 & Brass C360000
4	91106123				N/A	N/A		N/A	Hex Bolt ½"-13 x 1¼"	6	Zinc Plated Steel
	N/A				95606107	N/A		N/A	Hex Bolt ½"-13 x 1½"	6	
	N/A				N/A	91106006		N/A	Hex Bolt ⅝"-11 x 1¾"	6	
	N/A				N/A	N/A		95606110	Hex Bolt ⅝"-11 x 2"	8	
5	91306013				91306014	91306016		91306018	Mounting Ring	1	Stainless Steel CF8 or CF8M
6	91916003				91916014	91916016		91916008	Clapper	1	Stainless Steel CF8 or CF8M
7	92116063				92116064	92116065	92116066	92116068	Access Cover	1	Ductile Iron 65-45-12
8	93416003				93416014	93416016		93416008	Seal Assembly	1	Stainless Steel 304 & EPDM
9	93706003				93706004	93706006		93706008	Access Cover Gasket	1	Buna-N or Neoprene
10	93722000				93722000	N/A		N/A	Bumpstop Assembly	1	Stainless Steel UNS S31600 & EPDM
	N/A				N/A	93722000		N/A		2	
	N/A				N/A	N/A		93722000		3	
11	93916006								Pushrod Guide	1	Acetal
12	93916066								Reset Shaft	1	Brass UNS C36000
13	94106066								Reset Housing	1	Brass UNS C36000
14	94356006								Reset Knob	1	Aluminum 6061
15	94506003				94506004	94506016		94506008	Lever	1	Stainless Steel UNS S17400
16	95006412				94006412	95006410		95006410	Striker	1	Aluminum Bronze C95400
17	95106006								Piston	1	Stainless Steel CF8M
18	95276006								Diaphragm	1	EPDM & Polyester
19	95306267				N/A	N/A		N/A	Retaining Ring, ⅜" Shaft, Lever Pin	2	Stainless Steel 15-7 or 17-7
	N/A				95306267	N/A		N/A	Retaining Ring, ½" Shaft, Lever Pin		
	N/A				N/A	95306269		N/A	Retaining Ring, ⅝" Shaft, Lever Pin		
	N/A				N/A	N/A		95316408	Retaining Ring, ¾" Shaft, Lever Pin		
20	95306268				N/A	N/A		N/A	Retaining Ring, ⅝" Shaft, Hinge Pin	2	Stainless Steel 15-7 or 17-7
	N/A				95306267	95306267		N/A	Retaining Ring, ½" Shaft, Hinge Pin		
	N/A				N/A	N/A		95316408	Retaining Ring, ¾" Shaft, Hinge Pin		
21	95406007								O-Ring, Reset Housing ID	1	Buna-N
22	95406024								O-Ring, Reset Housing & Pushrod Guide OD	2	Buna-N
23	95406407								O-Ring, Pushrod Guide ID	1	Buna-N
24	95406410				95406409	95436126		95406413	O-Ring, Upper Seat	1	Buna-N
25	95406411				95406420	95446226		95406412	O-Ring, Lower Seat	1	Buna-N
26	95506006								Pushrod	1	Stainless Steel UNS S30300
27	95606114								Socket Head Screw, ¼"-20 x ⅝"	6	Steel
28	95606127								Flat Head Socket Cap Screw ⅜"-16 x ¾"	1	Steel
29	95606133				N/A	N/A		N/A	Socket Head Screw #6-32 x ½"	1	Stainless Steel 18-8
	N/A				95606130	95606130		95606130	Socket Head Screw #10-32 x 1"		Stainless Steel UNS S31600
30	96016003				96016014	96016016		96016008	Seat	1	Stainless Steel CF8M
31	96206003				N/A	N/A		N/A	Hinge Pin	1	Stainless Steel UNS S30400
	N/A				96216086	9216086		96206008			Stainless Steel UNS S21800
32	96216003				N/A	N/A		N/A	Lever Pin	1	Stainless Steel UNS S17400
	N/A				96216044	96216047		96216008			Stainless Steel UNS S21800
33	96310003				96906904	96906904		96310008	Clapper Spacer	2	Teflon or Acetal
34	96406003				N/A	N/A		N/A	Lever Spring	1	Stainless Steel UNS S30400
	N/A				96406004	96406005		96406008			Stainless Steel UNS S31600
35	96406906								Piston/ Reset Spring	2	Stainless Steel UNS S31600
36	96906112				N/A	N/A		N/A	Spring Lock Washer, #6	1	Stainless Steel 18-8
	N/A				96906111	96906111		96906111	Spring Lock Washer, #10		Stainless Steel UNS S31600
37	95606140				N/A	N/A		N/A	Flat Head Socket Cap Screw ¼"-20 x ½"	2	Stainless Steel 18-8
	N/A				95606139	N/A		N/A			Stainless Steel UNS S31600
	N/A				N/A	N/A		95606135	Flat Head Socket Cap Screw ½"-13 x ¾"		Stainless Steel UNS S31600
38	98604402								Plug, ½" NPT	1	Steel
39	94616921								Knob Caution Label (Not Shown)	1	Polystyrene
40	91556922								Ball Chain, 1/8" (Not Shown) (Length is in Inches)	6	Nickel Plated Brass
41	91556923								Clamping Link, Ball Chain (Not Shown)	1	
42	6999993406								O-Ring Grease, Dupont™ Krytox® GPL-205	A/R	Krytox®