

# Reliable®

## Model GXLO Series Sprinklers

Storage and Non-Storage Sprinklers  
K11.2 (160 metric)


### Product Description

Reliable Model GXLO (extra-large orifice) upright and pendent sprinklers are standard coverage standard response sprinklers that utilize a robust center strut, solder in compression thermal element. These sprinklers are intended for use in hydraulically calculated control mode density area (CMDA) storage and non-storage occupancies in accordance with the area/density curves of NFPA 13 or other applicable standards.

The Model GXLO sprinkler is FM Approved as a standard response storage and non-storage sprinkler when used in accordance with FM Global Property Loss Prevention Data Sheets.

For new installations, the sprinkler is provided with either 3/4-inch NPT or ISO 7-R3/4 threads. The upright version is also available with 1/2-inch NPT or ISO 7-R1/2 threads for retrofit installations only. Sprinklers without guards are installed using the Model H wrench.

For use as an intermediate level sprinkler, the Model GXLO upright sprinkler is available with a factory installed water shield. Various other water shields, guards, or guard/shield options are also available for both upright and pendent models (please refer to Technical Specifications on following pages). Sprinkler guards or guard/shields may be installed in the field or factory installed. Use of the Model JV sprinkler wrench is required for installation where a guard is added to the sprinkler prior to threading the assembly into a fitting.



Model GXLO Series Sprinklers



Upright with Factory Installed Shield

### Model GXLO Specifications

Table A

Style	Sprinkler Identification Number (SIN)	Listings and Approvals	Sensitivity	K-Factor
Upright	R2921	cULus, FM	Standard Response	11.2 (160 metric)
Pendent	R2916	FM		

**Technical Specifications**

**Style:** Upright  
**Threads:** 3/4" NPT or ISO 7-1R3/4  
 1/2" NPT or ISO 7-1R1/2 for  
 Retrofit Application ONLY  
**Nominal K-Factor:** 11.2 (160 metric)  
**Max. Working Pressure:** 175 psi (12 bar)

**Material Specifications**

**Thermal Sensor:** Solder Capsule  
**Sprinkler Frame:** Brass Alloy  
**Button/Cup:** Brass Alloy  
**Sealing Assembly:** Brass with PTFE  
**Load Screw:** Bronze  
**Deflector:** Bronze Alloy  
**Levers:** Bronze Alloy  
**Ejection Spring:** Stainless Steel

**Sprinkler Finishes**

See Table C)

**Sensitivity**

Standard Response

**Temperature Ratings**

See Table D

**Guards & Shields**

D-6 Guard & Water Shield (cULus)  
 D-7 Guard & Water Shield (FM)  
 Water Shield (factory installed) (FM)

**Sprinkler Wrench**

Model H  
 Model JV (when guard is installed prior to  
 make-in)


**Listings and Approvals**

cULus Listed  
 FM Approved



**Model GXLO Upright Components and Dimensions**

**Figure 1**



**Model GXLO Pendent Sprinkler**

**SIN R2916**

**Technical Specifications**

**Style:** Pendent  
**Threads:** 3/4" NPT or ISO 7-1R3/4  
**Nominal K-Factor:** 11.2 (160 metric)  
**Max. Working Pressure:** 175 psi (12 bar)

**Material Specifications**

**Thermal Sensor:** Beryllium Nickel Solder Link  
**Sprinkler Frame:** Brass Alloy  
**Button/Cup:** Brass Alloy  
**Sealing Assembly:** Brass Alloy with PTFE  
**Load Screw:** Bronze  
**Deflector:** Bronze Alloy  
**Levers:** Bronze Alloy

**Sprinkler Finishes**  
 See Table C

**Sensitivity**

Standard Response

**Temperature Ratings**

See Table D

**Guards & Shields**

D-8 Guard (FM)  
 D-9 Guard & Water Shield (FM)

**Sprinkler Wrench**

Model H  
 Model JV (when guard is installed prior to make-in)


**Listings and Approvals**

FM Approved



**Model GXLO Pendent Components and Dimensions**

**Figure 2**



**Model GXLO Commodity Selection and Design Criteria Overview**

**Table B**

<b>Storage Type</b>	<b>NFPA</b>	<b>FM GLOBAL</b>
Sprinkler Type	CMDA	Storage
Response Type	SR	SR
System Type	Pendent - Wet Upright - Wet, Dry, Preaction	Pendent - Wet Upright - Wet, Dry, Preaction
Temperature Rating °F (°C)	165, 212, 286 (74, 100, 141)	165, 212, 286 (74, 100, 141)
Roof Construction	See NFPA 13	See FM Global 2-0
Ceiling Slope	See NFPA 13	See FM Global 2-0
Maximum Coverage Area	See NFPA 13	See FM Global 2-0
Minimum Coverage Area	See NFPA 13	See FM Global 2-0
Maximum Spacing	See NFPA 13	See FM Global 2-0
Minimum Spacing	See NFPA 13	See FM Global 2-0
Minimum Clearance to Commodity	See NFPA 13	See FM Global 2-0
Sprinkler Distance to Ceiling	See NFPA 13	See FM Global 2-0
Open Frame, Single, Double, Multiple Row, or Portable Rack Storage of Class I - IV Commodity and Group A Plastic	See NFPA 13	See FM 2-0 & 8-9
Solid Pile or Palletized Storage of Class I - IV Commodity and Group A Plastic	See NFPA 13	See FM 2-0 & 8-9
Idle Pallet Storage	See NFPA 13	See FM 2-0,8-9 & 8-24
Rubber Tire Storage	See NFPA 13	See FM 8-3
Rolled Paper Storage	See NFPA 13	Pendent - N/A Upright - See FM 8-21
Flammable Liquid Storage	See NFPA 30	See FM 7-29 and 8-9
Aerosol Storage	See NFPA 13	See FM 7-31
Auto Components in Portable Racks	N/A	N/A

## Sprinkler Finishes

**Table C**

Standard Finishes	Special Application Finishes	
Bronze	Lead Plated <sup>(1)</sup>	165°F (74°C), 212°F (100°C) and 286°F (141°C) Temp. Ratings
Chrome <sup>(1)</sup>	Wax <sup>(1)(2)</sup>	165°F (74°C) Clear Wax, 212°F (100°C) Brown Wax
	Wax/Lead <sup>(1)(2)</sup>	165°F (74°C) Clear Wax, 212°F (100°C) Brown Wax

<sup>(1)</sup> cULus, upright (without shield) only.

<sup>(2)</sup> 212°F (100°C) Brown wax may be used on 286°F (141°C) Sprinklers when maximum ambient temperatures do not exceed 150°F (66°C).

## Temperature Ratings

**Table D**

Classification	Sprinkler Rating		Maximum Ambient Temperature		Frame Color
	°F	°C	°F	°C	
Ordinary	165	74	100	38	Uncolored
Intermediate	212	100	150	66	White
High	286	141	225	107	Blue

## Installation


Model GXLO sprinklers must be installed according to appropriate NFPA Standards, FM Global Loss Prevention Data Sheets, and/or the requirements of the authority having jurisdiction.

Use only the Model H sprinkler wrench for sprinkler installation or use the Model JV wrench to install the sprinkler/guard assembly (Figure 3). Any other type of wrench may damage the sprinkler. Damaged sprinklers must be replaced immediately.

A leak tight joint should be obtained with a torque of 14 to 20 lb-ft (19 to 27 N·m) for 3/4 inch NPT and ISO 7-R3/4 thread sprinklers. For 1/2 inch NPT and ISO 7-R1/2 thread sprinklers the recommended installation torque is 8 to 18 lb-ft (11 to 24 N·m). Exceeding the maximum recommended torque may cause leakage or impairment of the sprinklers.

## Wrenches

**Figure 3**



## Maintenance

Reliable Model GXLO sprinklers should be inspected and the sprinkler system maintained in accordance with NFPA 25, as well as the requirements of any Authorities Having Jurisdiction.

Prior to installation, sprinklers should remain in the original cartons and packaging until used. This will minimize the potential for damage to sprinklers that could cause improper operation or non-operation.

Do not clean sprinklers with soap and water, ammonia liquid or any other cleaning fluids. Remove dust by gentle vacuuming without touching the sprinkler.

Replace any sprinkler which has been painted (other than factory applied). A stock of spare sprinklers should be maintained to allow quick replacement of damaged or operated sprinklers.

Failure to properly maintain sprinklers may result in inadvertent operation or non-operation during a fire event.

## Guarantee

For the Reliable Automatic Sprinkler Co., Inc. guarantee, terms, and conditions, visit [www.reliablesprinkler.com](http://www.reliablesprinkler.com).

## Ordering Information

Specify the following when ordering.

### Model GXLO Sprinkler

- [Upright] [3/4" NPT] [ISO 7-R3/4]
- [Pendent] [3/4" NPT] [ISO 7-R3/4]
- [Upright Retrofit] [1/2" NPT] [ISO 7-R1/2]
- [Upright with factory installed shield]

### Temperature Rating

- [165°F (74°C)] [212°F (100°C)] [286°F (141°C)]

### Finish

- See Table C

### Guard/Shield

- See Technical Specifications

### Sprinkler Wrench

- [Model H] [Model JV (required with pre-installed guards)]