



Model SRMT1 Special Grooved Reducing Tee

cULus Listed
300 psi (20.7 bar)

SRMT1 Special Grooved Reducing Tee Technical Data

Operating Specifications

Maximum Working Pressure:
300 psi (20.7 bar)

Material Specifications

Body: ASTM A536 Grade 65-45-12 Ductile Iron

Design Specification

Groove: AWWA-C606
FNPT: ASME B1.20.1

Available Finishes

Hot dipped galvanized (ASTM A-153)

Listings and Approvals

cULus Listed



SRMT1 Special Grooved Reducing Tee Dimensions

Figure 1




					Table A
Nominal Size in (mm)	Pipe O.D. in/mm	E - E Dimension in (mm)	C - E Dimension in (mm)	C - C Dimension in (mm)	Weight lb (kg)
2 x 2 x 1-1/2 x 1 (50 x 50 x 40 x 25)	2.375 x 2.375 x 1.900 x 1.315 (60.3 x 60.3 x 48.3 x 33.7)	6-1/2 (165.1)	6-1/2 (165.1)	4-1/4 (107.9)	5.5 (2.50)