

Reliable®

Model J168 Standard Response Upright Sprinkler (SIN RA1124)

Note: This sprinkler is a UL Listed Control Mode Density Area sprinkler.

Features:

1. Utilizes Standard Response center strut solder sensor.
2. 165°F (74°C), 212°F (100°C) and 286°F (141°C) temperature ratings.
3. Available in brass, lead coated, wax coated and wax over lead coated finishes.
4. Provides higher flows at much lower pressures for all occupancies, especially in high density applications, such as the protection of high-piled storage.
5. Limits density increases for plastic pallet applications per NFPA 13.

Listings & Approvals

1. Listed by Underwriters Laboratories Inc. and UL certified for Canada (cULus) to include storage applications.
2. NYC MEA 258-93-E
3. FM Approved as a storage sprinkler.

Technical Data

Applications

Wet, Dry and Pre-Action Sprinkler Systems

Hazards

Ordinary, Extra Hazard and Storage Occupancies per NFPA 13

For Sprinkler Spacing, Positioning, and Density/Area Flow Calculations: refer to NFPA 13

Minimum Working Pressure

7 psi (0,5 bar) residual (flowing)

Maximum Working Pressure

Rated 175 psi (12,1 bar)

Factory tested to 500 psi (34, 5 bar)

Discharge Coefficients (K Factor)

$K=16.8 \text{ GPM}/\text{psi}^{1/2}$ (242 LPM/bar)^{1/2}

Pipe Thread Connection

3/4 NPT (R3/4)

Overall Length

3 1/8 inch (79,4 mm)



Model J168 Upright Sprinkler

Product Description

The Reliable Model J168 Automatic sprinkler utilizes the center strut solder in compression principle of construction. The fusible alloy is captured in the cylinder of the solder capsule by a stainless steel ball. When the fusible alloy melts, the ball moves into the cylinder allowing the cylinder to separate from the center strut. When this happens, the lever is released to spring free from the sprinkler so that all operating parts clear the waterway allowing the deflector to distribute the discharging water in a hemispherical pattern.

The Reliable Model J168, 16.8 K-factor sprinkler was tested in full scale fire tests to qualify for the protection of rack and high piled storage.

Ordering Information

Specify:

1. Model J168 Upright
2. Temperature rating (see page 2)
3. Finish (see page 2)
4. Model J1 Installation Wrench

Design Criteria

FM Approval Requirements

The Reliable Standard Response standard spray J168, K-16.8 Upright Sprinkler is approved to be installed in accordance with FM Data Sheets 8-9 and 2-0. (FM guidelines may be different from UL and C-UL Listing criteria).

cULus Listing Requirements

The Reliable Standard Response J168 Upright Sprinkler is cULus Listed for use in occupancy classifications up to and including Extra-Hazard, for hydraulically calculated wet or dry systems per NFPA 13, with a minimum operating pressure of 7 psi (48,3 kPa) in wet or dry systems. Use the standard sprinkler positioning requirements and density/area sprinkler protection criteria provided in NFPA 13.

Also:

The J168 Sprinkler is cULus Listed for use in High-Piled Storage Occupancies as defined in NFPA 13. This sprinkler may be used for the protection of solid piled, palletized, rack storage (single, double, multiple-row and portable), bin box, and shelf storage including, but not limited to: encapsulated or unencapsulated Class I-IV and Group A or B plastics, cartoned, expanded or unexpanded, as well as exposed unexpanded. For hydraulically calculated wet or dry systems per NFPA 13 with a minimum operating pressure of 7 psi (0,5 bar). Use the standard sprinkler positioning requirements and density/area sprinkler protection criteria provided in NFPA 13 for High-Piled Storage Occupancies.

Refer to NFPA 13 for specific requirements for various combinations of building heights, storage heights, sprinkler- to-commodity clearance, storage arrangements, commodity classifications, and lesser or greater required design densities.

Note: The J168 Sprinkler can be used in any application or building height as allowed by NFPA13 or FM guidelines. The J168 is a standard response standard spray sprinkler with a larger K factor to provide greater water flows at lower pressures.

Installation

The Model J168 Upright Sprinklers are to be installed as follows:

- Install in upright position only.
- Apply pipe thread sealant to NPT threads, hand tighten into the sprinkler fitting.
- Install sprinkler by wrench boss only.
- Wrench tighten with the dedicated J1 Sprinkler Wrench.
- A leak tight 3/4 NPT (R3/4) sprinkler joint can be obtained with a torque of 14 - 20 ft. lbs.
- Higher torques may compromise the seal or function integrity of the sprinkler.

Temperature Ratings

Classification	Sprinkler Rating		Maximum Ambient Temperature		Frame Color
	°F	°C	°F	°C	
Ordinary	165	74	100	38	Uncolored White Blue
Intermediate	212	100	150	66	
High	286	141	225	107	

Special Application Finishes	
Lead Plated	165°F (74°C), 212°F (100°C) and 286°F (141°C) Temp. Ratings
Wax-Coated ⁽¹⁾⁽²⁾	165°F (74°C) Clear Wax, 212°F (100°C) Brown Wax.
Wax-Coated Over Lead Plated ⁽¹⁾⁽²⁾	165°F (74°C) Clear Wax, 212°F (100°C) Brown Wax.

⁽¹⁾ 212°F (100°C) brown wax may be used on 286°F (141°C) sprinklers when maximum ambient temperatures do not exceed 150°F (66°C).

⁽²⁾ Not FM Approved.

Caution: The Reliable Standard Response J168 Upright Sprinkler must be installed and maintained per the application NFPA standards, as well as the standards of other authorities having jurisdiction.



Model J1 Wrench

Maintenance

Model J168 Sprinklers should be inspected and the sprinkler system maintained in accordance with NFPA 25. Do not clean sprinklers with soap and water, ammonia or any other cleaning fluids. Remove dust by using a soft brush or gentle vacuuming. Remove any sprinkler that had been painted (other than factory applied) or damaged in any way. A stock of spare sprinklers should be maintained to allow quick replacement of damaged or operated sprinklers. Prior to installation, sprinklers should be maintained in the original cartons and packaging until used to minimize the potential for damage to sprinklers that would cause improper operation or non-activation.




Fig. 1

Model J168 Technical Data

Table A

ITEM	DESCRIPTION
Sprinkler Identification Number (SIN)	RA1124
K Factor US (Metric)	16.8 (240)
Thread Size	3/4" (ISO 7-R3/4)
Sprinkler Orientation	Upright
Maximum Working Pressure, PSI (bar)	175 PSI (12 bar)

Storage Type	NFPA	FM GLOBAL
Sprinkler Type	CMDA	Storage
Response Type	SR	SR
System Type	Wet, Dry and Preaction	Wet, Dry and Preaction
Temperature Rating F (C)	165,212,286 (74,100,141)	165,212,286 (74, 100,141)
Roof Construction	See NFPA 13	See FM Global 2-0
Ceiling Slope	See NFPA 13	See FM Global 2-0
Maximum Coverage Area	See NFPA 13	See FM Global 2-0
Minimum Coverage Area	See NFPA 13	See FM Global 2-0
Maximum Spacing	See NFPA 13	See FM Global 2-0
Minimum Spacing	See NFPA 13	See FM Global 2-0
Minimum Clearance to Commodity	See NFPA 13	See FM Global 2-0
Sprinkler Distance to Ceiling	See NFPA 13	See FM Global 2-0
Open Frame, Single, Double, Multiple Row, or Portable Rack Storage of Class I-IV, Cartoned Unexp Plastics	See NFPA 13	See FM 2-0 & 8-9
Solid Pile or Palletized Storage of Class I-IV and Cartoned Unexp Plastics	See NFPA 13	See FM 2-0 & 8-9
Idle Pallet Storage	See NFPA 13	See FM 2-0,8-9 & 8-24
Rubber Tire Storage	See NFPA 13	See FM 2-0 & 8-3
Rolled Paper Storage	See NFPA 13	N/A
Flammable Liquid Storage	See NFPA 30	See FM 7-29 & 8-9
Aerosol Storage	See NFPA 30B	See FM 7-31
Auto Components in Portable Racks	N/A	N/A

The equipment presented in this bulletin is to be installed in accordance with the latest published Standards of the National Fire Protection Association, Factory Mutual Research Corporation, or other similar organizations and also with the provisions of governmental codes or ordinances whenever applicable.

Products manufactured and distributed by Reliable have been protecting life and property for over 90 years.

Manufactured by



Reliable Automatic Sprinkler Co., Inc.
 (800) 431-1588 Sales Offices
 (800) 848-6051 Sales Fax
 (914) 829-2042 Corporate Offices
 www.reliablesprinkler.com Internet Address



Revision lines indicate updated or new data.
 EG. Printed in U.S.A. 07/19 P/N 9999970290