# Model KFR56-300 Series Sprinklers

Quick-response, Standard Spray Fusible Link Sprinklers

K5.6 (80 metric), 300 psi (20.7 bar) rated cULus Listed

# **Product Description**

Model KFR56-300 series sprinklers are standard spray, quickresponse sprinklers with a fusible link operating element. The sprinklers are cULus Listed for a maximum working pressure of 300 psi (20.7 bar). See Table C for available finishes. All KFR56-300 sprinklers have a nominal K-factor of 5.6 (80 metric).

Model KFR56-300 series sprinklers are available in Ordinary (165°F [74°C]) or Intermediate (212°F [100°C]) temperature classification. Model KFR56-300 Pendent sprinklers are available with Model F1, Model F2, or Model FP recessed escutcheons.



Model KFR56-300 series sprinklers are listed and approved for installation in accordance with NFPA 13. Follow requirements of NFPA 13 for Quick-response Standard Spray Sprinklers when installing Model KFR56-300 series sprinklers.



Model KFR56-300 Pendent





Model KFR56-300 Upright



Model KFR56-300 HSW

# Installation

Model KFR56-300 series sprinklers must be installed in accordance with the requirements of NFPA 13. The Model F1, F2, and FP escutcheons are the only recessed escutcheons listed and approved for use with Model KFR56-300 Pendent sprinklers. The use of any other recessed escutcheon will void all approvals and warranties. Do not install Model FP escutcheons in ceilings that are positively pressurized with respect to the occupied space below.

Use only the Model W2 sprinkler wrench for installing Model KFR56-300 series pendent, upright, and horizontal sidewall sprinklers, and use only the Model W1 wrench for installing Model KFR56-300 series recessed pendent, conical concealed pendent (CCP), and recessed horizontal sidewall sprinklers. The use of wrenches other than those specified may damage these sprinklers.

Recommended installation torque is 14-20 ft-lbs (19 - 27 N·m). Do not tighten sprinklers over the maximum recommended torque. Exceeding the maximum recommended torque may cause leakage or impairment of the sprinklers.

# **Listings & Approvals**

Listed by Underwriters Laboratories, Inc. and UL Certified for Canada (cULus)

Sprinklers, Automatic and Open (VNIV)

Model KFR Series Sprinkler Summary						
Sprinkler Model	Orientation	Listing or Approval	Max. Working Pressure psi (bar)	Sprinkler Identification Number (SIN)		
KFR56-300 Pendent	Pendent	cULus	300 (20.7)	RA3914		
KFR56-300 Upright	Upright	cULus	300 (20.7)	RA3924		
KFR56-300 HSW	HSW	cULus	300 (20.7)	RA3934		

# Model KFR56-300 Pendent sprinkler

**SIN RA3914** 

#### **Technical Specifications**

Style: Pendent, Recessed Pendent, or Conical

Concealed Pendent

Threads: 1/2" NPT or ISO7-1R1/2 Nominal K-Factor: 5.6 (80 metric) Max. Working Pressure: 300 psi (20.7 bar)

#### **Material Specifications**

Thermal Sensor: Beryllium Nickel Strut and Lever: Stainless Steel Roto-clip: Stainless Steel Sprinkler Frame: Brass Alloy

Cap: Bronze Alloy

Sealing Washer: Nickel with PTFE Load Screw: Copper Alloy Deflector: Brass Alloy

# Sprinkler Wrenches Model W2 (pendent)

Model W1 (recessed) Model W14 (with guard installed)

Listings and Approvals

cULus Listed

#### Sprinkler Finishes

(See Table C)

#### Sensitivity

Quick-response

#### **Temperature Ratings**

165°F (74°C), Gray Link 212°F (100°C), White Link

#### **Recessed Escutcheons/Cover Plates**

Model F1 escutcheon Model F2 escutcheon Model FP escutcheon Model CCP cover plate

#### **Guards/Water Shields**


F-7 Guard


F-8 Guard/Water Shield S-1 Water Shield




# Model KFR56-300 Pendent Sprinkler Components and Dimensions

Figure 1





Reliable



# Model KFR56-300 Upright Sprinkler

**Technical Specifications** 

Style: Upright

Threads: 1/2" NPT or ISO7-1R1/2 Nominal K-Factor: 5.6 (80 metric) Max. Working Pressure: 300 psi (20.7bar)

**Material Specifications** 

Thermal Sensor: Beryllium Nickel Strut and Lever: Stainless Steel Roto-clip: Stainless Steel Sprinkler Frame: Brass Alloy

Cap: Bronze Alloy

Sealing Washer: Nickel with PTFE Load Screw: Copper Alloy Deflector: Brass Alloy

# Sprinkler Wrench

Model W2

Model W14 (with guard installed)

#### **Listings and Approvals**

cULus Listed

### **Sprinkler Finishes**

(See Table C)

# Sensitivity

Quick-response

# **Temperature Ratings**

165°F (74°C), Gray Link 212°F (100°C), White Link

# **Guards/Water Shields**

F-1 Guard


F-3 Guard/Water Shield




# Model KFR56-300 Upright Sprinkler Components and Dimensions

Figure 2

**SIN RA3924** 





Reliable



# Model KFR56-300 HSW Horizontal Sidewall Sprinkler

Technical Specifications

Style: HSW or Recessed HSW Threads: 1/2" NPT or ISO7-1R1/2 Nominal K-Factor: 5.6 (80 metric)

Max. Working Pressure: 300 psi (20.7 bar)

**Material Specifications** 

Thermal Sensor: Beryllium Nickel Strut and Lever: Stainless Steel Roto-clip: Stainless Steel Sprinkler Frame: Brass Alloy

Cap: Bronze Alloy

Sealing Washer: Nickel with PTFE Load Screw: Copper Alloy Deflector: Brass Alloy

Sprinkler Wrench

Model W2 (HSW) Model W1 (recessed)

Model W14 (with guard installed)

### **Listings and Approvals**

cULus Listed

#### Sprinkler Finishes

(See Table C)

#### Sensitivity

Quick-response

## **Temperature Ratings**

165°F (74°C), Gray Link 212°F (100°C), White Link

### Recessed Escutcheons

Model F1 escutcheon Model FP escutcheon

## Guards


F-7 Guard




# Model KFR56-300 HSW Sprinkler Components and Dimensions


Figure 3


**SIN RA3934** 













#### F1 RECESSED ESCUTCHEON INSTALLATION

#### **F2 RECESSED ESCUTCHEON INSTALLATION**





#### **CCP COVER PLATE INSTALLATION**

#### FP RECESSED ESCUTCHEON INSTALLATION


Note: Model KFR spriinklers with Model CCP cover plate or Model FP recessed escutcheon may not be used in locations where the pressure in the ceiling above the sprinkler is positive with respect to the protected space. Ensure that the holes in the sprinkler cup are unobstructed following installation.









Note: Photos are intended to depict escutcheon style; actual sprinkler will vary.



# F1 RECESSED ESCUTCHEON INSTALLATION



#### **F2 RECESSED ESCUTCHEON INSTALLATION**



# FP RECESSED ESCUTCHEON INSTALLATION


Note: Model KFR spriinklers with Model FP recessed escutcheon may not be used in locations where the pressure in the space behing the sprinkler is positive with respect to the protected space. Ensure that the holes in the sprinkler cup are unobstructed following installation.



Standard Finishes			Special Application Finishes		
Sprinkler	F1, F2 , and FP <sup>(2)</sup> Escutcheons	CCP Cover Plate	Sprinkler	F1, F2 , and FP <sup>(2)</sup> Escutcheons	CCP Cover Plate
Bronze	Brass		Bright Brass	Bright Brass	Bright Brass
Chrome Plated	Chrome Plated	Chrome Plated	Dull Chrome	Dull Chrome	Dull Chrome
White Polyester	White Polyester	White Paint	Black Polyester	Black Polyester	Black Paint
			Custom Color Polyester	Custom Color Polyester	Custom Color Paint

#### Notes:

- (1) Paint or any other coating applied over the factory finish will void all approvals and warranties.
- (2) The Model FP escutcheon assembly consists of an unfinished galvanized cup with a finished escutcheon ring.



#### **Maintenance**

Reliable Model KFR56-300 series sprinklers should be inspected and the sprinkler system maintained in accordance with NFPA 25, as well as the requirements of any Authorities Having Jurisdiction.

Prior to installation, sprinklers should remain in the original cartons and packaging until used. This will minimize the potential for damage to sprinklers that could cause improper operation or non-operation.

Do not clean sprinklers with soap and water, ammonia liquid or any other cleaning fluids. Remove dust by gentle vacuuming without touching the sprinkler.

Replace any sprinkler which has been painted (other than factory applied). A stock of spare sprinklers should be maintained to allow quick replacement of damaged or operated sprinklers.

Failure to properly maintain sprinklers may result in inadvertent operation or non-operation during a fire event.

#### Guarantee

For the Reliable Automatic Sprinkler Co., Inc. guarantee, terms, and conditions, visit www.reliablesprinkler.com.

# **Ordering Information**

Specify the following when ordering.

#### **Sprinkler**

- Model (KFR56-300 Pendent, KFR56-300 Upright, or KFR56-300 HSW)
- Temperature Rating [165°F (74°C) or 212°F (100°C)]
- Threads (1/2" NPT or ISO 7-1 R1/2)
- Finish (See Table C)

# **Escutcheon or Coverplate**

- Type (None, F1, F2, FP, or CCP)
- Finish (See Table C)

#### **Guards/Water Shields**

• See sprinkler information pages in this bulletin

#### Sprinkler Wrench

- W2 (Pendent, Upright, & HSW)
- W1 (Recessed Pendent & HSW, CCP)
- W14 (with guard installed)