




Flexible Sprinkler Hose with Fittings



Reliable®

Series RFB Braided Hose Assemblies



Series RFU Unbraided Hose Assemblies



The **RASCOFLEX** Flexible Sprinkler Drop is manufactured for installation on suspended ceiling grids. They can be applied onto grid types such as, T-Bar, metal stud, wood beam, or hat channel grids. RASCOFLEX complete sets come ready to install out of the box and are UL Listed and FM Approved.

RASCOFLEX drops are designed for use in hydraulically intended wet, deluge, pre-action or dry sprinkler systems per NFPA 13, 13R, and 13D guidelines

RASCOFLEX Components


- (Hose Model) 1" Nominal ID Braided Hose
- Lengths: 24", 31", 40", 48", 60", 72"
- 1/2" and 3/4" straight reducers
- 1/2" and 3/4" elbow reducer
- 24" (610mm) and 48" (1219mm) bracket that can be used on suspended T-Bar, Metal Stud, Wood Beam, and Hat Channel ceiling grids.

Technical Data


- Maximum Working Pressure:
 - ♦ 200 psi per FM Approval
 - ♦ 175 psi per UL Listing
- Maximum Ambient Temperature: 300°F
- Connection to Branch Line: 1-inch/25mm NPT/BSPT
- Minimum Bend Radius of Flexible Sprinkler Hose:
 - ♦ 3" (76mm) per UL Listing
 - ♦ 7" (178mm) per FM Approval
- Maximum Number 90° Bends:
Refer to the "Friction Loss Data" on page 5
- Maximum K-Factor of Flexible Sprinkler Hose to be connected Reducing Nipple:
 - ♦ 1/2": 5.6 US (80 Metric)
 - ♦ 3/4": 14.0 US (200 Metric)
- Listing and Approvals
 - ♦ Braided: FM Approved, UL Listed
 - ♦ Unbraided: UL Listed




Braided Flexible Hose



Unbraided Flexible Hose



Bracket Assembly



Material Specifications

Hose	Stainless Steel 304	O-Ring	EPDM
Reducer	Zinc Plated Carbon Steel	Bracket-L	Zinc Plated SPCC Steel
Nipple	Zinc Plated Carbon Steel	Bracket-S	Zinc Plated SPCC Steel
Nut	Zinc Plated Carbon Steel	Braid	Stainless Steel 304
Isolation Ring	Nylon 66	Bar Stock	Zinc Plated SGCC Steel

Braided Hose UL Listed

Model	Outlet Size NPT (inch)	Length inch (mm)	Maximum Number 90° Bends at 3" (76mm) Bend Radius	UL Listed Maximum Equivalent Length of SCH 40 1 inch Diameter Pipe (C=120), ft (m)
RFB24H	1/2	24 (609.6)	2	10 (3)
RFB24T	3/4	24 (609.6)	2	13 (4)
RFB31H	1/2	31 (787.4)	3	14 (4.3)
RFB31T	3/4	31 (787.4)	3	16 (3.9)
RFB40H	1/2	40 (1016)	4	21 (6.4)
RFB40T	3/4	40 (1016)	4	23 (7)
RFB48H	1/2	48 (1219.2)	4	24 (7.3)
RFB48T	3/4	48 (1219.2)	4	26 (7.9)
RFB60H	1/2	60 (1524)	4	25 (7.6)
RFB60T	3/4	60 (1524)	4	30 (9.1)
RFB72H	1/2	72 (1828.8)	5	36 (11)
RFB72T	3/4	72 (1828.8)	5	33 (10.1)

Unbraided Hose UL Listed

Model	Outlet Size NPT (inch)	Length inch (mm)	Maximum Number 90° Bends at 4" (102mm) Bend Radius	UL Listed Maximum Equivalent Length of SCH 40 1 inch Diameter Pipe (C=120), ft (m)
RFU24H	1/2	24 (609.6)	2	21 (6.4)
RFU24T	3/4	24 (609.6)	2	29 (8.8)
RFU31H	1/2	31 (787.4)	2	28 (8.5)
RFU31T	3/4	31 (787.4)	2	32 (9.7)
RFU40H	1/2	40 (1016)	3	41 (12.5)
RFU40T	3/4	40 (1016)	3	52 (15.8)
RFU48H	1/2	48 (1219.2)	3	53 (16.1)
RFU48T	3/4	48 (1219.2)	3	59 (18.0)
RFU60H	1/2	60 (1524)	3	61 (18.6)
RFU60T	3/4	60 (1524)	3	63 (19.2)
RFU72H	1/2	72 (1828.8)	3	65 (19.8)
RFU72T	3/4	72 (1828.8)	3	75 (22.9)



Braided Hose FM Approval

Length of Flexible Hose (inch)	Outlet Size		Sprinkler K-Factor	Maximum Ambient Temperature °F (°C)	Maximum Working Pressure psi (bar)	Maximum Number of 90° Bends at 7" (178mm) Bend Radius	Equivalent Length of 1" (33.7mm) Sch. 40 Pipe ft (m)
	Size (inch)	Type					
24"	1/2	Straight	5.6 (80)	300°F (149°C)	200 (13.79)	1	9.7 (2.9)
	1/2	90° Elbow	5.6 (80)	300°F (149°C)	200 (13.79)	0	11.5 (3.5)
	3/4	Straight	14.0 (200)	300°F (149°C)	200 (13.79)	1	9.9 (3)
	3/4	90° Elbow	14.0 (200)	300°F (149°C)	200 (13.79)	0	10.2 (3.1)
31"	1/2	Straight	5.6 (80)	300°F (149°C)	200 (13.79)	2	12.4 (3.8)
	1/2	90° Elbow	5.6 (80)	300°F (149°C)	200 (13.79)	2	15.8 (4.8)
	3/4	Straight	14.0 (200)	300°F (149°C)	200 (13.79)	2	13.7 (4.1)
	3/4	90° Elbow	14.0 (200)	300°F (149°C)	200 (13.79)	2	14.5 (4.4)
40"	1/2	Straight	5.6 (80)	300°F (149°C)	200 (13.79)	2	15.9 (4.8)
	1/2	90° Elbow	5.6 (80)	300°F (149°C)	200 (13.79)	2	21.6 (6.6)
	3/4	Straight	14.0 (200)	300°F (149°C)	200 (13.79)	2	18.5 (5.6)
	3/4	90° Elbow	14.0 (200)	300°F (149°C)	200 (13.79)	2	20 (6)
48"	1/2	Straight	5.6 (80)	300°F (149°C)	200 (13.79)	3	19.0 (5.8)
	1/2	90° Elbow	5.6 (80)	300°F (149°C)	200 (13.79)	3	25.9 (7.9)
	3/4	Straight	14.0 (200)	300°F (149°C)	200 (13.79)	3	22.7 (6.9)
	3/4	90° Elbow	14.0 (200)	300°F (149°C)	200 (13.79)	3	24.8 (7.5)
60"	1/2	Straight	5.6 (80)	300°F (149°C)	200 (13.79)	4	23.7 (7.2)
	1/2	90° Elbow	5.6 (80)	300°F (149°C)	200 (13.79)	4	33.1 (10)
	3/4	Straight	14.0 (200)	300°F (149°C)	200 (13.79)	4	29.1 (8.8)
	3/4	90° Elbow	14.0 (200)	300°F (149°C)	200 (13.79)	4	32.2 (9.8)
72"	1/2	Straight	5.6 (80)	300°F (149°C)	200 (13.79)	4	28.4 (8.6)
	1/2	90° Elbow	5.6 (80)	300°F (149°C)	200 (13.79)	4	40.4 (12.3)
	3/4	Straight	14.0 (200)	300°F (149°C)	200 (13.79)	4	35.5 (10.8)
	3/4	90° Elbow	14.0 (200)	300°F (149°C)	200 (13.79)	4	39.5 (12)

Limited Warranty

Reliable Automatic Sprinkler Co. warrants that their products will be free of any defects in materials and workmanship under normal conditions of use and service for period of (2) two years from the date of sale. Under this warranty, the obligation is limited to replacing or repairing any product that is returned to RASCOFLEX and after the completion of inspection of defects in material or workmanship under normal operating conditions of use/service. To either repair or replace any product is upon Reliable Automatic Sprinkler Co. to decide. The following are excluded from the coverage of the warranty:

- a. Components other than those manufactured or sold by Reliable Automatic Sprinkler Co.
- b. The installation, designing, inspection, or testing process done in a manner not in compliance with the appropriate and applicable requirements, codes, law, regulation or rule of any federal, state or local governmental or industry standards such as NFPA
- c. Products that have not been inspected and maintained in accordance with Reliable specifications and NFPA standards
- d. Defect resulting from ordinary wear and tear.
- e. Products that have been altered in any way by anyone other than Reliable Sprinkler Co.
- f. Products that have been misused
- g. Exposure to abnormal environmental conditions

This warranty is non-transferable and shall benefit only the original purchaser of the Reliable Flexible Sprinkler product. If any provision here-of or any portion of any provision shall be held invalid, the remainder of this Limited Warranty shall not be affected thereby, and all provisions of this Limited Warranty shall remain valid and in full force and effect to the fullest extent permitted by law.

THIS LIMITED WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. NOTWITHSTANDING ANY PROVISION TO THE CONTRARY HEREIN OR ANY APPLICABLE LAW TO THE CONTRARY, IN NO EVENT SHALL RELIABLE AUTOMATIC SPRINKLER CO., BE LIABLE FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES UNDER ANY CIRCUMSTANCES WHATSOEVER, WHETHER ARISING FROM ANY BREACH OF THIS LIMITED WARRANTY OR OTHERWISE ARISING FROM OR IN CONNECTION WITH THE USE OR OPERATION OF, OR ANY DEFECT IN, ANY RELIABLE SPRINKLER CO, PRODUCT OR OTHERWISE.

**CORPORATE OFFICE:**

103 Fairview Park Drive
Elmsford, NY 10523
Tel.: 800.821.2138
www.reliablesprinkler.com

CORPORATE MANUFACTURING FACILITY:

1470 Smith Grove Road
Liberty, SC 29657
Tel.: 864.843.1700

WORLDWIDE DISTRIBUTION CENTERS, FABRICATION FACILITIES & SALES OFFICES**NEW YORK, NY (Elmsford)**

Tel.: 800.431.1588
Fax: 800.848.6051

HOUSTON, TX

Tel.: 866.978.9965
Fax: 866.978.9979

HAMBURG, GERMANY

Tel.: +49.40.5589 818-71
Fax: +49.40.5589 818-73

BOSTON, MA (Walpole)

Tel.: 800.431.1588
Fax: 800.848.6051

DENVER, CO

Tel.: 877.440.2598
Fax: 877.205.7230

SHANGHAI, CHINA

Tel.: +86.21.54037021
Fax: +86.21.54037022

WASHINGTON, DC (Lorton, VA)

Tel.: 877.883.8831
Fax: 877.851.1553

LOS ANGELES, CA (Brea)

Tel.: 800.352.4365
Fax: 800.848.6055

SINGAPORE

Tel.: +65.9859.0690
Fax: +65.6734.3176

ATLANTA, GA (Norcross)

Tel.: 800.652.1819
Fax: 800.848.6052

SAN FRANCISCO, CA (San Leandro)

Tel.: 800.352.4365
Fax: 800.848.6055

ADELAIDE, AUSTRALIA

Tel.: +61.8.81629555
Fax: +61.8.81629359

ORLANDO, FL (Longwood)

Tel.: 800.801.3097
Fax: 800.862.0934

SEATTLE, WA (Kent)

Tel.: 877.327.2563
Fax: 877.327.2574

DUBAI, UNITED ARAB EMIRATES

Tel.: +971.48808830

MIAMI, FL (Miramar)

Tel.: 954.437.2520
Fax: 954.437.2289

TORONTO CANADA

Tel.: 800.790.6443
Fax: 800.790.6486

FABRICATION:**GRAND PRAIRIE, TX**

Tel.: 972.352.6400
Fax: 972.352.6402

CHICAGO, IL (Hanover Park)

Tel.: 800.228.6274
Fax: 800.848.6053

WESTERN CANADA

Tel.: 877.327.2563
Fax: 877.327.2574

PORTLAND, OR

Tel.: 503.282.5506
Fax: 503.282.0092

MINNEAPOLIS, MN (Roseville)

Tel.: 877.827.2816
Fax: 877.827.3043

MEXICO & LATIN AMERICA

Tel.: 800.442.6742
Fax: 800.848.6054

DENVER, CO

Tel.: 877.440.2598
Fax: 877.205.7230

DALLAS, TX

Tel.: 800.442.6742
Fax: 800.848.6054

LONDON, UNITED KINGDOM

RELIABLE FIRE SPRINKLERS (UK) LTD
Tel.: +44.1342316800
Fax: +44.1342314679

P/N 9999970508 9/2017