

# F1-80 Series Standard-Response Sprinklers

K-factor 8.0 (115)

# **Features**

- Standard coverage standard-response sprinklers
- Upright and pendent orientations
- Low profile, compact design
- Available in a wide variety of finishes
- Available as Intermediate Level sprinklers

# **Product Description**

Reliable Model F1 series sprinklers are standard-response standard spray automatic fire sprinklers utilizing a 5mm glass bulb thermal element.

Pendent sprinklers may be installed exposed or surface mounted using escutcheons such as the Reliable Models B, C, or HB (reference Technical Bulletin 204). When installed recessed, the Model F1-80 series sprinklers are specifically listed with and may only be installed with listed Reliable recessed escutcheons. Refer to the technical information on the following pages for specific listings for recessed installations and refer to Figure 3 for dimensional information.

When fitted with an approved Reliable water shield, these sprinklers may considered intermediate sprinklers for use in racks, below grated walkways, and other areas where intermediate level sprinklers are required.

Table A provides a summary of the approvals and availability of specific Model F1 series sprinkler configurations. Additional technical information for each sprinkler model is provided on the following pages.



Model F1-80 Upright



Model F1-80 Pendent

**Note:** Not all versions of the product are shown.

| F1-80 Series Sprinkler Summary |  |                                 |                       |                    |   |
|--------------------------------|--|---------------------------------|-----------------------|--------------------|---|
| Sprinkler<br>Model             | K-Factor gpm/psi <sup>1/2</sup><br>(lpm/bar <sup>1/2</sup> ) | Max. Working Pressure psi (bar) | Listings & Approvals  | Orientation        | Sprinkler<br>Identification<br>Number (SIN) |
| F1-80                          | 8.0 (115)  | 175 (12)                        | cULus, FM, LPCB, VdS, | Upright<br>Pendent | RA6222                                      |
| 1 1-00                         | 0.0 (113)  | 250 (17) (cULus only)           | CE, UKCA              |                    | RA6212                                      |

# Model F1-80 Upright Sprinkler

**SIN RA6222** 

# **Technical Specifications**

Style: Upright

Threads: 3/4" NPT or ISO 7-R3/4 Nominal K-Factor: 8.0 (115) Max. Working Pressure:

175 psi (12 bar)

250 psi (17 bar) (cULus only)

#### **Material Specifications**

Thermal Sensor: 5mm Glass Bulb Sprinkler Frame: Brass Alloy

Cap: Bronze Alloy

Sealing Washer: Nickel with PTFE

Load Screw: Copper Alloy Deflector: Brass Alloy

# Sprinkler Finishes

(See Table B)

# Sensitivity

Standard response

# **Temperature Ratings**

135°F (57°C)

155°F (68°C)

175°F (79°C)

200°F (93°C)

286°F (141°Ć)

360°F (182°C)

#### **Guards & Shields**

F-1 Guard (cULus)

F-2 Guard (FM)

F-3 Guard with Shield (cULus, FM)

# **Sprinkler Wrenches**

Model W2

Model W14 (with guard installed)

# **Listings and Approvals**

cULus FM LPCB


VdS CE

UKCA: 0832-UKCA-CPR-S5076



# Model F1-80 Upright Sprinkler Components and Dimensions

Figure 1



Shown with Optional Factory Installed Water Shield (Intermediate Upright)

# Model F1-80 Pendent Sprinkler

# **SIN RA6212**

# **Technical Specifications**

Style:

Pendent

Recessed Pendent

Threads: 3/4" NPT or ISO 7-R3/4 Nominal K-Factor: 8.0 (115) Max. Working Pressure: 175 psi (12 bar)

250 psi (17 bar) (cULus only)

**Material Specifications** 

Thermal Sensor: 5mm Glass Bulb Sprinkler Frame: Brass Alloy

Cap: Bronze Alloy

Sealing Washer: Nickel with PTFE

**Load Screw:** Copper Alloy **Deflector:** Brass Alloy

#### **Sprinkler Finishes**

(See Table B)

# Sensitivity

Standard response

# Temperature Ratings(1)

135°F (57°C)

155°F (68°C)

175°F (79°C)

200°F (93°C)

286°F (141°C)

360°F (182°C)

#### **Recessed Escutcheons**

Model F1 (cULus)

Model F2 (cULus, FM)

Model FP (cULus)

#### Guards & Shields(2)

F-2 Guard (FM)

F-6 Guard/Shield Kit (FM)

F-7 Guard (cULus)

F-8 Guard/Shield Kit (cULus)

S-2 Shield (cUlus, FM)

### **Sprinkler Wrenches**

Model W2 (pendent)

Model W4 (recessed)

Model W14 (with guard installed)

# Listings and Approvals(3)

cULus Listed

FM Approved

LPCB

VdS

CE

UKCA: 0832-UKCA-CPR-S5077




### Notes:

- 1. 286°F (141°C) and higher temperature rated sprinklers not listed for recessed use.
- 2. Not suitable for use with recessed pendent installations.
- 3. When used surface mounted or exposed. See Recessed Escutcheon section for specific approvals when installed recessed.

# Model F1-80 Pendent Sprinkler Components and Dimensions


Figure 2




Shown with Optional S-1 Water Shield (Ordered Separately)

Note: Please refer to Figure 3 for recessed installation.





F1\_REC\_PEND



Models F1 & F1FR Pendent Sprinkler with Model FP Recessed Escutcheon 1/2" (13mm) Nominal Adjustment

Note: Model FP recessed assemblies may not be used where the pressure in the space above the ceiling is positive with respect to the protected area. Ensure that the openings in the Model FP cup are unobstructed following installation.







| Sprinkler and Escutcheon Finishes <sup>(1)</sup> |  |                               |  |  |  |  |
|--|--|-------------------------------|--|--|--|--|
| Standar  | d Finishes                               | Special Application Finishes  |  |  |  |  |
| Sprinkler  | F1, F2 and FP <sup>(2)</sup> Escutcheons | Sprinkler                     | F1, F2 and FP <sup>(2)</sup> Escutcheons |  |  |  |
| Bronze   | Brass                                    | Electroless Nickel PTFE(3)(4) | Bright Brass                             |  |  |  |
| Chrome Plated                                    | Chrome Plated                            | Bright Brass <sup>(5)</sup>   | Satin Chrome                             |  |  |  |
| White Polyester <sup>(3)</sup>                   | White Polyester                          | Satin Chrome                  | Custom Color Polyester                   |  |  |  |
|  |  | Custom Color Polyester(3)(6)  |  |  |  |  |
|  |  | Lead Plated <sup>(3)</sup>    |  |  |  |  |
|  |  | Wax Coated(3)(7)              |  |  |  |  |
|  |  | Wax Over Lead(3)(7)           |  |  |  |  |

#### Notes:

- Paint or any other coating applied over the factory finish will void all approvals and warranties. 1.
- 2. Model FP escutcheons utilize a galvanized steel cup with a finished trim ring.
- 3 cULus Listed as corrosion resistant.
- 4. FM Approved as corrosion resistant.
- 5. For 200°F (93°C) maximum temperature rated sprinklers only.
- 6. cULus only.
- Clear wax used on ordinary temperature rated sprinklers; brown wax used on intermediate temperature rated sprinklers. Brown wax may be used on high temperature rated sprinklers where the ambient temperature does not exceed 150°F (66°C).

# Installation

Model F1 Series sprinklers must be installed in accordance with NFPA13 and the requirements of all applicable authorities having jurisdiction. Model F1 Series sprinklers must be installed with the Reliable sprinkler installation wrench identified in this Bulletin. Any other wrench may damage the sprinkler. The Models W2 and W4 wrenches have two sets of jaws. Use the smallest set of jaws that fit on the wrench flats of the sprinkler. A leak tight sprinkler joint can be obtained with a torque of 8 to 18 lb-ft (11 to 24 N·m). Do not tighten sprinklers over the maximum recommended installation torque. Exceeding the maximum recommended installation torque may cause leakage or impairment of the sprinkler.

Glass bulb sprinklers have orange bulb protectors or protective caps to minimize bulb damage during shipping, handling and installation. Reliable sprinkler installation wrenches are designed to install sprinklers with bulb protectors in place. Remove the bulb protector at the time when the sprinkler system is placed in service for fire protection. Removal of the bulb protector before this time may leave the bulb vulnerable to damage. Remove bulb protectors by undoing the clasp by hand. Do not use tools to remove bulb protectors.

# Maintenance

Reliable Model F1 series sprinklers should be inspected and the sprinkler system maintained in accordance with NFPA 25, as well as the requirements of any Authorities Having Jurisdiction.

Prior to installation, sprinklers should remain in the original cartons and packaging until used. This will minimize the potential for damage to sprinklers that could cause improper operation or non-operation.

Do not clean sprinklers with soap and water, ammonia liquid or any other cleaning fluids. Remove dust by gentle vacuuming without touching the sprinkler.

Replace any sprinkler which has been painted (other than factory applied). A stock of spare sprinklers should be maintained to allow quick replacement of damaged or operated sprinklers. Failure to properly maintain sprinklers may result in inadvertent operation or non-operation during a fire event.



# Guarantee

For the guarantee, terms, and conditions, visit www. reliablesprinkler.com.

# **Ordering Information**

# Specify the following when ordering:

# Model

• F1-80

# **Deflector/Orientation**

- Upright
- Upright Intermediate
- Pendent

# **Temperature Rating**

• See sprinkler technical specifications

# Sprinkler Finish

See Table B

# **Recessed Escutcheon**

- F1
- F2
- FP

# **Escutcheon Finish**

See Table B

# **Sprinkler Wrench**

- Model W2 (upright and pendent)
- Model W4 (recessed)
- Model W14 (with guard installed)