

READY TO PROTECT FLAWLESS UNDER PRESSURE



HOME HYDRANT
TALCO FIRE SYSTEMS

U.S. PATENTS #8,678,032 & #8,905,069



EACH HOME HYDRANT®
FIRE PUMP SYSTEM IS
TESTED THOROUGHLY,
INCLUDES A PERFORMANCE
REPORT AND SHIPS
COMPLETELY ASSEMBLED.



MEETS IRC CODE
REQUIREMENTS
ALL ELECTRICAL
COMPONENTS SIT AT LEAST
18" OFF THE FLOOR.



NEW

Riser Drain &
Pump Bleeder
Valve

18"

- Auto Fill Valve
(not shown, on top of tank)
- Discharge Control Valve
- Test Valve
- Riser Support Bracket
- Pressure Gauge
- Pressure Switch
- Control Box w/
Run Timer
- Grooved Coupling
- NEW** Riser Drain
- NEW** Pump
Bleeder Valve
- Pump
- Suction Hose
- Suction Valve
- Tank Drain

Shown: HH3-150C


FIRE MARSHAL RECOMMENDED. SPRINKLER FITTER APPROVED.



HOME HYDRANT
TALCO FIRE SYSTEMS
U.S. PATENTS #8,678,032 & #8,905,069

Talco's Home Hydrant® is the most complete and compact residential fire pump system on the market.

WATER STORAGE TANK SIZES



HOME HYDRANT® UNITS - NFPA 13D

250, 350 or 450 Gallon Water Storage Tank


230 Volt, Single-Phase Electric Motor: 1.5 to 3HP

Discharge Manifold / Fire Riser components:

Check Valve • Pressure Switch • Pressure Gauge • Test Connection
System Drain • Pump Bleeder Valve • Flow Switch (optional)

MODEL	HH - 150SP	HH - 150C	HH - 300C
GPM	PSI	PSI	PSI
0 Churn	56	48	59
30	52	43	55
40	48	40	53
50	45	38	50
60	38	-	48

PUMP PERFORMANCE CURVES



TALCO
— FIRE SYSTEMS —

RESIDENTIAL & COMMERCIAL
FIRE PUMP SPECIALISTS

6040 NW 112th Avenue
Portland, Oregon 97220

1-800-878-8055
www.talcofire.com