

## Reliable Attic Sprinklers

- See Bulletin 056
- Specific Application
- Sprinklers for Sloped
- Combustible and Noncombustible
- Light Hazard Concealed Spaces



**AH42 / AH56**



**DD56-6 / DD56-27**



**DS56**



**GP56**



**DD80-6 / DD80-27**

1.800.431.1588  
 www.reliablesprinkler.com

Part Number	Short Code	Temperature		Finish	List Price
<b>MODEL AH42 UPRIGHT K4.2 (60) THREAD 1/2" RA5623 • Roof Slope = 4:12 to 8:12</b>					
MN21112699	AH42	212°F	100°C	Bronze	\$ 58.30
<b>MODEL AH56 UPRIGHT K5.6 (80) THREAD 1/2" RA5626 • Roof Slope = 4:12 to 8:12</b>					
MN21112799	AH56	212°F	100°C	Bronze	\$ 58.30
<b>MODEL DD56-6 UPRIGHT K5.6 (80) THREAD 1/2" RA5624 • Roof Slope = 4:12 to &lt;6:12</b>					
MN21113099	DD566	212°F	100°C	Bronze	\$ 316.09
<b>MODEL DD56-27 UPRIGHT K5.6 (80) THREAD 1/2" RA5694 • Roof Slope = 6:12 to 8:12</b>					
MN21113199	DD5627	212°F	100°C	Bronze	\$ 316.09
<b>MODEL DS56 UPRIGHT K5.6 (80) THREAD 1/2" RA5625 • Roof Slope = 4:12 to 8:12</b>					
MN21112899	DS56	212°F	100°C	Bronze	\$ 316.09
<b>MODEL GP56 UPRIGHT K5.6 (80) THREAD 1/2" RA5695 • Roof Slope = 4:12 to 8:12</b>					
MN21112999	GP56	212°F	100°C	Bronze	\$ 53.42
<b>MODEL DD80-6 UPRIGHT K8.0 (115) THREAD 3/4" RA5622 • Roof Slope = 4:12 to &lt;6:12</b>					
MN21113398	DD806	212°F	100°C	Bronze	\$ 316.09
<b>MODEL DD80-27 UPRIGHT K8.0 (115) THREAD 3/4" RA5692 • Roof Slope = 6:12 to 8:12</b>					
MN21113498	DD8027	212°F	100°C	Bronze	\$ 316.09

6880130002	WDS56	Model DS56 Sprinkler Wrench - Model DS56	\$ 202.23
6880050100	WW2	Model W2 Sprinkler Wrench - Models: AH42, AH56, DD56, DD80, & GP56	\$ 95.50

# NEW



### LT56 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb



### LT56L PENDENT

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Link

### LT56 300 PENDENT

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

### LT56L-300 PENDENT

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Link

Part Number	Short Code	Temperature		Finish	List Price
<b>MODEL LT56 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5814</b>					
BY15113299	LT56P1B	155°F	68°C	Bronze	\$ 56.18
BY15213299	LT56P1C	155°F	68°C	Chrome	\$ 61.79
BY15873299	LT56P1W	155°F	68°C	White	\$ 61.79
BY20113299	LT56P2B	200°F	93°C	Bronze	\$ 56.18
BY20213299	LT56P2C	200°F	93°C	Chrome	\$ 61.79
BY20873299	LT56P2W	200°F	93°C	White	\$ 61.79
<b>MODEL LT56L PENDENT K5.6 (80) THREADS 1/2" (15MM) R5814</b>					
MY16113299	LT56LP1B	165°F	74°C	Bronze	\$ 56.18
MY16213299	LT56LP1C	165°F	74°C	Chrome	\$ 61.79
MY16873299	LT56LP1PW	165°F	74°C	White	\$ 61.79
MY21113299	LT56LP2B	212°F	100°C	Bronze	\$ 56.18
MY21213299	LT56LP2C	212°F	100°C	Chrome	\$ 61.79
MY21873299	LT56LP2W	212°F	100°C	White	\$ 61.79
<b>MODEL LT56-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) RA5914</b>					
B015113299	LT56P1B3	155°F	68°C	Bronze	\$ 56.18
B015213299	LT56P1C3	155°F	68°C	Chrome	\$ 61.79
B015873299	LT56P1W3	155°F	68°C	White	\$ 61.79
B020113299	LT56P2B3	200°F	93°C	Bronze	\$ 56.18
B020213299	LT56P2C3	200°F	93°C	Chrome	\$ 61.79
B020873299	LT56P2W3	200°F	93°C	White	\$ 61.79
<b>MODEL LT56L-300 PENDENT K5.6 (80) THREADS 1/2" (15MM) R5914</b>					
M016113299	LT56LP1B3	165°F	74°C	Bronze	\$ 56.18
M016213299	LT56LP1C3	165°F	74°C	Chrome	\$ 61.79
M016873299	LT56LP1W3	165°F	74°C	White	\$ 61.79
M021113299	LT56LP2B3	212°F	100°C	Bronze	\$ 56.18
M021213299	LT56LP2C3	212°F	100°C	Chrome	\$ 61.79
M021873299	LT56LP2W3	212°F	100°C	White	\$ 61.79
<b>MODEL FV TWO-PIECE RECESSED ESCUTCHEONS &amp; COLLAR ASSEMBLY</b>					
6801720600	FVB	1/2" (15mm)		Bronze	\$ 16.70
6801722100	FVC	1/2" (15mm)		Chrome	\$ 11.13
6801728700	FVW	1/2" (15mm)		White	\$ 11.13
<b>MODEL FP TWO-PIECE RECESSED ESCUTCHEONS &amp; COLLAR ASSEMBLY</b>					
6801412100	FPC	1/2" (15mm)		Chrome	\$ 18.39
6801417200	FPW	1/2" (15mm)		White	\$ 18.39

6880050100	WW2	Pendent requires Model W2 Wrench	\$ 95.50
6880060000	WGFR	Recessed requires GFR2 Wrench	\$ 288.74



### LT56 CCP

- K-Factor = 5.6 (80)
- **SIN RA5814**
- See Bulletin 058
- Glass Bulb

### LT56L CCP

- K-Factor = 5.6 (80)
- **SIN R5814**
- See Bulletin 058
- Fusible Link

### LT56 300 CCP

- K-Factor = 5.6 (80)
- **SIN RA5914**
- See Bulletin 058
- Glass Bulb

### LT56L-300 CCP

- K-Factor = 5.6 (80)
- **SIN R5914**
- See Bulletin 058
- Fusible Link

Part Number	Short Code	Temperature		Finish	List Price
<b>MODEL LT56 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5814</b>					
BZ15173299	LT56C1	155°F	68°C	Bronze	\$ 67.41
BZ20173299	LT56C2	200°F	93°C	Bronze	\$ 67.41
<b>MODEL LT56-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5914</b>					
BI15173299	LT56C13	155°F	68°C	Bronze	\$ 67.41
BI20173299	LT56C23	200°F	93°C	Bronze	\$ 67.41
<b>MODEL LT56L CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5814</b>					
MZ16173299	LT56LC1	165°F	74°C	Bronze	\$ 67.41
MZ21173299	LT56LC2	212°F	100°C	Bronze	\$ 67.41
<b>MODEL LT56L-300 CCP CONCEALED K5.6 (80) THREADS 1/2" (15MM) R5914</b>					
MI16173299	LT56LC13	165°F	74°C	Bronze	\$ 67.41
MI21173299	LT56LC23	212°F	100°C	Bronze	\$ 67.41
<b>MODEL CCP CONICAL CONCEALED COVER PLATES</b>					
6887161321	CCP0C76	135°F	57°C	Chrome	\$ 78.48
6887161318	CCP0W76	135°F	57°C	White	\$ 30.58
6887161390	CCP0SP76	135°F	57°C	Specialty	\$ 51.36
6887161621	CCP1C76	165°F	74°C	Chrome	\$ 78.48
6887161618	CCP1W76	165°F	74°C	White	\$ 30.58
6887161690	CCP1SP76	165°F	74°C	Specialty	\$ 51.36
6880060000	WGFR	Concealed requires GFR2 Wrench			\$ 288.74



### LT56C FLAT CONCEALED

- K-Factor = 5.6 (80)
- **SIN RA5994**
- See Bulletin 058

Part Number	Short Code	Temperature		Finish	List Price
<b>MODEL LT56C CONCEALED K5.6 (80) THREADS 1/2" (15MM) RA5994</b>					
M916173299	LTC1	165°F	74°C	Bronze	\$ 78.65
M921173299	LTC2	212°F	100°C	Bronze	\$ 78.65
<b>MODEL LT56C CONCEALED BSPT THREADS 1/2" (15MM) RA5994</b>					
M916173292	LTC1M	165°F	74°C	Bronze	\$ 78.65
M921173292	LTC2M	212°F	100°C	Bronze	\$ 78.65
<b>MODEL G4 COVER PLATES</b>					
6887011321	CG40C	135°F	57°C	Chrome	\$ 33.75
6887011372	CG40W	135°F	57°C	White	\$ 33.75
6887011311	CG40B	135°F	57°C	Bronze	\$ 46.41
6887011374	CG40OW	135°F	57°C	Off-White	\$ 45.91
6887011390	CG40SP	135°F	57°C	Specialty	\$ 46.03
6887011316	CG40FB	135°F	57°C	Black Painted	\$ 45.97
6887011367	CG40BP	135°F	57°C	Black Plated	\$ 56.18
6887011305	CG40BB	135°F	57°C	Bright Brass	\$ 56.18
6887011323	CG40CD	135°F	57°C	Satin Chrome	\$ 56.18
6887011310	CG40SS	135°F	57°C	Stainless Steel	\$ 56.18
6887011621	CG41C	165°F	74°C	Chrome	\$ 33.75
6887011672	CG41W	165°F	74°C	White	\$ 33.75
6887011611	CG41B	165°F	74°C	Bronze	\$ 46.41
6887011674	CG41OW	165°F	74°C	Off-White	\$ 45.91
6887011690	CG41SP	165°F	74°C	Specialty	\$ 46.03
6887011616	CG41FB	165°F	74°C	Black Painted	\$ 45.91
6887011667	CG41BP	165°F	74°C	Black Plated	\$ 56.18
6887011605	CG41BB	165°F	74°C	Bright Brass	\$ 56.18
6887011623	CG41CD	165°F	74°C	Satin Chrome	\$ 56.18
6887011610	CG41SS	165°F	74°C	Stainless Steel	\$ 56.18
<b>MODEL G4 PERFORATED COVER PLATES</b>					
6887181321	CG40CP	135°F	57°C	Chrome	\$ 36.45
6887181372	CG40WP	135°F	57°C	White	\$ 36.45
6887181390	CG40SPP	135°F	57°C	Specialty	\$ 48.72
6887181621	CG41CP	165°F	74°C	Chrome	\$ 36.45
6887181672	CG41WP	165°F	74°C	White	\$ 36.45
6887181690	CG41SPP	165°F	74°C	Specialty	\$ 48.72

6880170020      WFC      Requires Model FC Wrench      \$ 287.62

**Notes:**

Sprinklers and coverplates sold and packaged separately



**F1S5 LO LARGE ORIFICE SPECIAL RESPONSE STANDARD SPRAY**

- K-Factor = 115 (8.0)
- Thread Size = R1/2
- Bulletin 024



Part Number	Short Code	Temperature	Finish	List Price
<b>MODEL F1S5 LO UPRIGHT K8.0( 115) THREADS 1/2"(15MM ) BSPT THREADS</b>				
KA13113492		135°F	57°C	Bronze \$ 30.85
KA15113492		155°F	68°C	Bronze \$ 30.85
KA17113492		175°F	79°C	Bronze \$ 30.85
KA20113492		200°F	93°C	Bronze \$ 30.85
KA28113492		286°F	141°C	Bronze \$ 30.85
KA13213492		135°F	57°C	Chrome \$ 36.01
KA15213492		155°F	68°C	Chrome \$ 36.01
KA17213492		175°F	79°C	Chrome \$ 36.01
KA20213492		200°F	93°C	Chrome \$ 36.01
KA28213492		286°F	141°C	Chrome \$ 36.01
<b>MODEL F1S5 LO PENDENT K8.0( 115) THREADS 1/2"(15MM ) BSPT THREADS</b>				
KB13113492		135°F	57°C	Bronze \$ 30.85
KB15113492		155°F	68°C	Bronze \$ 30.85
KB17113492		175°F	79°C	Bronze \$ 30.85
KB20113492		200°F	93°C	Bronze \$ 30.85
KB28113492		286°F	141°C	Bronze \$ 30.85
KB13213492		135°F	57°C	Chrome \$ 36.01
KB15213492		155°F	68°C	Chrome \$ 36.01
KB17213492		175°F	79°C	Chrome \$ 36.01
KB20213492		200°F	93°C	Chrome \$ 36.01
KB28213492		286°F	141°C	Chrome \$ 36.01
<b>F1 ESCUTCHEONS</b>				
6800630001	GF1B	15mm (1/2")	Bronze	\$ 17.68
6800600001	GF1C	15mm (1/2")	Chrome	\$ 9.54
6800640001	GF1W	15mm (1/2")	White	\$ 9.54
<b>F2 ESCUTCHEONS</b>				
6800830000	GF2B	15mm (1/2")	Bronze	\$ 17.68
6800800000	GF2C	15mm (1/2")	Chrome	\$ 9.54
6800840000	GF2W	15mm (1/2")	White	\$ 9.54
<b>FP PUSH-ON/THREADS-OFF ESCUTCHEONS</b>				
6801412100	FPC	FP PUSH-ON/THREADS-OFF	Chrome	\$ 18.39
6801417200	FPW	FP PUSH-ON/THREADS-OFF	White	\$ 18.39

6880050100	WW2	Requires Model W2 Sprinkler Wrench	\$ 95.50
6880060000	WGFR	Recessed Use Model GFR2 Sprinkler Wrench	\$ 288.74