Model REL-GV Globe Valve

200 psi (13.8 bar)

Product Description

Reliable Model REL-GV globe valves are intended for installation as trim or drain valves for fire protection equipment. The valves have a rated working pressure of 200 psi (13.8 bar) and feature a brass valve body with FNPT end connections.

Model REL-GV Globe Valve

Installation

The Reliable globe valves shall be installed in accordance with NFPA 13, “Standard for the Installation of Sprinkler Systems,” as well as the requirements of any authorities having jurisdiction. Verify compatibility of the valve materials with the water supply and the environment where the valve will be installed prior to installation.

WARNING: Model REL-GV globe valves contain lead and are not for use in systems carrying water intended for human consumption.

Maintenance

The owner is responsible for maintaining the fire protection system in proper operating condition. Any system maintenance or testing that involves placing a control valve out of service will eliminate the fire protection that is provided by the fire protection system.

The Reliable globe valve shall periodically be given a thorough inspection and test. NFPA 25, “Inspection, Testing and Maintenance of Water Based Fire Protection Systems,” provides minimum maintenance requirements. Inspect the valve for corrosion, damage, and wear as required and replace as necessary. Increase the frequency of inspections when the valve is exposed to corrosive conditions or chemicals that could impact the valve materials.

Guarantee

For Reliable Automatic Sprinkler Co., Inc. guarantee, terms, and conditions, visit www.reliablesprinkler.com.

Ordering Information

Specify the following when ordering:

Reliable Model REL-GV Globe Valve
Valve Size

- 3/8” (10 mm)
- 1/2” (15 mm)
- 3/4” (20 mm)
- 1” (25 mm)
- 1-1/4” (32 mm)
- 1-1/2” (40 mm)
- 2” (50 mm)

Model REL-GV Globe Valves

Technical Specifications
Pressure Rating:
200 psi (13.8 bar)

Material Specifications
Body: C37700 Brass Alloy
Bonnet: C37700 Brass Alloy
Seat: C37700 Brass Alloy
Stem: C37700 Brass Alloy
Stem Packing: PTFE
Seat Seal: EPDM Rubber

End Connections
Female NPT



Model REL-GV Globe Valve Dimensions

Figure 1



Dimensions in. (mm)

Table A

Valve Size	A	B	C
1/2 (15)	1-7/8 (48)	2-15/16 (75)	2-3/8 (60)
3/4 (19)	2-1/16 (53)	2-15/16 (75)	2-3/8 (60)
1 (25)	2-1/2 (63)	3-3/16 (80)	2-9/16 (65)
1-1/4 (32)	3 (77)	3-5/8 (92)	2-9/16 (65)
1-1/2 (40)	3-9/16 (84)	4-1/2 (114)	3-1/8 (80)
2 (50)	3-7/8 (99)	5-1/8 (130)	3-15/16 (100)