



Model 114 Welded Outlet Fitting

cULus Listed, FM Approved
300 psi (20.7 bar)

Model 114 Welded Outlet Fitting Technical Data

Operating Specifications
Maximum Working Pressure:
300 psi (20.7 bar)

Material Specifications
Weld O Let: Steel Pipe ASTM A53
Steel ASTM1008-1026

Design Specifications
Groove: AWWA-C606

Listings and Approvals:
cULus Listed ⁽³⁾
FM Approved ^(1, 2, 3)



Notes:

1. Size-on size (i.e. 2 x 2) Model 114 Welded Outlet Fittings are not FM Approved.
2. FM rated working pressure when welded on Schd. 5 or lightwall pipe is 175 psi.
3. Refer to the UL and FM Approval websites for the most current pressure ratings.

Model 114 Welded Outlet Fitting Dimensions

Figure 1




Table A

Nominal Outlet Size in (mm)	Nominal Run Size in (mm)	Outlet Length in (mm)	Inside Diameter in (mm)	Outside Diameter in (mm)	Wall Thickness in (mm)	Part Number
		A	B	C	D	
1-1/4 (32) x	1-1/2 (40)	1-1/2 (38)	1.368 (34.7)	1.660 (42.2)	0.140 (3.6)	6833600000
	2 - 2-1/2 (50 - 65)					6833600001
	3 - 4 (80 - 100)					6833600002