

CERTIFICATE OF COMPLIANCE

Certificate Number 20190107-EX3646
Report Reference EX3646-20040416
Issue Date 2019-JANUARY-07

Issued to: RELIABLE AUTOMATIC SPRINKLER CO INC
1470 SMITH GROVE RD
LIBERTY SC 29657

**This certificate confirms that
representative samples of**

RESIDENTIAL AUTOMATIC SPRINKLERS
See Following pages

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety: UL1626, Standard for Residential Sprinklers for Fire-
Protection Service
ULC/ORD C-1626-03, Other Recognized Document for
Residential Sprinklers for Fire-Protection Service

Additional Information: See the UL Online Certifications Directory at
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Mark. Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>




CERTIFICATE OF COMPLIANCE

Certificate Number 20190107-EX3646
Report Reference EX3646-20040416
Issue Date 2019-JANUARY-07

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

SIN RA0611, 1/2 in. NPT, K = 3.0, RA0612, 1/2 in. NPT, K = 4.3, SIN RA0616, 1/2 in. NPT, K = 4.9, and SIN RA0914, 1/2 in. NPT, K=5.6 concealed pendent, fusible solder link type heat responsive element with cover plates. SIN RA0613, 1/2 in. NPT, K = 5.8 and SIN RA0618, 3/4 in. NPT, K = 7.6 concealed pendent, fusible solder link type heat responsive element with cover plates. These sprinklers have a maximum pressure of 175 psig for wet systems only for spacings, flow rates and temperature ratings as indicated below:

Residential sprinklers for smooth flat ceilings.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/about/locations/>

