

Reliable®

Model F1 Residential Sprinklers for Design Density of .05 gpm/ft²

**Model F1 Res Sprinklers engineered for the lowest flows
to meet the minimum design density of .05 gpm/ft²**

Types:


1. F1 Res 30 Pendent
2. F1 Res 30 Recessed Pendent/F2
3. F1 Res 30 Recessed Pendent/FP
4. F1 Res 49 Pendent
5. F1 Res 49 Recessed Pendent/F1
6. F1 Res 49 Recessed Pendent/FP
7. F1 Res 58 Pendent
8. F1 Res 58 Recessed Pendent/F1
9. F1 Res 58 Recessed Pendent/FP
10. F1 Res 76 Pendent
11. F1 Res 76 Recessed Pendent/F1
12. F1 Res 76 Recessed Pendent/FP
13. F1 Res 30 CCP Pendent
14. F1 Res 49 CCP Pendent
15. F1 Res 58 CCP Pendent
16. F1 Res 76 CCP Pendent
17. F1 Res 44 HSW
18. F1 Res 44 Recessed HSW/F2
19. F1 Res 58 HSW
20. F1 Res 58 HSWX
21. KRes58 HSWX
22. F1 Res 58 HSW Recessed HSW/F2
23. F1 Res 44 SWC



F1 Res 30, 49, 58 & 76
Recessed Pendent / F1



F1 Res 30, 49, 58 & 76
Recessed Pendent / FP



F1 Res 58 HSWX



F1 Res 30, 49, 58 & 76
CCP Pendent



F1 Res 44 & 58
Recessed HSW/F2



F1 Res 44 SWC

Listings & Approvals

1. Listed by Underwriters Laboratories Inc. and UL Certified for Canada (cULus)

Sprinklers for .10 Density: Refer to Bulletin 176

UL Listing Category

Residential Automatic Sprinkler

UL Guide Number

VKKW

Patents

US Patent No. 6,516,893 applies to the Model F1 Res 49 & 58 Pendent Sprinklers

US Patent No. 7,353,882 applies to Model F1 Res 44 & 58 HSW Sprinklers

US Patent No. 7,784,555 applies to Model F1 Res 44 SWC Sprinklers

Product Description

Model F1 Res Pendent sprinklers (Figs. 1, 2, 3, & 4) are fast response sprinklers combining excellent durability, high sensitivity glass-bulb and low profile decorative design. The F1 Res

Horizontal Sidewall sprinklers (Figs. 5, 6 & 7) are equally attractive when above ceiling piping cannot be used.

The 3mm glass-bulb pendent sprinklers permit the efficient use of residential water supplies for sprinkler coverage in residential fire protection design.

The low flow F1 Res sprinklers are specially engineered for fast thermal response to meet the sensitive fire protection application needs of the latest residential market standards (UL 1626 Standard). Upon fire conditions, rising heat causes a sprinkler's heat-sensitive element, glass bulb or link to actuate, releasing the waterway for water flow onto the deflector, evenly distributing the discharged water to control a fire.

Technical Data:

- Thermal Sensor: Soldered Element (Link) or Nominal 3mm glass-bulb
- Sprinkler Frame : Brass Casting
- Sprinklers' Pressure Rating : 175 psi
Factory Hydrostatically Tested to 500 psi
- Thread Size: ½" NPT (R½)
- K-Factor: 3.0 (43.2) (Actual) - F1 Res 30 Pendent Sprinkler
4.9 (70.6) (Actual) - F1 Res 49 Pendent Sprinkler
5.8 (83.5) (Actual) - F1 Res 58 Pendent & HSW Sprinkler
7.6 (109)(Actual) - F1 Res 76 Pendent Sprinkler
4.4 (63) (Actual) - F1 Res 44 HSW Sprinkler
- Density: Minimum 0.05 gpm/ft²

Application

Model F1 Res Sprinklers are used for Residential Fire Protection according to UL 1626 Standard*. For ceiling types: Smooth Flat Horizontal, or beamed, or sloped, in accordance with NFPA 13D, 13R, or 13 2013 editions. Be sure that orifice size, temperature rating, deflector style and sprinkler type are in accordance with the latest published standards of The National Fire Protection Association or the approving authority having jurisdiction.

Installation

Models F1 Res sprinklers are to be installed as shown. Model F1, F2 and FP Escutcheons, illustrated herewith, are

the only recessed escutcheons to be used with Model F1 Res sprinklers. Use of any other recessed escutcheon will void all approvals and warranties. For installing Model F1 Res Pendant sprinklers use only the Model D sprinkler Wrench; for installing Models F1 Res Recessed Pendant, CCP & SWC sprinklers use only the Model GFR2 sprinkler wrench; for installing Model F1 Res Recessed HSW sprinklers use only the Model GFR2 Sprinkler Wrench. Use of wrenches other than those specified may damage these sprinklers. Install F1 Res 44 with a ceiling to deflector distance of 4" - 12". Flow arrow on deflector must point away from near wall and "Top" marking must face ceiling.

Escutcheon*, F1 or F2, Data:

Type	Adjustment Inch (mm)	"A" Inch (mm)	Face of fitting to ceiling Inch (mm)	"B" Deflector Distance below bottom of beam Inch (mm)
F1	3/4 (19.0)	Min. Recessed = 1 ⁵ / ₈ (41.3) Max. Recessed = 7/8 (22.2)	3/8 (9.5) 1 ¹ / ₈ (28.6)	1 ³ / ₄ (44.4) 1 (25.4)
F2	1/2 (12.7)	Min. Recessed = 1 ⁵ / ₈ (41.3) Max. Recessed = 1 ¹ / ₈ (28.6)	3/8 (9.5) 7/8 (22.2)	1 ³ / ₄ (44.4) 1 ¹ / ₄ (31.7)

* Note: Escutcheons F1 or F2 may be used with Model F1 Res 49, 58 & 76 Recessed Pendant Sprinkler

• Model F1 Res 30, 49, 58 & 76 Pendant



• Model F1 Res 30 Recessed Pendant / F2

• Model F1 Res 49, 58 & 76 Recessed Pendant / F1



F1 escutcheon, 3/4" (19mm) adjustment




Fig. 1




Fig. 2

Technical Data: F1Res 30 Pendant and Recessed Pendant (SIN R3511)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Sprinkler Temp. Rating		Max. Ambient Temp.		Actual K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
1/2" NPT (R1/2)	2 ¹ / ₆₄ " (8.2)	175 (12)	155 175	68 79	100	38	3.0 (43.2)	2.25 (57)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	8 (30,3)	7.0 (0,48)	8 (30,3)	7.0 (0,48)	Smooth Ceilings 1 ¹ / ₄ to 4 (31.7 to 102) using F2 escutcheon.	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	10 (37,8)	11 (0,76)	10 (37,8)	11 (0,76)	Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams 1 ¹ / ₄ to 1 ³ / ₄ (31.7 to 44.4) using F2 escutcheon	
16 x 16 (4,9 x 4,9)	16 (4,9)	13 (49)	18.8 (1,3)	13 (49)	18.8 (1,3)		

For Ceiling types refer to NFPA 13, 13R or 13D

Technical Data: F1Res 49 Pendent and Recessed Pendent (SIN R3516)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Sprinkler Temp. Rating		Max. Ambient Temp.		Actual K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
½" NPT (R½)	7/16" (11)	175 (12)	155 175	68 79	100 150	38 66	4.9 (70.6)	2.25 (57)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	13 (49)	7.0 (0,48)	13 (49)	7.0 (0,48)	Smooth Ceilings 1¼ to 4 (31.7 to 102) using F2 escutcheon. 1 to 4 (25.4 to 102) using F1 escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams 1¼ to 1¾ (31.7 to 44.4) using F2 escutcheon, 1 to 1¾ (25.4 to 44.4) using F1 escutcheon	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	13 (49)	7.0 (0,48)	13 (49)	7.0 (0,48)		
16 x 16 (4,9 x 4,9)	16 (4,9)	13 (49)	7.0 (0,48)	13 (49)	7.0 (0,48)		
18 x 18 (5,5 x 5,5)	18 (5,5)	17 (64,3)	12 (0,83)	17 (64,3)	12 (0,83)		
20 x 20 (6,1 x 6,1)	20 (6,1)	20 (75,7)	16.7 (1,14)	20 (75,7)	16.7 (1,14)		

For Ceiling types refer to NFPA 13, 13R or 13D

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	15 (57)	9.4 (0,65)	15 (57)	9.4 (0,65)	Smooth Ceilings 4 to 8 (100 to 203) using F2 escutcheon. 4 to 8 (100 to 203) using F1 escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams 4¼ to 8 (108 to 203) using F2 escutcheon, 4 to 8 (100 to 203) using F1 escutcheon	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	16 (60,5)	10.6 (0,73)	16 (60,5)	10.6 (0,73)		
16 x 16 (4,9 x 4,9)	16 (4,9)	17 (64,3)	12.0 (0,83)	17 (64,3)	12.0 (0,83)		
18 x 18 (5,5 x 5,5)	18 (5,5)	19 (72)	15.0 (1,0)	19 (72)	15.0 (1,0)		
20 x 20 (6,1 x 6,1)	20 (6,1)	22 (83,2)	20.2 (1,4)	22 (83,2)	20.2 (1,4)		

Technical Data: F1Res 58 Pendent and Recessed Pendent (SIN R3513)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Sprinkler Temp. Rating		Max. Ambient Temp.		Actual K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
½" NPT (R½)	½" (13)	175 (12)	155 175	68 79	100 150	38 66	5.8 (83.5)	2.25 (57)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	16 (61)	7.6 (0,53)	16 (61)	7.6 (0,53)	Smooth Ceilings 1¼ to 4 (31.7 to 102) using F2 escutcheon. 1 to 4 (25.4 to 102) using F1 escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams 1¼ to 1¾ (31.7 to 44.4) using F2 escutcheon, 1 to 1¾ (25.4 to 44.4) using F1 escutcheon	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	16 (61)	7.6 (0,53)	16 (61)	7.6 (0,53)		
16 x 16 (4,9 x 4,9)	16 (4,9)	16 (61)	7.6 (0,53)	16 (61)	7.6 (0,53)		
18 x 18 (5,5 x 5,5)	18 (5,5)	19 (72)	10.8 (0,75)	19 (72)	10.8 (0,75)		
20 x 20 (6,1 x 6,1)	20 (6,1)	22 (83,3)	14.4 (1,0)	22 (83,3)	14.4 (1,0)		

For Ceiling types refer to NFPA 13, 13R or 13D

Technical Data: F1 Res 76 Pendant and Recessed Pendant (SIN R7618)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Sprinkler Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
3/4" NPT (R3/4)	17/32" (13.5)	175 (12)	155	68	100	38	7.6 (109)	2.25 (57)
			175	79	150	66		

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	21 (79,5)	7.6 (0,53)	21 (79,5)	7.6 (0,53)	Smooth Ceilings 4¼ to 8 (108 to 203) using F2 escutcheon. 4 to 8 (100 to 203) using F1 escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams 4¼ to 8 (108 to 203) using F2 escutcheon. 4 to 8 (100 to 203) using F1 escutcheon	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	21 (79,5)	7.6 (0,53)	21 (79,5)	7.6 (0,53)		
16 x 16 (4,9 x 4,9)	16 (4,9)	21 (79,5)	7.6 (0,53)	21 (79,5)	7.6 (0,53)		
18 x 18 (5,5 x 5,5)	18 (5,5)	21 (79,5)	7.6 (0,53)	21 (79,5)	7.6 (0,53)		
20 x 20 (6,1 x 6,1)	20 (6,1)	23 (87,1)	9.2 (0,63)	23 (87,1)	9.2 (0,63)		


For Ceiling types refer to NFPA 13, 13R or 13D

• **Model F1 Res 30, 49, 58 & 76 CCP Pendant***



* Not listed for corrosion resistance.

• **Model F1 Res 30, 49, 58 & 76 Recessed Pendant / FP**



FP push-on/thread-off escutcheon




Fig. 3




Fig. 4

Note: The F1 Res 76 will use a 1" x 3/4" reducer.

CCP Cover Plate Data:

"A" Cover Adjustment Inch (mm)	"B" CCP Height Inch (mm)	"C" Deflector Distance below bottom of beam Inch (mm)
1/2 (12.7)	15/16 (24)	1/2 (13) - 1 (25.4)
5/16 (7.9)	3/4 (19)	1/2 (13) - 1 (25.4)

FP Escutcheon Data:

FP Position	"A" Inch (mm)	"B" Deflector Distance below bottom of beam Inch (mm)
Max. Recessed	7/16 (11)	1/2 (12.7)
Min. Recessed	15/16 (24)	1 (25.4)

Note: Sprinklers shown in Fig. 3 and Fig. 4 are not suitable for installation in ceilings which have positive pressure in the space above.

Technical Data: F1Res 30 CCP Pendant and Recessed Pendant/FP (SIN R3511)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	CCP Assembly Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
½" NPT (R½)	21/64" (8.2)	175 (12)	135	57	100	38	3.0 (43.2)	2.25 (57)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	8 (30,3)	7.0 (0,48)	Smooth Ceilings ½ to 1 (13 to 25.4) using CCP. ½ to 1 (13 to 25.4) using FP escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams ½ to 1 (13 to 25.4) using CCP. ½ to 1 (13 to 25.4) using FP escutcheon.	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	11 (37,8)	13.4 (0,92)		

For Ceiling types refer to NFPA 13, 13R or 13D

Technical Data: F1Res 49 CCP Pendant and Recessed Pendant/FP (SIN 3516)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	CCP Assembly Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
½" NPT (R½)	7/16" (11)	175 (12)	135	57	100	38	4.9 (70.6)	2.25 (57)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	13 (49)	7.0 (0,48)	Smooth Ceilings ½ to 1 (13 to 25.4) using CCP. ½ to 1 (13 to 25.4) using FP escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams ½ to 1 (13 to 25.4) using CCP. ½ to 1 (13 to 25.4) using FP escutcheon.	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	13 (49)	7.0 (0,48)		
16 x 16 (4,9 x 4,9)	16 (4,9)	14 (53)	8.2 (0,56)		
18 x 18 (5,5 x 5,5)	18 (5,5)	18 (68,1)	13.5 (0,93)		
20 x 20 (6,1 x 6,1)	20 (6,1)	20 (75,7)	16.7 (1,14)		

For Ceiling types refer to NFPA 13, 13R or 13D

Technical Data: F1Res 58 CCP Pendant and Recessed Pendant/FP (SIN R3513)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	CCP Assembly Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
½" NPT (R½)	½" (13)	175 (12)	135	57	100	38	5.8 (83.5)	2.25 (57)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	16 (61)	7.6 (0,53)	Smooth Ceilings ½ to 1 (13 to 25.4) using CCP. ½ to 1 (13 to 25.4) using FP escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams ½ to 1 (13 to 25.4) using CCP. ½ to 1 (13 to 25.4) using FP escutcheon.	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	16 (61)	7.6 (0,53)		
16 x 16 (4,9 x 4,9)	16 (4,9)	16 (61)	7.6 (0,53)		
18 x 18 (5,5 x 5,5)	18 (5,5)	19 (72)	10.8 (0,75)		
20 x 20 (6,1 x 6,1)	20 (6,1)	22 (83,3)	14.4 (1,0)		

For Ceiling types refer to NFPA 13, 13R or 13D

Technical Data: F1Res 76 CCP Pendant and Recessed Pendant/FP (SIN R7618)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	CCP Assembly Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
3/4" NPT (R3/4)	17/32" (13.5)	175 (12)	135	57	100 150	38 66	7.6 (109)	2.25 (57)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	21 (79,5)	7.6 (0,53)	Smooth Ceilings 1/2 to 1 (13 to 25.4) using CCP. 1/2 to 1 (13 to 25.4) using FP escutcheon. Beamed Ceilings per NFPA 13D, 13R or 13 installed in beams 1/2 to 1 (13 to 25.4) using CCP. 1/2 to 1 (13 to 25.4) using FP escutcheon.	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	21 (79,5)	7.6 (0,53)		
16 x 16 (4,9 x 4,9)	16 (4,9)	21 (79,5)	7.6 (0,53)		
18 x 18 (5,5 x 5,5)	18 (5,5)	22 (83,3)	8.4 (0,58)		
20 x 20 (6,1 x 6,1)	20 (6,1)	25 (94,6)	10.8 (0,74)		

For Ceiling types refer to NFPA 13, 13R or 13D





Fig. 5

• **Model F1 Res 44 & 58 HSW**



• **Model F1 Res 44 & 58 Recessed HSW/F2**



F2 escutcheon, 1/2" (13mm) adjustment

Technical Data: F1Res 44 HSW & HSW/F2 (SIN R3531)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Sprinkler Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
1/2" NPT (R1/2)	3/8" (10)	175 (12)	155 175	68 79	100 150	38 66	4.4 (63)	2.45 (62)

Escutcheon, F2, Data:

Type	Adjustment Inch (mm)	Face of Fitting to wall Inch (mm)
F2	1/2 (13)	3/16 - 11/16 (4.7 - 17.4)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	12 (45,4)	7.5 (0,52)	12 (45,4)	7.5 (0,52)	4 to 6 (100 to 152); ½ (13) recessed using F2 escutcheon	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	14 (53,0)	10.2 (0,71)	14 (53,0)	10.2 (0,71)		
16 x 16 (4,9 x 4,9)	16 (4,9)	16 (60,6)	13.3 (0,92)	16 (60,6)	13.3 (0,92)		
16 x 18 (4,9 x 5,5)	16 (4,9)	18 (68,1)	16.8 (1,16)	18 (68,1)	16.8 (1,16)		
18 x 18 (5,5 x 5,5)	18 (5,5)	19 (72,0)	18.7 (1,29)	19 (72,0)	18.7 (1,29)		
16 x 20 (4,9 x 6,1)	16 (4,9)	23 (87,1)	27.4 (1,89)	23 (87,1)	27.4 (1,89)		
12 x 12 (3,6 x 3,6)	12 (3,6)	14 (53,0)	10.2 (0,71)	14 (53,0)	10.2 (0,71)	6 to 12 (152 to 305); ½ (13) recessed using F2 escutcheon	
14 x 14 (4,3 x 4,3)	14 (4,3)	16 (60,6)	13.3 (0,92)	16 (60,6)	13.3 (0,92)		
16 x 16 (4,9 x 4,9)	16 (4,9)	17 (64,4)	15.0 (1,04)	17 (64,4)	15.0 (1,04)		
16 x 18 (4,9 x 5,5)	16 (4,9)	20 (75,7)	20.7 (1,43)	20 (75,7)	20.7 (1,43)		
16 x 20 (4,9 x 6,1)	16 (4,9)	23 (87,1)	27.4 (1,89)	23 (87,1)	27.4 (1,89)		

For Ceiling types refer to NFPA 13, 13R or 13D

Technical Data: F1Res 58 HSW & HSW/F2 (SIN R3533)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Sprinkler Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
½" NPT (R½)	½" (13)	175 (12)	155 175	68 79	100 150	38 66	5.8 (83.5)	2.45 (62)

Escutcheon, F2, Data:

Type	Adjustment Inch (mm)	Face of Fitting to wall Inch (mm)
F2	½ (13)	¾ ₁₆ - 1 ¹¹ / ₁₆ (4.7 - 17.4)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	16 (60,6)	7.6 (0,53)	16 (60,6)	7.6 (0,53)	4 to 6 (100 to 152); ½ (13) recessed using F2 escutcheon	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	18 (68,2)	9.7 (0,69)	18 (68,2)	9.7 (0,69)		
16 x 16 (4,9 x 4,9)	16 (4,9)	21 (79,5)	13.2 (0,91)	21 (79,5)	13.2 (0,91)		
16 x 18 (4,9 x 5,5)	16 (4,9)	25 (94,7)	18.6 (1,28)	25 (94,7)	18.6 (1,28)		
16 x 20 (4,9 x 6,1)	16 (4,9)	29 (109,8)	25.0 (1,73)	29 (109,8)	25.0 (1,73)		
12 x 12 (3,6 x 3,6)	12 (3,6)	22 (83,3)	14.4 (1,0)	22 (83,3)	14.4 (1,0)	6 to 12 (152 to 305); ½ (13) recessed using F2 escutcheon	
14 x 14 (4,3 x 4,3)	14 (4,3)	22 (83,3)	14.4 (1,0)	22 (83,3)	14.4 (1,0)		
16 x 16 (4,9 x 4,9)	16 (4,9)	26 (98,4)	20.1 (1,39)	26 (98,4)	20.1 (1,39)		
16 x 18 (4,9 x 5,5)	16 (4,9)	31 (117,4)	28.6 (1,97)	31 (117,4)	28.6 (1,97)		

For Ceiling types refer to NFPA 13, 13R or 13D

• **Model F1 Res 44 SWC***



* Not listed for corrosion resistance.




Fig. 6

Technical Data: F1Res 44 SWC (SIN R3531)

Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Cover Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)
			°F	°C	°F	°C		
1/2" NPT (R1/2)	3/8" (10)	175 (12)	135	57	100	38	4.4 (63)	2.45 (62)

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)		
12 x 12 (3,6 x 3,6)	12 (3,6)	13 (49,2)	8.7 (0,60)	4 to 6 (100 to 152); 1/2 (13) recessed using F2 escutcheon	8 (2,4)
14 x 14 (4,3 x 4,3)	14 (4,3)	14 (53,0)	10.2 (0,71)		
16 x 16 (4,9 x 4,9)	16 (4,9)	17 (64,3)	15.0 (1,1)		
16 x 18 (4,9 x 5,5)	16 (4,9)	19 (71,8)	18.7 (1,13)		
16 x 20 (4,9 x 6,1)	16 (4,9)	23 (87,1)	27.4 (1,89)		
12 x 12 (3,6 x 3,6)	12 (3,6)	14 (52,9)	10.2 (0,71)	6 to 12 (152 to 305); 1/2 (13) recessed using F2 escutcheon	
14 x 14 (4,3 x 4,3)	14 (4,3)	15 (56,7)	11.7 (0,81)		
16 x 16 (4,9 x 4,9)	16 (4,9)	18 (68,1)	16.8 (1,16)		
16 x 18 (4,9 x 5,5)	16 (4,9)	20 (75,6)	20.7 (1,43)		

For Ceiling types refer to NFPA 13, 13R or 13D

Technical Data: F1Res 58 HSWX (SIN RA3533)

	Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Sprinkler Temp. Rating		Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)	Sprinkler Identification Number (SIN)
				°F	°C	°F	°C			
Bulb	½" NPT (R½)	½" (13)	175 (12)	155 175	68 79	100 150	38 66	5.8 (83.5)	2.45 (62)	RA3533

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (155°F/68°C)		Intermediate Temp. Rating (175°F/79°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)	Flow GPM (L/min)	Pressure PSI (bar)		
18 x 20 (5,5 x 6,1)	18 (5,5)	30 (114)	26.8 (1,85)	30 (114)	26.8 (1,85)	4 to 6 (100 to 152); ½ (13) recessed using F2 escutcheon	8 (2,4)
20 x 20 (6,1 x 6,1)	20 (6,1)	30 (114)	26.8 (1,85)	30 (114)	26.8 (1,85)		
16 x 22 (4,9 x 6,7)	16 (4,9)	33 (125)	32.4 (2,23)	33 (125)	32.4 (2,23)		
16 x 24 (4,9 x 7,3)	16 (4,9)	38 (144)	42.9 (2,96)	38 (144)	42.9 (2,96)		
14 x 26 (4,3 x 7,9)	14 (4,3)	42 (160)	52.4 (3,75)	42 (160)	52.4 (3,75)		
18 x 20 (5,5 x 6,1)	18 (5,5)	35 (133)	36.4 (2,5)	35 (133)	36.4 (2,5)	6 to 12 (152 to 305); ½ (13) recessed using F2 escutcheon	
16 x 22 (4,9 x 6,7)	16 (4,9)	38 (144)	42.9 (2,96)	38 (144)	42.9 (2,96)		
16 x 24 (4,9 x 7,3)	16 (4,9)	42 (160)	52.4 (3,6)	42 (160)	52.4 (3,6)		
14 x 26 (4,3 x 7,9)	14 (4,3)	46 (174)	62.9 (4,34)	46 (174)	62.9 (4,34)		

For Ceiling types refer to NFPA 13, 13R or 13D






Fig. 7

- **Model F1 Res 58 HSWX (Bulb)**



- **Model KRes58 HSWX (Link)**



Technical Data: KRes58 HSWX (RA3593)

	Thread Size	Nominal Orifice Inch (mm)	Max. Pressure psi (bar)	Max. Ambient Temp.		K Factor	Sprinkler Length Inch (mm)	Sprinkler Identification Number (SIN)
				°F	°C			
Link	½" NPT (R½)	½" (13)	175 (12)	100	38	5.8 (83.5)	2.45 (62)	RA3593

Max. Coverage area Ft x Ft (m x m)	Max. Spacing Ft (m)	Ordinary Temp. Rating (165°F/74°C)		Top of Deflector to Ceiling Inch (mm)	Minimum Spacing Ft (m)
		Flow GPM (L/min)	Pressure PSI (bar)		
18 x 20 (5,5 x 6,1)	18 (5,5)	29 (109)	25 (1,72)	4 to 6 (100 to 152); ½ (13) recessed using F2 escutcheon	8 (2,4)
20 x 20 (6,1 x 6,1)	20 (6,1)	30 (114)	26.8 (1,85)		
16 x 22 (4,9 x 7,3)	16 (4,9)	33 (125)	32.4 (2,23)		
16 x 24 (4,9 x 7,3)	16 (4,9)	38 (144)	42.9 (2,96)		
14 x 26 (4,3 x 7,9)	14 (4,3)	42 (160)	52.4 (3,75)		
18 x 20 (5,5 x 6,1)	18 (5,5)	35 (133)	36.4 (2,5)	6 to 12 (152 to 305); ½ (13) Recessed using F2 escutcheon	
16 x 22 (4,9 x 6,7)	16 (4,9)	38 (144)	42.9 (2,96)		
16 x 24 (4,9 x 7,3)	16 (4,9)	42 (160)	52.4 (3,6)		
14 x 26 (4,3 x 7,9)	14 (4,3)	46 (174)	62.9 (4,34)		

For Ceiling types refer to NFPA 13, 13R or 13D

Maintenance

Model F1 Res 30, 49, F1 Res 58, F1 Res 76 and F1 Res 44 Sprinklers should be inspected and the sprinkler system maintained in accordance with NFPA 25, 13, 13D, and 13R. Do not clean sprinkler with soap and water, Ammonia or any other cleaning fluids. Remove dust by using a soft brush or gentle vacuuming. Remove any sprinkler which has been painted (other than factory applied) or damaged in any way. A stock of spare sprinklers should be maintained to allow quick replacement of damaged or operated sprinklers. Prior to installation, sprinklers should remain in the original cartons and packaging until used. This will minimize the potential for damage to sprinklers that could cause improper operation or non-operation.

Model F1 Res 30, 49 & 58 Pendent Sprinkler Specifications

Sprinklers shall be [cULus Listed] [New York City MEA Approved (258-93-E)] low flow residential pendent sprinklers engineered to provide a minimum design density of 0.05 gpm/ft² over the listed coverage area. Listed flows as specified by the manufacturer's technical data sheets are to be used. Residential sprinklers shall be installed in conformance with the manufacturer's installation guidelines and the applicable installation standard. Deflector-to-ceiling distance listing shall be 1" to 8" maximum, only for F1Res 49. Sprinkler frame and deflector shall be of bronze frame construction having a ½" NPT thread. Wa-

ter seal assembly shall consist of a Teflon* coated Belleville spring washer with top-loaded extruded or cold head cup with 3 mm glass bulb containing no plastic parts, and having a temperature rating of [155°F (68°C)] [175°F (79°C)]. Sprinklers shall have a nominal K-factor of 3.0, 4.9 and 5.8. Standard finish: [Bronze] [Chrome-plated] [White Polyester] [Special finish- specify]. Residential pendent sprinklers shall be Reliable Model F1 Res 30, 49 & 58, SIN R3511, R3516 & R3513 (Bulletin 135).

Model F1 Res 49 & 58 Recessed Pendent/F1, Model F1 Res 30, 49 & 58 Recessed Pendent/F2, Model F1 Res 30, 49 & 58 Recessed Pendent/FP

Sprinklers shall be [cULus Listed] [New York City MEA Approved (258-93-E)] low flow residential recessed pendent sprinklers engineered to provide a minimum design density of 0.05 gpm/ft² over the listed coverage area. Listed flows as specified by the manufacturer's technical data sheets are to be used. Residential sprinklers shall be installed in conformance with the manufacturer's installation guidelines and the applicable installation standard. Deflector-to-ceiling distance listing shall be 1" to 8" maximum, only for F1Res 49. Sprinkler frame and deflector shall be of bronze frame construction having a ½" NPT thread. Water seal assembly shall consist of a Teflon* coated Belleville spring washer with top-loaded extruded

*DuPont Registered Trademark

or cold head cup with 3 mm glass bulb containing no plastic parts, and having a temperature rating of [155°F (68°C)] [175°F (79°C)]. Sprinklers shall have a nominal K-factor of 3.0, 4.9 & 5.8. Standard finish: [Bronze] [Chrome-plated] [White Polyester] [Special finish– specify]. Recessed escutcheon assembly shall be a steel, two-piece escutcheon [with ½” adjustment (Model F2)] [with ¾” adjustment (Model F1)] [of push-on and thread off design with ½” adjustment (Model FP)]. Standard finish shall be [brass][bright chrome] [white painted]. Residential recessed pendent sprinklers shall be Reliable [Model F1 Res 30, 49 & 58 Recessed Pendent/F1] [Model F1 Res 30, 49 & 58 Recessed Pendent/F2] [Model F1 Res 30, 49 & 58 Recessed Pendent/FP] SIN R3511, R3516 & R3513 (Bulletin 135).

Model F1 Res 30, 49 & 58 CCP Pendent (Concealed)

Sprinklers shall be [cULus Listed] [New York City MEA Approved (258-93-E)] low flow residential concealed sprinklers engineered to provide a minimum design density of 0.05 gpm/ft² over the listed coverage area. Listed flows as specified by the manufacturer’s technical data sheets are to be used. Residential sprinklers shall be installed in conformance with the manufacturer’s installation guidelines and the applicable installation standard. Sprinkler frame and deflector shall be of bronze frame construction having a ½” NPT thread. Water seal assembly shall consist of a Teflon* coated Belleville spring washer with top-loaded extruded or cold head cup with 3 mm glass bulb containing no plastic parts, and having a temperature rating of 155°F (68°C). Cover plate assembly shall consist of a brass cover plate and copper alloy retainer flange. Method of attaching the cover plate to the sprinkler cup shall be a push-on and thread-off design allowing a ½” cover plate adjustment. Cover plate temperature rating shall be 135°F (57°C). A plastic protective cap shall be provided and factory installed inside the sprinkler cup to protect the sprinkler from damage, which could occur during construction before the cover plate is installed. Standard cover plate finish: [White] [Custom Color– specify]. Concealed pendent sprinklers shall be Reliable Model F1 Res 30, 49 & 58 CCP, SIN R3511, R3516 & R3513 (Bulletin 135).

Model F1 Res 44, F1 Res 58 Horizontal Sidewall, F1 Res 58 HSWX & KRes58 HSWX Residential Sprinkler Specifications

Sprinklers shall be [cULus Listed] low flow residential horizontal sidewall sprinklers engineered to provide a minimum design density of 0.05 gpm/ft² over the listed coverage area. Listed flows as specified by the manufacturer’s technical data sheets are to be used. Residential sprinklers shall be installed in conformance with the manufacturer’s installation guidelines and the applicable installation standard. Sprinkler frame and deflector shall be of bronze frame construction having a ½” NPT thread. Water seal assembly shall consist of a Teflon* coated Bel-

leville spring washer with top-loaded extruded or cold head cup with 3 mm glass bulb containing no plastic parts, and having a temperature rating of [155°F (68°C)] [175°F (79°C)]. The solder element (Link) version, the water seal consist of a cap with a bellville spring washer and a temperature rating of 165°F (74°C). The recessed assembly for the HSWX (Bulb & Link) should be a steel two pieces escutcheon with 1/2” adjustment (Model F2) standard finish should be Bright Chrome and white painted. The F1 Res 58 HSW is also available with low lead frame. F1 Res 58 HSW and HSWX sprinklers shall have a nominal K Factor of 5.8 and F1 Res 44 a nominal K factor of 4.4. Standard finish: [Bronze] [Chrome-plated] [White Polyester] [Special finish– specify]. Residential horizontal sidewall sprinklers shall be Reliable Model F1 Res 44, F1 Res 58, F1 Res 58 HSWX & Model KRes58 HSWX, SIN R3531, RA3533 & RA3593 (Bulletin 135).

Model F1 Res 44 Recessed Horizontal Sidewall Sprinkler

Use description for the Model F1 Res 44 horizontal sidewall sprinkler with the following modifications: Replace “horizontal sidewall sprinkler” with “recessed horizontal sprinkler.” Add: Recessed escutcheon assembly shall be a steel, two-piece escutcheon with ½” adjustment (Model F2). Standard finish shall be [brass][bright chrome] [white painted] [Special finish– specify]. Residential recessed horizontal sidewall sprinklers shall be Reliable Model F1 Res 44/F2, SIN R3531 (Bulletin 135).

Model F1 Res 76 Pendent

Sprinklers shall be [cULus Listed] low flow residential pendent sprinklers engineered to provide a minimum design density of 0.05 gpm/ft² over the listed coverage area. Listed flows as specified by the manufacturer’s technical data sheets are to be used. Residential sprinklers shall be installed in conformance with the manufacturer’s installation guidelines and the applicable installation standard. Sprinkler frame and deflector shall be of bronze frame construction having a ¾” NPT thread. Water seal assembly shall consist of a Teflon* coated Belleville spring washer with machined or cold head cup with 3 mm glass bulb containing no plastic parts, and having a temperature rating of [155°F (68°C)] [175°F (79°C)]. Sprinklers shall have a nominal K-factor of 7.6. Standard finish: [Bronze] [Chrome-plated] [White Polyester] [Special finish– specify]. Residential pendent sprinklers shall be Reliable Model F1 Res 76, SIN R7618 (Bulletin 135).

*DuPont Registered Trademark

**Model F1 Res 76 Recessed Pendent/F1,
Model F1 Res 76 Recessed Pendent/F2,
Model F1 Res 76 Recessed Pendent/FP**

Sprinklers shall be [cULus Listed] low flow residential recessed pendent sprinklers engineered to provide a minimum design density of 0.05 gpm/ft² over the listed coverage area. Listed flows as specified by the manufacturer's technical data sheets are to be used. Residential sprinklers shall be installed in conformance with the manufacturer's installation guidelines and the applicable installation standard. Sprinkler frame and deflector shall be of bronze frame construction having a 3/4" NPT thread. Water seal assembly shall consist of a Teflon* coated Belleville spring washer with machined or cold head cup with 3 mm glass bulb containing no plastic parts, and having a temperature rating of [155°F (68°C)] [175°F (79°C)]. Sprinklers shall have a nominal K-factor of 7.6. Standard finish: [Bronze] [Chrome-plated] [White Polyester] [Special finish- specify]. Recessed escutcheon assembly shall be a steel, two-piece escutcheon [with 1/2" adjustment (Model F2)] [with 3/4" adjustment (Model F1)] [of push-on and thread off design with 1/2" adjustment (Model FP)]. Standard finish shall be [brass][bright chrome] [white painted]. Residential recessed pendent sprinklers shall be Reliable [Model F1 Res 76 Recessed Pendent/F1] [Model F1 Res 76 Recessed Pendent/F2] [Model F1 Res 76 Recessed Pendent/FP] SIN R7618 (Bulletin 135).

Model F1 Res 76 CCP Pendent (Concealed)

Sprinklers shall be [cULus Listed] low flow residential concealed sprinklers engineered to provide a minimum design density of 0.05 gpm/ft² over the listed coverage area. Listed flows as specified by the manufacturer's technical data sheets are to be used. Residential sprinklers shall be installed in conformance with the manufacturer's installation guidelines and the applicable installation standard. Sprinkler frame and deflector shall be of bronze frame construction having a 3/4" NPT thread. Water seal assembly shall consist of a Teflon* coated Belleville spring washer with machined or cold head cup with 3 mm glass bulb containing no plastic parts, and having

a temperature rating of 155°F (68°C). Cover plate assembly shall consist of a brass cover plate and copper alloy retainer flange. Method of attaching the cover plate to the sprinkler cup shall be a push-on and thread-off design allowing a 1/2" cover plate adjustment. Cover plate temperature rating shall be 135°F (57°C). A plastic protective cap shall be provided and factory installed inside the sprinkler cup to protect the sprinkler from damage, which could occur during construction before the cover plate is installed. Standard cover plate finish: [White] [Custom Color- specify]. Concealed pendent sprinklers shall be Reliable Model F1 Res 76 CCP, SIN R7618 (Bulletin 135).

Finishes ⁽¹⁾

Standard Finishes		
Sprinkler	F1, F2, FP Escutcheons	Cover Plates
Bronze Chrome Plated White and Black Polyester ⁽²⁾ Coated	Brass Bright Chrome Plated White Painted	White Painted Chrome

Special Application Finishes	
Sprinkler	F1, F2, FP Escutcheons
Electroless Nickel PTFE(Teflon [®]) ⁽²⁾ Bright Brass Black Plated Black Paint Off White Chrome Dull	Electroless Nickel PTFE (Teflon [®]) Bright Brass Black Plated Black Paint Off White Chrome Dull

⁽¹⁾ Other finishes and colors are available on special order.

Consult factory for details.

⁽²⁾ cULus listed Corrosion Resistant

Note: Paint or any other coating applied over the factory finish will void all approvals and warranties.

Ordering Information

Specify:

1. Sprinkler Model
2. Sprinkler Type
3. Temperature Rating
4. Sprinkler Finish
5. Escutcheon Finish
6. Cover Plate Finish

*DuPont Registered Trademark

The equipment presented in this bulletin is to be installed in accordance with the latest published Standards of the National Fire Protection Association, Factory Mutual Research Corporation, or other similar organizations and also with the provisions of governmental codes or ordinances whenever applicable.

Products manufactured and distributed by Reliable have been protecting life and property for over 90 years, and are installed and serviced by the most highly qualified and reputable sprinkler contractors located throughout the United States, Canada and foreign countries.

Manufactured by



Reliable Automatic Sprinkler Co., Inc.

(800) 431-1588

(800) 848-6051

(914) 829-2042

www.reliablesprinkler.com

Sales Offices

Sales Fax

Corporate Offices

Internet Address



Recycled Paper

Revision lines indicate updated or new data.