



## Model J168 Standard Response Upright Sprinkler (SIN RA1124)

**Note:** This sprinkler is a UL Listed Control Mode Density Area sprinkler.

### Features

1. Utilizes Standard Response center strut solder sensor.
2. 165 °F (74 °C), 212 °F (100 °C) and 286 °F (141 °C) temperature ratings.
3. Available in brass, lead coated, wax coated and wax over lead coated finishes.
4. Provides higher flows at much lower pressures for all occupancies, especially in high density applications, such as the protection of high-piled storage.
5. Limits density increases for plastic pallet applications per NFPA 13.

### Listings and Approvals

1. Listed by Underwriters Laboratories Inc. and UL certified for Canada (cULus) to include storage applications.
2. NYC MEA 258-93-E
3. FM Approved as a storage sprinkler.

### Technical Data

#### Applications

Wet, Dry and Pre-Action Sprinkler Systems

#### Hazards

Ordinary, Extra Hazard and Storage

Occupancies per NFPA 13

For Sprinkler Spacing, Positioning and Density/Area Flow Calculations: refer to NFPA 13

#### Minimum Working Pressure

7 psi (0.5 bar) residual (flowing)

#### Maximum Working Pressure

Rated 175 psi (12.1 bar)

Factory tested to 500 psi (34,5 bar)

#### Discharge Coefficients (K-Factor)

$K=16.8 \text{ gpm/psi}^{1/2}$  (242 lpm/bar)<sup>1/2</sup>

#### Pipe Thread Connection

3/4 NPT (R3/4)

#### Overall Length

31/8" (79.4 mm)

Refer to CA-167



Sprinkler Identification Number RA1124

### Product Description

The Reliable Model J168 Automatic sprinkler utilizes the center strut solder in compression principle of construction. The fusible alloy is captured in the cylinder of the solder capsule by a stainless steel ball. When the fusible alloy melts, the ball moves into the cylinder allowing the cylinder to separate from the center strut. When this happens, the lever is released to spring free from the sprinkler so that all operating parts clear the waterway allowing the deflector to distribute the discharging water in a hemispherical pattern.

The Reliable Model J168, 16.8 K-Factor sprinklers were tested in full scale fire tests to qualify them for the protection of rack and high piled storage.

### Availability and Service

Reliable products are available through an extensive network of domestic and international distributors. See the Reliable Web site at [www.reliablesprinkler.com](http://www.reliablesprinkler.com) for additional information.

### Ordering Information

#### Specify:

Model J168 Upright

Temperature rating (see page 2)

Finish (see page 2)

Model J1 Installation Wrench



Model J1 Sprinkler Wrench

## Design Criteria

### FM Approval Requirements

The Reliable Standard Response standard spray J168, K-16.8 Upright Sprinkler is approved to be installed in accordance with FM Data Sheets 8-9 and 2-0. (FM guidelines may be different from UL and C-UL Listing criteria).

### cULus Listing Requirements

The Reliable Standard Response J168 Upright Sprinkler is cULus Listed for use in occupancy classifications up to and including Extra-Hazard, for hydraulically calculated wet or dry systems per NFPA 13, with a minimum operating pressure of 7 psi (48.3 kPa) in wet or dry systems. Use the standard sprinkler positioning requirements and density/area sprinkler protection criteria provided in NFPA 13.

### Also:

The J168 Sprinkler is cULus Listed for use in High-Piled Storage Occupancies as defined in NFPA 13. This sprinkler may be used for the protection of solid piled, palletized, rack storage (single, double, multiple-row and portable), bin box and shelf storage including, but not limited to: encapsulated or unencapsulated Class I-IV and Group A or B plastics, cartoned, expanded or unexpanded, as well as exposed unexpanded. For hydraulically calculated wet or dry systems per NFPA 13 with a minimum operating pressure of 7 psi (0.5 bar). Use the standard sprinkler positioning requirements and density/area sprinkler protection criteria provided in NFPA 13 for High-Piled Storage Occupancies.

Refer to NFPA 13 for specific requirements for various combinations of building heights, storage heights, sprinkler-to-commodity clearance, storage arrangements, commodity classifications and lesser or greater required design densities.

**Note:** The J168 Sprinkler can be used in any application or building height as allowed by NFPA13 or FM guidelines. The J168 is a standard response standard spray sprinkler with a larger K-Factor to provide greater water flows at lower pressures.

## Temperature Ratings

Classification	Sprinkler Rating		Maximum Ambient Temperature		Frame Color
	°F	°C	°F	°C	
Ordinary	165	74	100	38	Uncolored White Blue
Intermediate	212	100	150	66	
High	286	141	225	107	

Special Application Finishes	
Lead Plated	165 °F (74 °C), 212 °F (100 °C) and 286 °F (141 °C)
Wax-Coated <sup>(1)(2)</sup>	Temp. Ratings 165 °F (74 °C) Clear Wax, 212 °F (100 °C) Brown Wax.
Wax-Coated Over Lead Plated <sup>(1)(2)</sup>	165 °F (74 °C) Clear Wax, 212 °F (100 °C) Brown Wax.

<sup>(1)</sup> 212 °F (100 °C) brown wax may be used on 286 °F (141 °C) sprinklers when maximum ambient temperatures do not exceed 150 °F (66 °C).

<sup>(2)</sup> Not FM Approved.

**Caution:** The Reliable Standard Response J168 Upright Sprinkler must be installed and maintained per the application NFPA standards, as well as the standards of other authorities having jurisdiction.

## Installation

The Model J168 Upright Sprinklers are to be installed as follows:

- Install in upright position only.
- Apply pipe thread sealant to NPT threads, hand tighten into the sprinkler fitting.
- Install sprinkler by wrench boss only.
- Wrench tighten with the dedicated J1 Sprinkler Wrench.
- A leak tight  $\frac{3}{4}$  NPT ( $R\frac{3}{4}$ ) sprinkler joint can be obtained with a torque of 14-20 ft-lb
- Higher torques may compromise the seal or function integrity of the sprinkler.

## Maintenance

Model J168 Sprinklers should be inspected and the sprinkler system maintained in accordance with NFPA 25. Do not clean sprinklers with soap and water, ammonia or any other cleaning fluids. Remove dust by using a soft brush or gentle vacuuming. Remove any sprinkler that had been painted (other than factory applied) or damaged in any way. A stock of spare sprinklers should be maintained to allow quick replacement of damaged or operated sprinklers. Prior to installation, sprinklers should be maintained in the original cartons and packaging until used to minimize the potential for damage to sprinklers that would cause improper operation or non-activation.


## Model J168 Standard Response Upright Sprinkler

Sprinklers shall be standard response upright spray sprinklers cULus Listed for use in occupancy classifications up to and including extra hazard and for storage occupancies in accordance with NFPA 13. Sprinkler construction shall be a bronze, die-cast frame with grooved wrench flat and copper-alloy deflector. Water seal assembly shall consist of a fusible solder thermal element utilizing a center strut solder-in-compression principle of construction with metal Belleville spring washer, coated on both sides with Teflon film. Sprinkler temperature rating shall be [165 °F (74 °C)] [212 °F (100 °C)] [286 °F (141 °C)]. Sprinklers shall have a nominal K-Factor of 16.8 (241.9) and have a  $\frac{3}{4}$ " NPT (R) thread. The rated working pressure shall be 175 psi (12.1 bar). Standard finish shall be bronze. Sprinklers shall be Reliable Model J168 standard response upright sprinklers, Bulletin 011 (SIN RA1124).

## Special Application Finishes Option

Exposed sprinklers subject to corrosive atmospheres shall have a factory-applied [165 °F (74 °C) clear wax-coated] [212 °F (100 °C) brown wax-coated] [lead plated for 165 °F (74 °C), 212 °F (100 °C), or 286 °F (141 °C)] [wax-coated over lead plated] corrosion resistant coating.

## Engineering Specification



### Notes:

- (1) Grooved sprinkler boss provided to insure that the Sprinkler wrench does not slip during installation.
- (2) A tight  $\frac{3}{4}$ " NPT sprinkler joint should be obtained with a torque of 14 to 20 ft-lb Higher levels of torque may distort the sprinkler inlet cause leakage or impairment.

# Reliable... For Complete Protection

Reliable offers a wide selection of sprinkler components. Following are some of the many precision-made Reliable products that guard life and property from fire around the clock.

- Automatic sprinklers
- Flush automatic sprinklers
- Recessed automatic sprinklers
- Concealed automatic sprinklers
- Adjustable automatic sprinklers
- Dry automatic sprinklers
- Intermediate level sprinklers
- Open sprinklers
- Spray nozzles
- Alarm valves
- Retarding chambers
- Dry pipe valves
- Accelerators for dry pipe valves
- Mechanical sprinkler alarms
- Electrical sprinkler alarm switches
- Water flow detectors
- Deluge valves
- Detector check valves
- Check valves
- Electrical system
- Sprinkler emergency cabinets
- Sprinkler wrenches
- Sprinkler escutcheons and guards
- Inspectors test connections
- Sight drains
- Ball drips and drum drips
- Control valve seals
- Air maintenance devices
- Air compressors
- Pressure gauges
- Identification signs
- Fire department connection

---

The equipment presented in this bulletin is to be installed in accordance with the latest published Standards of the National Fire Protection Association, Factory Mutual Research Corporation, or other similar organizations and also with the provisions of governmental codes or ordinances whenever applicable. Products manufactured and distributed by Reliable have been protecting life and property for over 90 years, and are installed and serviced by the most highly qualified and reputable sprinkler contractors located throughout the United States, Canada and foreign countries.

---

Manufactured by

**Reliable**<sup>®</sup>

**The Reliable Automatic Sprinkler Co., Inc.**

(800) 431-1588

(800) 848-6051

(914) 829-2042

[www.reliablesprinkler.com](http://www.reliablesprinkler.com)

Sales Offices

Sales Fax

Corporate Offices

Internet Address



Recycled  
Paper

Revision lines indicate updated or new data.

EG. Printed in U.S.A. 07/14

P/N 9999970290